



# NCR 120-22 NCR 120C-22

## AL-type dies



### Dies for Dual-rated Aluminum Connectors

Dies to be used with the 12 ton tool			Number of crimps per connector <sup>1</sup>						
Type	Wire size	Color code	Anderson	Blackburn®	Burndy	ILSCO	Panduit	T&B	Penn-Union
KA12-8	8 AWG	Blue							
KA12-6	6 AWG	Gray							
KA12-4	4 AWG	Green							
KA12-2	2 AWG	Pink	1	1	1	1	1	1	1
KA12-1	1 AWG	Gold							
KA12-1/0	1/0 AWG	Tan							
KA12-2/0	2/0 AWG	Olive							
KA12-3/0	3/0 AWG	Ruby							
KA12-4/0	4/0 AWG	White	2	2	2	2	2	2	2
KA12-250	250 kcmil	Red							
KA12-300	300 kcmil	Blue							
KA12-350	350 kcmil	Brown							
KA12-400	400 kcmil	Green							
KA12-500	500 kcmil	Pink	3	3	3	3	3	3	3
KA12-600	600 kcmil	Black							
KA12-750	750 kcmil	Yellow							

<sup>1</sup> Use the number of crimps listed in this column instead of the number provided with the connector

When used with Greenlee KA12 die series, the tool (NCR 120-22 & NCR 120C-22) is cULus classified for use with the following connector brands.

Connector type	Barrel type	Anderson	Blackburn®	Burndy	ILSCO	Panduit	T&B	Penn-Union
Dual-rated Aluminum Splice	Short	VACS	ASP	YS-A	AS	SA	60501-60578	PIK
Dual-rated Aluminum Lug	Long	VACL	ATL	YA-A YA-ATN	ACL/ACN 2ACL/2ACN ALNS/ALNN/ALND	LAA/LAB	60101-60176 60230-60278	BLUA





# NCR 120-22 NCR 120C-22

## CU-type dies



### Dies for Copper Connectors

Dies to be used with the 12 ton tool			Number of crimps per connector <sup>1</sup>						
Type	Wire size	Color code	Anderson	Blackburn®	Burndy	ILSCO	Panduit	T&B	Penn-Union
KC12-8	8 AWG	Red							
KC12-6	6 AWG	Blue							
KC12-4	4 AWG	Gray							
KC12-2	2 AWG	Brown							
KC12-1	1 AWG	Green	1	1	1	1	1	1	1
KC12-1/0	1/0 AWG	Pink							
KC12-2/0	2/0 AWG	Black							
KC12-3/0	3/0 AWG	Orange							
KC12-4/0	4/0 AWG	Purple							
KC12-250	250 kcmil	Yellow							
KC12-300	300 kcmil	White							
KC12-350	350 kcmil	Red							
KC12-400	400 kcmil	Blue	2	2	2	2	2	2	2
KC12-500	500 kcmil	Brown							
KC12-600	600 kcmil	Green							
KC12-750	750 kcmil	Black							

<sup>1</sup> Use the number of crimps listed in this column instead of the number provided with the connector

When used with Greenlee KC12 die series, the tool (NCR 120-22 & NCR 120C-22) is cULus classified for use with the following connector brands.

Connector type	Barrel type	Anderson	Blackburn®	Burndy	ILSCO	Panduit	T&B	Penn-Union
Copper Splice	Short	VHSS	CSP	YS-L	CT	SCSS/SCS	54504-54523-TB	BCU
	Long	VHS	CU	YS	CTL	SCL/SCH	54804-54823	BBCU
Copper Lug	Short	VHCS	CTL-2/CTL	YA-2LN/YA-L/YA-2L YA/YA-L-TC/ YA-L-2TC	CSW CRA/CRB CRC	LCAS/LCA LCD/LCAN	54104-54123-TB 54204-54223	BLU
	Long	VHCL	CTL-L/LCN	YA/YAZ YA-2N/YA-2TC YAZ-2N/YAZ-2TC	CLN/CLW CRA-L/CRB-L CRA-2L/CRB-2L/ CRC-2L	LCB/LCC	54930BE-54923BE 54850BE-54880BE	BBLU

