



# METALWORKING — SIMPLE WITH HILTI



Choose the line to meet your needs for performance, productivity, and price.

●●●●● <b>Ultimate</b> Ultimate performance for demanding applications	●●●●○ <b>Premium</b> Premium performance for a wide range of applications	●●●○○ <b>Standard</b> Hilti quality at an economical price
---	---	--

## BONDED CUTTING



	SPX		Diameter	Thickness	Arbor	Type	Qty	Item number	
	SP	P							
Cutting	■	■	4.5"	.040	7/8"	T1	25	2235153	
	■	■	4.5"	.045	7/8"	T1	25	2235154	
	■	■	5"	.040	7/8"	T1	25	2235155	
	■	■	5"	.045	7/8"	T1	25	2235156	
	■	■	6"	.045	7/8"	T1	25	2235157	
	■	■	7"	.045	7/8"	T1	25	2235158	
	■	■	4.5"	.045	7/8"	T1	25	2235159	
	■	■	4.5"	1/8"	7/8"	T1	25	2234757	
	■	■	4.5"	.045	7/8"	T27	25	2235205	
	■	■	5"	.045	7/8"	T1	25	2235170	
	■	■	5"	.045	7/8"	T27	25	2235206	
	■	■	5"	1/8"	7/8"	T1	25	2234758	
	■	■	6"	.045	7/8"	T1	25	2235171	
	■	■	6"	.045	7/8"	T27	25	2235207	
	■	■	6"	1/8"	7/8"	T1	25	2234759	
	■	■	7"	.045	7/8"	T1	25	2235172	
	■	■	7"	.045	7/8"	T27	25	2235176	
	■	■	4.5"	.045	7/8"	T1	25	2235177	
	■	■	4.5"	.045	7/8"	T27	25	2235208	
	■	■	5"	.045	7/8"	T1	25	2235178	
	■	■	5"	.045	7/8"	T27	25	2235181	
	■	■	6"	.045	7/8"	T1	25	2235179	
	■	■	6"	.045	7/8"	T27	25	2235209	
	■	■	7"	.045	7/8"	T1	25	2234753	
	Rough Grinding	■	■	4.5"	1/4"	5/8"-II	T27	10	2235210
		■	■	4.5"	1/4"	7/8"	T27	10	2235183
		■	■	5"	1/4"	5/8"-II	T27	10	2235211
		■	■	5"	1/4"	7/8"	T27	10	2235131
■		■	6"	1/4"	5/8"-II	T27	10	2235212	
■		■	6"	1/4"	7/8"	T27	10	2235132	
■		■	7"	1/4"	5/8"-II	T27	10	2235213	
■		■	7"	1/4"	7/8"	T27	10	2235133	
■		■	9"	1/4"	5/8"-II	T27	10	2235214	
■		■	9"	1/4"	7/8"	T27	10	2235134	
■		■	4.5"	1/4"	5/8"-II	T27	10	2235215	
■		■	4.5"	1/4"	7/8"	T27	10	2235189	
■		■	5"	1/4"	5/8"-II	T27	10	2235191	
■		■	5"	1/4"	7/8"	T27	10	2235136	
■		■	6"	1/4"	5/8"-II	T27	10	2235192	
■		■	6"	1/4"	7/8"	T27	10	2235137	
■		■	7"	1/4"	5/8"-II	T27	10	2235193	
■		■	7"	1/4"	7/8"	T27	10	2235138	
■		■	9"	1/4"	5/8"-II	T27	10	2235194	
■		■	9"	1/4"	7/8"	T27	10	2235139	

## FLAP DISC



	SPX		Dia.	Grit	Arbor	Qty	Item number	
	SP	P						
Flat	■	■	4.5"	60	7/8"	10	2243311	
	■	■	4.5"	36-40	7/8"	10	2243317	
	■	■	4.5"	80	7/8"	10	2243361	
	■	■	5"	80	7/8"	10	2243261	
	■	■	5"	36-40	7/8"	10	2243270	
	■	■	5"	60	7/8"	10	2243373	
	■	■	7"	36-40	7/8"	10	2243275	
	■	■	4.5"	60	5/8"-11	10	2243313	
	■	■	4.5"	80	5/8"-11	10	2243363	
	■	■	4.5"	36-40	5/8"-11	10	2243369	
	■	■	4.5"	36-40	7/8"	10	2243316	
	■	■	4.5"	60	7/8"	10	2243357	
	■	■	4.5"	80	7/8"	10	2243359	
	■	■	4.5"	120	7/8"	10	2243365	
	■	■	5"	80	7/8"	10	2243259	
	■	■	5"	120	7/8"	10	2243265	
	■	■	5"	36-40	7/8"	10	2243268	
	■	■	5"	60	7/8"	10	2243371	
	■	■	7"	36-40	7/8"	10	2243274	
	■	■	5"	80	5/8"-11	10	2243263	
	■	■	5"	36-40	5/8"-11	10	2243272	
	■	■	5"	60	5/8"-11	10	2243375	
	■	■	5"	80	5/8"-11	10	2243264	
	■	■	5"	120	5/8"-11	10	2243267	
	■	■	5"	36-40	5/8"-11	10	2243273	
	■	■	4.5"	60	5/8"-11	10	2243314	
	■	■	4.5"	80	5/8"-11	10	2243364	
	■	■	4.5"	120	5/8"-11	10	2243315	
	■	■	4.5"	36-40	5/8"-11	10	2243370	
	■	■	5"	60	5/8"-11	10	2243258	
	Convex	■	■	4.5"	80	7/8"	10	2243287
		■	■	4.5"	60	7/8"	10	2243325
		■	■	4.5"	36-40	7/8"	10	2243333
		■	■	5"	60	7/8"	10	2243295
		■	■	5"	80	7/8"	10	2243298
		■	■	5"	36-40	7/8"	10	2243301
		■	■	7"	36-40	7/8"	10	2243354
		■	■	4.5"	36-40	5/8"-11	10	2243334
		■	■	4.5"	60	5/8"-11	10	2243285
		■	■	4.5"	80	5/8"-11	10	2243330
■		■	5"	60	5/8"-11	10	2243336	
■		■	5"	36-40	5/8"-11	10	2243303	
■		■	5"	80	5/8"-11	10	2243340	
■		■	7"	36-40	5/8"-11	10	2243355	
■		■	4.5"	120	7/8"	10	2243288	
■		■	4.5"	36-40	7/8"	10	2243290	
■		■	4.5"	60	7/8"	10	2243323	
■		■	4.5"	80	7/8"	10	2243327	
■		■	5"	60	7/8"	10	2243293	
■		■	5"	36-40	7/8"	10	2243299	
■	■	5"	80	7/8"	10	2243337		
■	■	5"	120	7/8"	10	2243342		
■	■	7"	36-40	7/8"	10	2243353		
■	■	5"	60	5/8"-11	10	2243297		
■	■	5"	36-40	5/8"-11	10	2243304		
■	■	4.5"	60	5/8"-11	10	2243286		
■	■	4.5"	80	5/8"-11	10	2243331		
■	■	4.5"	120	5/8"-11	10	2243289		
■	■	5"	80	5/8"-11	10	2243341		
■	■	5"	120	5/8"-11	10	2243344		
■	■	7"	36-40	5/8"-11	10	2243356		

\* Trimmable definition — Traditionally with fiberglass backed flap discs, once the flaps are gone the disc is at the end of its life. With Hilti's new Trimmable Nylon back plate you can trim the edge down to expose new flaps and extend the life of the disc, thus increase productivity.





# METALWORKING — SIMPLE WITH HILTI

Choose the line to meet your needs for performance, productivity, and price.

<b>Ultimate</b> Ultimate performance for demanding applications	<b>Premium</b> Premium performance for a wide range of applications	<b>Standard</b> Hilti quality at an economical price
--	--	---

## FILE BELT



	Dimension (mm)	SPX		Grit	Qty	Item number
		SP	P			
Rough Grinding	13 x 457	■	■	60	20	2243161
	13 x 457	■	■	80	20	2243162
	9 x 457	■	■	40	20	2243008
	9 x 457	■	■	60	20	2243009
	9 x 457	■	■	80	20	2243150
	9 x 457	■	■	120	20	2243151
	13 x 457	■	■	60	20	2243158
	13 x 457	■	■	80	20	2243159
	13 x 457	■	■	120	20	2243160
	30 x 457	■	■	40	20	2243152
	30 x 457	■	■	60	20	2243153
	30 x 457	■	■	80	20	2243156
	30 x 457	■	■	120	20	2243157
Finishing	13 x 457	■	■	Coarse	5	2243381
	13 x 457	■	■	Medium	5	2243382
	13 x 457	■	■	V-Fine	5	2243384
	13 x 457	■	■	Fine	5	2243389

### File Belt Accessories

Dimension (mm)	Description	Qty	Item number
25 x 9	Crowned arm	1	2242232
20 x 30	Small arm	1	2242233
30 x 30	Large arm	1	2242234
25 x 9	Pointed arm	1	2242231
-	Spacing ring set	1	2242230
-	Roller set	1	2242909

## TUBE BELT



	Dimension (mm)	SPX		Grit	Qty	Item number
		SP	P			
Rough Grinding	40 x 760	■	■	60	20	2243154
	40 x 760	■	■	80	20	2243155
	40 x 760	■	■	40	20	2243163
	40 x 760	■	■	60	20	2243164
	40 x 760	■	■	80	20	2243165
	40 x 760	■	■	120	20	2243166
Finishing	40 x 760	■	■	Coarse	10	2243385
	40 x 760	■	■	Medium	10	2243386
	40 x 760	■	■	V-Fine	10	2243388
	40 x 760	■	■	Fine	10	2243390
	40 x 760	■	■	Felt	10	2243397

### Tube Belt Accessories

Description	Qty	Item number
Interchangeable roller set	1	2242017
Guard plate	1	2242908

## WIRE WHEELS



	Description	SPX		Diameter	Qty	Item number
		SP	P			
Knotted / Crimped	Cup brush 3CS knotted	■	■	4.5"	6	41362
	Cup brush 3SS knotted	■	■	4.5"	6	41367
	Cup brush 4CS-BX knotted	■	■	4.5"	2	53733
	Cup brush 3CS crimped	■	■	4.5"	6	41363
	Cup brush 4CS-BX crimped	■	■	4.5"	2	53736
Full Cable / Str. Bead	Wheel brush 4CS full cable	■	■	4.5"	6	41365
	Wheel brush 4CS str. Bead	■	■	4.5"	6	41364
	Wheel brush 4SS str. Bead	■	■	4.5"	6	41366

## FIBER DISC



	Diameter	Grit	Qty	Item number
Rough Grinding	4.5"	36-40	25	2243218
	5"	36-40	25	2243251
	4.5"	60	25	2243216
	5"	60	25	2243253
	4.5"	80	25	2243220
	5"	80	25	2243255
	4.5"	24	25	2243240
	5"	24	25	2243222
	4.5"	36-40	25	2243214
	5"	36-40	25	2243249
	4.5"	60	25	2243238
	5"	60	25	2243221
	4.5"	80	25	2243208
	5"	80	25	2243219
	4.5"	120	25	2243209
	5"	120	25	2243217
	7"	36-40	25	2243226
	7"	36-40	25	2243229
	4.5"	36-40	25	2243212
	5"	36-40	25	2243247
	4.5"	60	25	2243239
	5"	60	25	2243223
	4.5"	80	25	2243210
	5"	80	25	2243215
	4.5"	120	25	2243211
	5"	120	25	2243213

### Back Pads

Diameter	Qty	Item number
7" hard	1	2243183
4.5" med	1	2243193
5" med	1	2243197
4.5" hard	1	2243176
5" hard	1	2243178

## BURNISHER



	Dimension (mm)	SPX		Grit	Qty	Item number	
		SP	P				
Rough Grinding	100	■	■	60	20	2243171	
	100	■	■	80	20	2243172	
	100	■	■	40	20	2243167	
	100	■	■	60	20	2243168	
	100	■	■	80	20	2243169	
	100	■	■	120	20	2243170	
	100	■	■	240	1	2243376	
	100	■	■	60	1	2243377	
	100	■	■	80	1	2243378	
	100	■	■	40	1	2243379	
	Finishing	100	■	■	Felt	5	2243392
		100	■	■	V-Fine	5	2243410
100		■	■	Coarse	5	2243411	
100		■	■	Medium	5	2243412	
100		■	■	Fine	5	2243413	
100		■	■	V-Fine	1	2243414	
100		■	■	Medium	1	2243416	

### Burnisher Accessories

Description	Qty	Item number
Dust extr. Hood	1	2240615
Inflatable expansion roller	1	2242019
Protective cover	1	2240612
Air pump	1	2240613
Parallel guide	1	2240616

