



# WORK WITH HILTI TO BECOME COMPLIANT WITHOUT ANY HASSLE

## 1926.1153 silica dust standards Table 1 compliance


The listed packages will provide you with the item numbers you need to build a 1926.1153 Table 1 compliant system. Let us do the rest.




### Instructions for ordering:

- If you need a new tool:** use the compliance kits listed below to order your tool with the correct accessory and vacuum
- If you have a tool already:** use the retrofit kits listed on page two to order the package you need to become Table 1 compliant
- If you want a new tool and a different vacuum:** use the tool item listed below under the 'single tool' column and the retrofit kit listed on page two


## SDS-MAX COMBIHAMMERS

Description	Compliance kit	Tool only
 <b>TE 50-AVR</b> includes VC 150-10 X	3561759	3553052
<b>TE 60-AVR</b> includes VC 150-6 X	3564155	3564151
<b>TE 60-ATC-AVR</b> includes VC 150-6 X	3564156	3564152
<b>TE 70-AVR</b> includes VC 150-10 X	3561762	3514170
<b>TE 70-ATC-AVR</b> includes VC 150-10 X	3561853	3514171
<b>TE 80-ATC-AVR</b> includes VC 150-10 X	3561854	2083438


## BREAKERS

Description	Compliance kit	Tool only
 <b>TE 500-AVR</b> includes VC 150-10 X	3561855	3512856
<b>TE 700-AVR</b> includes VC 150-6 X	3561856	3484793
<b>TE 800-AVR</b> includes VC 150-6 X	3561857	3531084
<b>TE 1000-AVR</b> includes VC 150-10 X	3561858	3523418
<b>TE 1500-AVR</b> includes VC 150-10 X	3561859	3455943
<b>TE 3000-AVR</b> includes VC 150-10 X	3561860	3492616

## ANGLE GRINDER CUTTING / GRINDING

Description	Compliance kit	Tool only
 <b>AG 450-7D cutting</b> includes a VC 125-6	3564375	3554440
<b>AG 450-7D grinding</b> includes VC 125-6	3564377	3554440
<b>AG 450-7D tuck pointing</b> includes VC 125-6	3564379	3554440
<b>AG 450-7S cutting</b> includes VC 125-6	3564374	3554361
<b>AG 450-7S grinding</b> includes a VC 125-6	3564376	3554361
<b>AG 450-7S tuck pointing</b> includes a VC 125-6	3564378	3554361
<b>5" Deadman cutting</b> includes a VC 150-10 X	3562165	3564653
<b>5" Deadman grinding</b> includes a VC 150-10 X	3562166	3564653
<b>5" Deadman tuck pointing</b> includes a VC 150-10 X	3562173	3564653
<b>5" Side switch cutting</b> includes a VC 150-10 X	3562167	3564654
<b>5" Side switch grinding</b> includes a VC 150-10 X	3562168	3564654
<b>5" Side switch tuck pointing</b> includes a VC 150-10 X	3562172	3564654

## SAWING/GRINDING

Description	Compliance kit	Tool only
 <b>DCH 230 DRS kit*</b> includes a VC 300-17 X	3564392	n/a
<b>DCH 300 DRS kit*</b> includes a VC 300-17 X	3564393	n/a
<b>DG 150 DRS kit</b> includes a VC 150-10 X	3564394	n/a

\*Hilti interprets the DCH tools as being a Table 1 "handheld grinder"









# COMPLY ON YOUR OWN TERMS

Hilti vacuums

The nomenclature of the vacuums will tell you everything you need to know about the features:

VC	150	-10	X	E
Vacuum cleaner	CFM rating check required cfm in sections xi and xii of 1926.1153 table 1	Tank capacity (in gallons)	If self-cleaning filter	If onboard outlet (11A Max)

Description							
		<b>VC 125-6</b> 6 gallons Manual filter-cleaning mechanism	<b>VC 125-9</b> 9 gallons Manual filter-cleaning mechanism	<b>VC 150-6 X</b> 6 gallons Self-cleaning filter	<b>VC 150-10 X</b> 10 gallons Self-cleaning filter	<b>VC 150-6 XE</b> 6 gallons Self-cleaning filter 11A outlet onboard	<b>VC 150-10 XE</b> 10 gallons Self-cleaning filter 11A outlet onboard
<b>DRS-S</b>	For rotary hammers with a depth gauge	3564007	3564280	3562118	3562119	3564278	3562120
<b>DRS-Y</b>	For Hilti SDS-max combihammers	3564282	3564363	3562121	3562122	3564281	3562153
<b>DRS-B</b>	For all Hilti breakers (not TE 3000)	3564009	3564010	3562154	3562155	3564008	3562156
<b>DRS 3000</b>	For only Hilti TE 3000	3564012	3564373	3562157	3562158	3564011	3562159
<b>4-1/2" cutting hood</b>	For cutting or tuck pointing with Hilti 4-1/2" angle grinders	3564381	3564391	3562160	3562161	3564389	3562181
<b>4-1/2" grinding hood</b>	For grinding with Hilti 4-1/2" angle grinders	3564390	3564382	3562179	3562180	3564380	3562162
<b>5" cutting hood</b>	For cutting or tuck pointing with Hilti 5" angle grinders	3564384	3564385	3562169	3562170	3564383	3562171
<b>5" grinding hood</b>	For grinding with Hilti 5" angle grinders	3564387	3564388	3562176	3562177	3564386	3562178

**HILTI BROUGHT THE FIRST HOLLOW DRILL BIT SYSTEM WITH NO MANUAL HOLE CLEANING FOR CHEMICAL ANCHOR INSTALLATION TO THE MARKET IN 2013**

Utilize these packages to purchase a 1926.1153 Table 1 compliant solution for chemical anchoring\*



Description	Package content	Item number
<b>HY 200-R TE 50 AVR SafeSet pack</b>	TE 50-AVR, VC 150-6 X, (40 tubes) HIT-HY 200-R 500/1/WH, HDE 500-A 18, 2x B 18/1.6 Li-ion, Charger C 4/36 Li-ion, HIT-CR 500, 2x TE-YD 3/4"-24", 2x TE-YD 7/8"-24", Toolbag small	3553983
<b>HY 200-R TE 70 AVR/ATC SafeSet pack</b>	TE 70 AVR/ATC, VC 150-10 X, (40 tubes) HIT-HY 200-R 500/1/WH, HDE 500-A 18, Charger C 4/36 Li-ion, 2x B 18/1.6 Li-ion, HIT-CR 500, 2x TE-YD 3/4"-24", 2x TE-YD 7/8"-24", Toolbag small	3501746
<b>RE 500 V3 TE 50 AVR SafeSet pack</b>	TE 50-AVR, VC 150-6 X, (40 tubes) HIT-RE 500 V3 500/500/1, HDE 500-A 18, 2x B 18/1.6 Li-ion, Charger C 4/36 Li-ion, HIT-CR 500, 2x TE-YD 3/4"-24", 2x TE-YD 7/8"-24", Toolbag small	3553984
<b>RE 500 V3 TE 70 AVR/ATC SafeSet pack</b>	TE 70 AVR/ATC, VC 150-10 X, (40 tubes) HIT-RE 500 V3 500/500/1, HDE 500-A 18, Charger C 4/36 Li-ion, 2x B 18/1.6 Li-ion, HIT-CR 500, 2x TE-YD 3/4"-24", 2x TE-YD 7/8"-24", Toolbag small	3537466

\*When the Hilti hollow drill bits are used with a Hilti vacuum, no HEPA filter is required since there is no separate hole cleaning



Hilti, Inc. (U.S.) 1-800-879-8000  
en español 1-800-879-5000

www.hilti.com

