CERTIFICATE OF COMPLIANCE

 Certificate Number
 2021-04-30-EX15279

 Report Reference
 EX15279-1994-04-22

EX15279-1999-08-23 EX15279-1999-08-24 EX15279-2009-03-20 EX15279-2017-08-14

Issue Date 2021-APRIL-30

Issued to: HILTI AKTIENGESELLSCHAFT

Feldkircherstrass 100

P.O. Box 333

Schaan, 9494 Liechtenstein

This is to certify that Hangers, Pipe

representative samples of Hangers, Pipe Certified for Canada

See addendum below for models

Have been investigated by UL in accordance with the

Standard(s) indicated on this Certificate.

Standard(s) for Safety: CAN/UL 203 – Pipe Hanger Equipment for Fire Protection

Service

Additional Information: See the UL Online Certifications Directory at

www.ul.com/database for additional information

Only those products bearing the UL Certification Mark should be considered as being covered by UL's Certification and Follow-Up Service.

Look for the UL Certification Mark on the product.

Ba Wally

Bruce Mahrenholz, Director North A

Bruce Mahrenholz, Director North American Certification Program

UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at http://ul.com/aboutul/locations/



CERTIFICATE OF COMPLIANCE

2021-04-30-EX15279 **Certificate Number** EX15279-1994-04-22 **Report Reference**

> EX15279-1999-08-23 EX15279-1999-08-24 EX15279-2009-03-20 EX15279-2017-08-14

2021-APRIL-30 **Issue Date**

Pipe hangers

		Rod Size,		
Model	Hanger Type	in.	NPS*	Comments
MAB- M10	Universal Beam Clamp	M10	4	_
MAB-11	Universal Beam Clamp	M10	4	_
MAB- M12	Universal Beam Clamp	M12	8	_
MAB-13	Universal Beam Clamp	M12	8	
MAB- M16	Universal Beam Clamp	M16	12	_
MAB-17	Universal Beam Clamp	M16	12	
LH	Band Hanger	3/8	1/2, 3/4, 1, 1-1/4, 1-1/2, 2, 2- 1/2, 3, 4	_
LH	Band Hanger	1/2	6, 8	_
MP-SP	Band Hanger	10 mm	Up to 4	_
MP-SP	Band Hanger	12 mm	5, 6	_
MP-SP	Band Hanger	16 mm	8	_
SDC-EG	Clevis Hanger	3/8	1/2, 3/4, 1, 1-1/4, 1-1/2, 2	_
SDC-EG	Clevis Hanger	1/2	2-1/2, 3	_
SDC-EG	Clevis Hanger	5/8	4, 5	_



Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, product a local UL Customer Service Representative at http://ul.com/aboutul/locations/



CERTIFICATE OF COMPLIANCE

Certificate Number 2021-04-30-EX15279 EX15279-1994-04-22 **Report Reference**

> EX15279-1999-08-23 EX15279-1999-08-24 EX15279-2009-03-20 EX15279-2017-08-14

2021-APRIL-30 **Issue Date**

SDC-EG	Clevis Hanger	3/4	6, 8	_
SDC-EG	Clevis Hanger	7/8	10, 12	_
SLC-EG	Clevis Hanger	3/8	2, 2-1/2	_
SLC-EG	Clevis Hanger	1/2	3	_
SLC-EG	Clevis Hanger	5/8	4, 5	_
SLC-EG	Clevis Hanger	3/4	6, 8	_
MP-SPN	Loop Hanger	M10	3/4, 1, 1-1/4, 1-1/2, 2, 2-1/2, 3, 4	
MP-SPN	Loop Hanger	M12	133mm, 5, 159 mm, 6	_
MP-SPN	Loop Hanger	M16	219.1 mm	_
MP-US	U-Strap	N/A	1/2, 3/4, 1, 1-1/4, 1-1/2, 2, 2- 1/2, 3, 3-1/2, 108mm, 4, 133mm, 5, 159mm, 6, 8, 10, 12	Can be installed on the bottom, side, or top (surge restraint) orientations
MP-UB (metric)	U-Bolt	N/A	1/2, 3/4, 1, 1-1/4, 1-1/2, 2, 2- 1/2, 3, 3-1/2, 108mm, 4, 133mm, 5, 159mm, 6, 8, 10, 12	Metric threads; Can be installed on the bottom, side, or top (surge restraint) orientations
MP-UB (NPT)	U-Bolt	N/A	1-1/2, 2, 2-1/2, 3, 3-1/2, 4, 5, 6, 8, 10, 12	NPT threads; Can be installed on the bottom, side, or top (surge restraint) orientations
MP-MS	Pipe Clamp	10 mm	1/2, 3/4, 1, 1-1/4, 1-1/2, 2, 2- 1/2, 3	_
MP-MS	Pipe Clamp	12 mm	4, 5, 6	_
MF-TSH	Trapezoidal Bracket	10 mm	3/4, 1	_

^{*} NPS = Nominal pipe size



Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, product a local UL Customer Service Representative at http://ul.com/aboutul/locations/

