

VERSATILE DIAMOND CORING SYSTEM WITH CONNECTIVITY

Core rig DD 150-U

Perform a wide variety of handheld or rig mounted coring applications like through penetrations and blind holes with new enhancements to the core rig DD 150-U that help make diamond coring easier than ever.

Experience improved efficiency with new features that include a real-time display with operator controls, usage statistics, service messages, and more. Also added is Bluetooth connectivity that seamlessly pairs with the water management system WMS 100 BLE so operators can easily manage water management status and access usage statistics via the Hilti Connect app.



Order information	
Description	Item number
Handheld coring tool DD 150-U BI	3685890
Handheld coring tool DD 150-U BI + Stand	3679403
Handheld coring tool DD 150-U BI + Stand + Core bit SPX-L	3679404

Accessories	
Description	Item number
Water management system WMS 100 BLE	3679407
Vacuum pump DD VP-U 120V	408998



- Ideal for rig-based wet drilling in concrete for pipe penetrations, cable trays, ducts, and railings and barriers
- · Hand-guided wet drilling for setting anchors & rebar
- Hand-guided dry drilling in masonry for pipe penetrations in plumbing & HVAC installations
- High motor performance and sturdy three-speed gearing offers optimum drilling speed
- Comfortable grip with 360° adjustable side handle, featuring integrated dust and water management function
- Real-time digital display with spirit level, gear selector, power control, advanced usage stats and service messages

recillical data	
Diameter range	3/8" - 6-1/4"
Base material	Concrete, Masonry
Operation mode	Hand-held or rig-mounted drilling system
Number of gears	3
No load RPM	Gear 1 - 840 rpm; Gear 2 -1640 rpm; Gear 3 - 3070 rpm
Weight according EPTA-Procedure 01/2003	18.4
Weight of complete system	48 lb
Dimensions (LxWxH)	20.3 x 5.1 x 6.3 in
A-weighted emission sound pressure level	89 dB(A)



Technical data



Tool warranty.