

L-RATIN	UL SYSTEM NO. C-AJ-2898 CONCRETE FLOOR/WALL OR BL F-RATING = 3-HR. T-RATING = 3-HR. IG AT AMBIENT = LESS THAN 1 CFM / SQ ING AT 400°F = LESS THAN 1 CFM / SQ F) FT	CAJ2898b.072221
B. ANY UL CLASSIFIED CONCRE	EIGHT CONCRETE FLOOR OR WALL (MI		D
ACCOMMODATE SEALANT. 4. MINIMUM 1" DEPTH HILTI FS-ONE 5. HILTI CP 648E WRAP STRIP (NOMI THE OUTER CIRCUMFERENCE OF PLACE WITH TAPE. BUTTED ENDS SHALL BE INSTALLED AND BUTTE 6. FIRST HILTI RETAINING COLLAR S OVERLAPPING 2" AND SECURED W OF RETAINING COLLAR TO BOTTO BOLTS, 3/16" x 1-1/2" LONG CONCH FASTENERS WITH 1-7/16" DIAMETE ANCHOR, 1/4" x 1-3/4" HILTI KWIK- ACTUATED FASTENERS WITH INTI 7. SECOND HILTI RETAINING COLLA WITH ENDS OVERLAPPING 2" AND	WOOL (MIN. 4 PCF DENSITY) TIGHTLY P MAX INTUMESCENT FIRESTOP SEALAN NAL 3/16" THICK x 1-3/4" WIDE) CONTINU THE PIPE, COVERING FOUR TIMES, WITH IN SUCCESSIVE LAYER SHALL BE OFFS D TIGHTLY TO BOTTOM SURFACE OF FI SHALL BE WRAPPED AROUND TOP LAYE WITH TWO NO. 8 SHEET METAL SCREWS OM SURFACE OF FLOOR WITH 1/4" x 1-1/4 RETE SCREW ANCHORS, MIN. 0.145" x 1- ER STEEL WASHER, 1/4" x 1-1/4" HILTI KN BOLT 3 STEEL EXPANSION ANCHOR, OF EGRATED WASHER. R SHALL BE WRAPPED AROUND BOTTO SECURED WITH FOUR NO. 8 SHEET METAL COLLAR WITH ONE NO. 8 SHEET METAL	T. JOUSLY WRAPPED AROU HENDS BUTTED AND HEL SET. TWO STACKS OF 4 LA LOOR. ER OF WRAP STRIPS WITH S. SECURE EVERY OTHER 4" LONG STEEL EXPANSIO 1/4" POWDER ACTUATED WIK-CON II+ CONCRETE S R HILTI X-DNI 27 P8 S15 PC DM LAYER OF WRAP STRIFT TAL SCREWS. SECURE EV	D IN AYERS I ENDS TAB DN CREW DWDER
NOTES : 1. MAXIMUM DIAMETER OF OPENING = 10". 2. ANNULAR SPACE = MINIMUM 0", MAXIMUM 1-1/4". 3. HILTI CP 648E WRAP STRIP WITH RETAINING COLLAR AND HILTI FS-ONE MAX INTUMESCENT FIRESTOP SEALANT ARE REQUIRED ON EACH SIDE OF A WALL ASSEMBLY.			
Hilti Firestop Systems	HILTI, Inc. Plano, Texas USA (800) 879-8000 ives through Innovation and Educ	Scale - C Date July 22, 2021 28	wing No. CAJ 98b