HSP/HFP Drywall Anchor 3.3.18

3.3.18.1 Product Description

The Hilti HSP/HFP Drywall Anchor is a self-drilling anchor designed for fast and reliable fastenings in drywall.

Product Features

- Shark tooth design for correct positioning and quick installation
- Cuts its own thread, no predrilling necessary

- Can be set with electric or standard screwdriver for quick and simple installation
- Removability adds to the anchor versatility
- Available in non-conductive nylon or zinc for a variety of applications
- Available with and without screws for your convenience

3.3.18.1	Product Description
3.3.18.2	Material Specifications
3.3.18.3	Technical Data
3.3.18.4	Installation Instructions
3.3.18.5	Ordering Information



3.3.18.2 Material Specifications

HSP Die cast zinc conforming to ASTM B86

HFP Polyamide 6.6 plastic; glass fiber reinforced

3.3.18.3 Technical Data

HSP/HFP Drywall Anchor Allowable Loads¹

Gypsum Wall Board Thickness	1/2"				5/8"			
Description	Tension		Shear		Tension		Shear	
Description	lb	(N)	lb	(N)	lb	(N)	lb	(N)
HSP with Screw # 8 x 1-3/16	15	(70)	35	(155)	24	(105)	55	(245)
HFP with Screw # 8 x 1-3/16	15	(70)	35	(155)	24	(105)	55	(245)

¹ Based on using a safety factor of 4.

3.3.18.4 Installation Instructions

Installation Instructions For Use (IFU) are included with each product package. They can also be viewed or downloaded on line at www.us.hilti.com (US) and www.hilti.ca (Canada). Because of the possibility of changes, always verify that downloaded IFU are current when used. Proper installation is critical to achieve full performance. Training is available on request. Contact Hilti Technical Services for applications and conditions not addressed in the IFU.

3.3.18.5 Ordering Information

	Anchor		
Description	Length (in.)	Screw Dia.	Box Qty
HSP	1-1/2	# 8	100
HSP-S Delivered with 100 screws, # 8 x 1-1/4"	1-1/2	# 8	100
HFP	1-1/2	# 8	100
HFP-S Delivered with 100 screws, # 8 x 1-1/4"	1-1/2	# 8	100
D-B PH2 HSP/HFP Phillips Head Bit	-	-	5