## **UL/cUL SYSTEM NO. FW-D-1141**


## FIRE-RATED JOINT THROUGH CONCRETE FLOOR ASSEMBLY


**ASSEMBLY RATING = 3-HR.** 

CLASS II MOVEMENT CAPABILITIES - 12.5% COMPRESSION AND 4% EXTENSION
L-RATING AT AMBIENT = LESS THAN 1 CFM / LIN FT
L-RATING AT 400°F = LESS THAN 1 CFM / LIN FT

**TOP VIEW** 

**SECTION A-A** 





- 1. CONCRETE WALL ASSEMBLY:
  - A. LIGHTWEIGHT OR NORMAL WEIGHT CONCRETE WALL (MINIMUM 4-1/2" THICK).
  - B. ANY UL/cUL CLASSIFIED CONCRETE BLOCK WALL.
- 2. LIGHTWEIGHT OR NORMAL WEIGHT CONCRETE FLOOR ASSEMBLY (MINIMUM 4-1/2" THICK).
- 3. MINIMUM 4-1/2" THICKNESS MINERAL WOOL SAFING (MIN. 4 PCF DENSITY) COMPRESSED MINIMUM 42%.
- 4. MINIMUM 1/8" (WET) THICKNESS HILTI CFS-SP SIL FIRESTOP SILICONE JOINT SPRAY APPLIED WITHIN THE JOINT, FLUSH WITH TOP SURFACE OF FLOOR AND OVERLAPPING MINIMUM 3/4" ONTO THE TOP SURFACE OF THE FLOOR AND SIDE OF THE WALL.

NOTE: MAXIMUM WIDTH OF JOINT = 3".



HILTI, Inc. Plano, Texas USA (800) 879-8000

Sheet	1 of 1
Scale	11/64" = 1"
Date	Jan. 05, 2022

FWD 1141a

Saving Lives through Innovation and Education