UL/cUL SYSTEM NO. FF-D-0155

FIRE-RATED JOINT THROUGH CONCRETE FLOOR ASSEMBLY


ASSEMBLY RATING = 3-HR.


CLASS II AND CLASS III MOVEMENT CAPABILITIES - 25% COMPRESSION OR EXTENSION

TOP VIEW

SECTION A-A

FFD0155a.062521





- 1. LIGHTWEIGHT OR NORMAL WEIGHT CONCRETE FLOOR (MINIMUM 4-1/2" THICK) (3-HR. FIRE-RATING).
- 2. MINIMUM 4" THICKNESS MINERAL WOOL SAFING (MIN. 4 PCF DENSITY) COMPRÉSSED MINIMUM 50% AND RECESSED TO ACCOMMODATE FIRESTOP JOINT SPRAY.
- 3. MINIMUM 1/8" (WET) THICKNESS HILTI CFS-SP WB FIRESTOP JOINT SPRAY APPLIED WITHIN THE JOINT, FLUSH WITH TOP SURFACE OF FLOOR.

NOTE: MAXIMUM WIDTH OF JOINT = 1".



HILTI, Inc. Plano, Texas USA (800) 879-8000

Sheet	1 of 1
Scale	7/32" = 1"
Date	June 25, 2021

FFD 0155a

Saving Lives through Innovation and Education