

FIRESTOP SLEEVE KIT (CFS-SL SK)

Product description

- The Hilti Firestop Sleeve Kit offers a more economical and intuitive solution for properly firestopping new cable applications requiring a sleeve
- Offered in 2" and 4" diameter versions
- Standard Kit includes (1) sleeve (2) flanges (2) firestop plugs (2) rubber gaskets

Product features

- Faster, easier, more intuitive installation for new cable runs
- Easier to install correctly
- Simpler to inspect
- Re-penetrable for future cable capacity
- Pre-cured, pre-formed firestop material does not expire, eliminating shelf-life concerns
- Protects most typical firestop penetration applications
- 4" diameter device is compatible with the Hilti Gangplate CFS-SL GP
- Buy American compliant
- Meets LEED™ requirements for indoor environmental quality credit 4.1 Low Emitting Materials
- Low VOC content and no CFCs or HCFCs

Areas of application

- Single and bundled cables in gypsum and CMU/Concrete
- New cable applications with a sleeve

Installation instructions

- See Hilti literature or third-party listings for complete application and installation details



Technical Data

	2" Device	4" Device
OD (device only)	2.5"	4.5"
OD (flange)	4.7"	6.7"
ID (device only)	2.3"	4.3"
Total length	10.5 in	
Expansion ratio (unrestricted)	Approx. 1:3	
Temperature resistance	5° F to 140° F (-15° C to 60° C)	
Intumescent activation	Approx. 392° F (200° C)	
Surface burning characteristics (ASTM E 84-10b)	Flame Spread: 10 Smoke Development: 15	
Tested in accordance with	ASTM E 814 CAN/ULC-S115 UL 1479 ASTM E 84 (CFS-PL only)	

