

CFS-MSL GPR RETROFIT GANGPLATES

Product description

· Surface-mounted gangplates for installing modular fire sleeves after drywall

Product features

- Includes ready-to-install smoke gasket no additional products required
- Modular design for easier customization you can combine different sizes of fire-rated sleeves within one frame
- Retrofittable design for easier installation in existing cable openings
- · Withstands the rigors of usage and time
- Can be installed in wall applications (not for floors)
- · Can be stacked in rows or columns
- Buy American Compliant

Areas of application

· Cable and cable bundles

For use with

· Gypsum wall systems rated up to 2 hours

Examples

- Electrical wiring
- Premise wiring
- Low voltage and datacom

Installation instructions

 See Hilti literature or third-party listings for complete application and installation details











Technical Data

9 x 4" (229 x 102mm)	12 x 4" (305 x 102mm)
13" (330mm)	16" (406mm)
0.8" (20mm)	0.8" (20mm)
6" (152mm)	6" (152mm)
-22 °F to 167 °F (-30 °C to 75 °C)	
Steel with zinc coating	
UL 1479 ASTM E 814 CAN/ULC-S115	
	13" (330mm) 0.8" (20mm) 6" (152mm) -22 °F to 167 °F (-30 °C Steel with zinc coating UL 1479 ASTM E 814







