
## **UL/cUL SYSTEM NO. C-AJ-0183**


## BLANK OPENING THROUGH CONCRETE FLOOR/WALL OR BLOCK WALL ASSEMBLY

F-RATING = 2-HR. T-RATING = 2-HR.

T-RATING =
TOP VIEW

SECTION A-A





- 1. CONCRETE FLOOR OR WALL ASSEMBLY (2-HR. FIRE-RATING) :
  - A. LIGHTWEIGHT OR NORMAL WEIGHT CONCRETE FLOOR (MINIMUM 4-1/2" THICK).
  - B. LIGHTWEIGHT OR NORMAL WEIGHT CONCRETE WALL (MINIMUM 5" THICK).
  - C. ANY UL/cUL CLASSIFIED CONCRETE BLOCK WALL.
- 2. MINIMUM 4" THICKNESS MINERAL WOOL (MIN. 4 PCF DENSITY) TIGHTLY PACKED AND RECESSED FROM TOP SURFACE OF FLOOR, OR BOTH SURFACES OF WALL.
- 3. MINIMUM 1/2" DEPTH HILTI FS-ONE MAX INTUMESCENT FIRESTOP SEALANT.

NOTES: 1. MAXIMUM AREA OF SQUARE, RECTANGULAR, OR CIRCULAR OPENING IS 160 SQ. IN., WITH A MAXIMUM DIMENSION OF 32".

2. MINIMUM 1/2" DEPTH HILTI FS-ONE MAX INTUMESCENT FIRESTOP SEALANT IS REQUIRED ON BOTH SIDES OF A WALL.



HILTI, Inc. Plano, Texas USA (800) 879-8000

Sheet	1 of 1
Scale	7/64" = 1"
Date	Nov. 21, 2022

CAJ 0183a