



MULTIPLE METAL PENETRANTS THROUGH CONCRETE FLOOR

F-RATING = 3-HR.

T-RATING = 1-HR.

TOP VIEW**SECTION A-A**

FA1225a.092623

1. LIGHTWEIGHT OR NORMAL WEIGHT CONCRETE FLOOR (MINIMUM 4-1/2" THICK) (3-HR. FIRE-RATING).
2. PENETRATING ITEMS TO BE ANY COMBINATION OF THE FOLLOWING (MAXIMUM QUANTITY = 4) :
 - A. MAXIMUM 1-1/2" NOMINAL DIAMETER STEEL PIPE (SCHEDULE 5 OR HEAVIER).
 - B. MAXIMUM 1-1/2" NOMINAL DIAMETER STEEL CONDUIT OR STEEL EMT.
 - C. MAXIMUM 1" NOMINAL DIAMETER COPPER PIPE OR TUBING.
3. HILTI CFS-CID U [2", 3", 4", OR 6"] OR CFS-CID U 2" CA CAST-IN FIRESTOP DEVICE CAST OR GROUTED INTO CONCRETE FLOOR WITH A MAXIMUM 2" EXTENSION ABOVE FLOOR.
4. MINIMUM 2" THICKNESS MINERAL WOOL (MINIMUM 4 PCF DENSITY) TIGHTLY PACKED AND FLUSH WITH TOP OF FIRESTOP DEVICE.

NOTES : 1. ANNULAR SPACE BETWEEN PENETRANTS = MINIMUM 1/4", MAXIMUM 1-1/2".
 2. ANNULAR SPACE BETWEEN PENETRANTS AND DEVICE = MINIMUM 1/4",
 MAXIMUM 1-1/2".

HILTI
 Hilti Firestop Systems

HILTI, Inc.
 Plano, Texas USA (800) 879-8000

Sheet	1 of 1
Scale	5/32" = 1"
Date	Sep. 26, 2023

Drawing No.

FA
1225a

Saving Lives through Innovation and Education