


UL SYSTEM NO. F-A-2410
PVC SHOWER DRAIN THROUGH CONCRETE FLOOR


F-RATING = 2-HR.
T-RATING = 0-HR.

FA2410a.092723

TOP VIEW



SECTION A-A



1. LIGHTWEIGHT OR NORMAL WEIGHT CONCRETE FLOOR (MINIMUM 4-1/2" THICK) (2-HR. FIRE-RATING).
2. HILTI CFS-CID U [2", 3", 4", OR 6"] OR CFS-CID U 2" CA CAST-IN FIRESTOP DEVICE CAST OR GROUTED INTO CONCRETE FLOOR. DEVICE TO BE CUT FLUSH WITH TOP SURFACE OF THE CONCRETE.
3. MAXIMUM 2" NOMINAL DIAMETER PVC PLASTIC PIPE (SCHEDULE 40) (CELLULAR OR SOLID CORE) WITH PVC SHOWER DRAIN FITTING.
4. MINERAL WOOL (MINIMUM 4 PCF DENSITY) TIGHTLY PACKED INTO THE DEVICE FLUSH WITH TOP SURFACE OF THE FLOOR. MINERAL WOOL IS OPTIONAL WHEN HILTI CFS-CID U 2" OR CFS-CID U 2" CA CAST-IN FIRESTOP DEVICE IS USED.



HILTI, Inc.
Plano, Texas USA (800) 879-8000

Sheet	1 of 1
Scale	5/32" = 1"
Date	Sep. 27, 2023

Drawing No.

**FA
2410a**

Saving Lives through Innovation and Education