UL/cUL SYSTEM NO. C-AJ-0081


BLANK OPENING IN CONCRETE FLOOR/WALL OR BLOCK WALL

F-RATING = 4-HR. T-RATING = 4-HR.

L-RATING AT AMBIENT= LESS THAN 1 CFM/SQ. FT.

L-RATING AT 400°F= LESS THAN 1 CFM/SQ. FT.

TOP VIEW SECTION A-A



- 1. CONCRETE FLOOR OR WALL ASSEMBLY (4-HR. FIRE-RATING):
 - A. LIGHTWEIGHT OR NORMAL WEIGHT CONCRETE FLOOR OR WALL (MINIMUM 4-1/2" THICK).
 - B. ANY UL/ULC CLASSIFIED CONCRETE BLOCK WALL.
- 2. FORMING NOT SHOWN. USE A RIGID BOARD MATERIAL TO SUPPORT HILTI CP 637 FIRESTOP MORTAR DURING ITS INITIAL CURE.
- 3. MINIMUM 4-1/2" DEPTH HILTI CP 637 FIRESTOP MORTAR.

NOTE: MAXIMUM AREA OF OPENING = 1024 SQ. IN. WITH A MAX. DIM. OF 32".



HILTI, Inc. Tulsa, Oklahoma USA (918) 252-6000

| Sheet | 1 of 1 |
|-------|---------------|
| Scale | 1/16" = 1" |
| Date | Feb. 21, 2002 |

CAJ 0081b

Saving Lives through Innovation and Education