

UL/cUL SYSTEM NO. C-AJ-8178

HVAC LINE SET THROUGH CONCRETE FLOOR/WALL OR BLOCK WALL ASSEMBLY

F-RATING = 2-HR. T-RATING = 1/4-HR., 1/2-HR., 1-HR. OR 1-3/4-HR.

BOTTOM VIEW







HILTI, Inc. Tulsa, Oklahoma USA (800) 879-8000

Sheet	1 of 2
Scale	7/32" = 1"
Date	Jan. 06, 2015

CAJ 8178c

Saving Lives through Innovation and Education

UL/cUL SYSTEM NO. C-AJ-8178

HVAC LINE SET THROUGH CONCRETE FLOOR/WALL OR BLOCK WALL ASSEMBLY

F-RATING = 2-HR.

T-RATING = 1/4-HR., 1/2-HR., 1-HR. OR 1-3/4-HR.

- 1. CONCRETE FLOOR OR WALL ASSEMBLY (2-HR. FIRE-RATING) :
 - A. LIGHTWEIGHT OR NORMAL WEIGHT CONCRETE FLOOR OR WALL (MINIMUM 4-1/2" THICK).
 - B. PRECAST (HOLLOW-CORE) CONCRETE FLOOR (MINIMUM 6" THICK).
 - C. ANY UL/cUL CLASSIFIED CONCRETE BLOCK WALL.
- 2. PENETRATING ITEM TO BE ANY OF THE FOLLOWING (MAX. QTY. = 2):
 - A. MAXIMUM 1" NOMINAL DIAMETER STEEL PIPE (SCHEDULE 10 OR HEAVIER).
 - B. MAXIMUM 1" NOMINAL DIAMETER CAST OR DUCTILE IRON PIPE.
 - C. MAXIMUM 1" NOMINAL DIAMETER COPPER PIPE OR TUBING.
 - D. MAXIMUM 1/2" NOMINAL DIAMETER STEEL CONDUIT OR EMT.
- 3. NOMINAL 3/4" THICK AB/PVC PIPE INSULATION INSTALLED ON METALLIC PIPES LARGER THAN NOMINAL 1/2" DIAMETER.
- 4. MAXIMUM 4 PAIR NO. 18 AWG THERMOSTAT CABLE WITH PVC JACKET.
- 5. PENETRATING ITEM TO BE ONE OF THE FOLLOWING:
 - A. MAXIMUM 1-1/4" NOMINAL DIAMETER PVC PLASTIC PIPE (CELLULAR OR SOLID CORE).
 - B. MAXIMUM 1-1/4" NOMINAL DIAMETER CPVC PLASTIC PIPE (CLOSED PIPING SYSTEM ONLY).
- 6. MINIMUM 1/2" DEPTH HILTI FS-ONE MAX OR FS-ONE INTUMESCENT FIRESTOP SEALANT APPLIED FLUSH WITH BOTTOM OF FLOOR AND APPLIED WITHIN INTERSTICES OF PENETRANTS TO MAXIMUM EXTENT POSSIBLE.
- 7. HILTI CP 643N FIRESTOP COLLAR WITH FASTENING HOOKS.
- 8. EACH FASTENING HOOK SECURED TO BOTTOM OF FLOOR WITH 1/4" x 1-1/4" LONG STEEL EXPANSION BOLTS, MIN. 0.145" x 1-1/4" POWDER ACTUATED FASTENERS WITH 1-7/16" DIAMETER STEEL WASHER, 1/4" x 1-1/4" HILTI KWIK-CON II+ CONCRETE SCREW ANCHOR, 1/4" x 1-3/4" HILTI KWIK-BOLT 3 STEEL EXPANSION ANCHOR, OR HILTI X-DNI 27 P8 S15 POWDER ACTUATED FASTENER WITH INTEGRATED WASHER.

ANNULAR SPACE	MINIMUM	MAXIMUM
BETWEEN METALLIC PIPES AND PERIPHERY OF OPENING	1/2"	1"
BETWEEN INSULATED PIPES AND PERIPHERY OF OPENING	0"	1"
BETWEEN CABLE AND PERIPHERY OF OPENING	1/2"	1"
BETWEEN NONMETALLIC PIPE AND PERIPHERY OF OPENING	0"	1"
BETWEEN PENETRANTS	0"	1"

NOTES: 1. MAXIMUM DIAMETER OF OPENING = 4".

- 2. MAXIMUM DIAMETER OF OPENING TO MATCH DIAMETER OF COLLAR USED.
- 3. CLOSED OR VENTED PIPING SYSTEM (PVC = SCHEDULE 40; CPVC = SDR 13.5).
- 4. HILTI CP 643N FIRESTOP COLLARS AND HILTI FS-ONE MAX OR FS-ONE INTUMESCENT FIRESTOP SEALANT ARE REQUIRED ON BOTH SIDES OF A WALL ASSEMBLY.



HILTI, Inc. Tulsa, Oklahoma USA (800) 879-8000

Sheet	2 of 2
Scale	-
Date	Jan. 06, 2015

CAJ 8178c

Saving Lives through Innovation and Education