
UL/cUL SYSTEM NO. F-C-7042

MECHANICAL SUPPORT MEMBER THROUGH WOOD FLOOR/CEILING ASSEMBLY

F-RATING = 1-HR. T-RATING = 0-HR.



- 1. WOOD FLOOR/CEILING ASSEMBLY (UL/cUL CLASSIFIED L500 SERIES) (1-HR. FIRE-RATING).
- 2. PENETRATING ITEM TO BE ONE OF THE FOLLOWING:
 - A. MAXIMUM 1-5/8" x 1-5/8" GALVANIZED OR PAINTED STEEL CHANNEL STRUT (MINIMUM 0.105" THICK).
 - B. MAXIMUM 3-1/4" x 1-5/8" GALVANIZED OR PAINTED STEEL "H" STRUT (MINIMUM 0.105" THICK).
 - C. MAXIMUM 3/8" DIAMETER UNJACKETED GALVANIZED STEEL CABLE.
 - D. MAXIMUM 1" DIAMETER GALVANIZED THREADED STEEL ROD.
 - E. MAXIMUM 2" x 2" x 1/8" THICK STEEL ANGLE.
- 3. MINIMUM 3/4" DEPTH HILTI FS-ONE MAX OR FS-ONE INTUMESCENT FIRESTOP SEALANT OR HILTI CP 606 FLEXIBLE FIRESTOP SEALANT.
- 4. MINIMUM 5/8" DEPTH HILTI FS-ONE MAX OR FS-ONE INTUMESCENT FIRESTOP SEALANT OR HILTI CP 606 FLEXIBLE FIRESTOP SEALANT.
 - NOTES: 1. MAXIMUM SIZE OF OPENING = 5" x 3" [OR MAXIMUM 3" DIAMETER].
 - 2. ANNULAR SPACE = MINIMUM 1/8", MAXIMUM 7/8".
 - 3. PENETRANT MAY BE INSTALLED AT AN ANGLE NOT GREATER THAN 45° FROM PERPENDICULAR.
 - 4. [NOT SHOWN, OPTIONAL] CHASE WALL THE THROUGH PENETRANT MAY BE ROUTED THROUGH A 1-HR. FIRE-RATED UL CLASSIFIED U300 SERIES WALL ASSEMBLY.



HILTI, Inc. Tulsa, Oklahoma USA (800) 879-8000

Sheet	1 of 1
Scale	3/16" = 1"
Date	Jan. 08, 2015

FC 7042b