## UL/cUL SYSTEM NO. FF-D-0055

## FIRE-RATED JOINT THROUGH CONCRETE FLOOR ASSEMBLY

ASSEMBLY RATING = 2-HR. OR 3-HR.


CLASS II MOVEMENT CAPABILITIES - 6% OR 12.5% COMPRESSION OR EXTENSION
L-RATING AT AMBIENT = LESS THAN 1 CFM / LIN FT

L-RATING AT 400°F = LESS THAN 1 CFM / LIN FT

**TOP VIEW** 

**SECTION A-A** 

FFD0055b.060121



- 1. LIGHTWEIGHT OR NORMAL WEIGHT CONCRETE FLOOR ASSEMBLY (2-HR. OR 3-HR. FIRE-RATING):
  - A. MINIMUM 4-1/2" THICK (2-HR FIRE-RATING).
  - B. MINIMUM 6" THICK (3-HR FIRE-RATING).
- 2. MINERAL WOOL SAFING (MIN. 4 PCF DENSITY) COMPRESSED 50% (SEE TABLE BELOW).
- 3. HILTI CP 606 FLEXIBLE FIRESTOP SEALANT (SEE TABLE BELOW).

ASSEMBLY RATING	MAX JOINT WIDTH	MIN THICKNESS OF MINERAL WOOL	MIN DEPTH HILTI CP 606
3-HR.	2"	5"	1/2"
2-HR.	2"	2"	1/2"
2-HR.	1"	2-1/2"	1/4"

NOTE: JOINT SYSTEM IS DESIGNED TO ACCOMMODATE A MAX 6% COMPRESSION OR EXTENSION FOR 3-HR. RATING AND MAX 12.5% COMPRESSION OR EXTENSION FOR 2-HR. RATING.



HILTI, Inc. Plano, Texas USA (800) 879-8000

Sheet	1 of 1
Scale	3/16" = 1"
Date	June 01, 2021

FFD 0055b

Saving Lives through Innovation and Education