

SIMPLE AND RELIABLE LASERS.

Line laser PM 2-L and Plumb laser PM 2-P

Arrive on the job with the highest accuracy and maximum versatility with the latest line and plumb lasers from Hilti. With one-button operation and always-on “Pulse Power” technology, the latest Hilti lasers drive productivity on the toughest jobs. And because Hilti offers the industry's best service, including laser calibration, you can be confident in your accuracy.



PULSE III POWER

Technical Data	PM 2-L	PM 2-P
Laser functions	Leveling and aligning	Transferring points
Accuracy at 30' / 10 m	± 1/8" (3 mm)	± 1/8" (3 mm)
Self-leveling range	±4°	±4°
Self-leveling time	<3 sec	<3 sec
Operating distance	33 ft (10 m) With receiver: 98 ft (30 m)	98 ft (30 m)
Laser class	635 nm, class 2 (IEC 825-1), class II (FDA 21 CFR)	635 nm, class 2 (IEC 825-1), class II (FDA 21 CFR)
IP protection class (except battery compartment)	IP 54 as per IEC 529 std	IP 54 as per IEC 529 std
Operating temperature	14° F to + 122° F (-10° C to + 50° C)	14° F to + 122° F (-10° C to + 50° C)
Battery type	Alkaline (4 AA)	Alkaline (4 AA)
Operating time	20 h	20 h
Dimensions (L x W x H)	4.2 x 2.2 x 3.75 in (107 x 65 x 95 mm)	4.2 x 2.5 x 5.4 in (107 x 63 x 137 mm)

Order Information

Description	Package Contents	Item No.
Line laser PM 2-L	Includes tool, pouch, (4) AA batteries and operating instructions in a cardboard box	02047044
Plumb laser PM 2-P	Includes tool, pouch, (4) AA batteries and operating instructions in a cardboard box	02047037

Applications

PM 2-L

- Leveling junction boxes, cable trays, radiators and pipe installations
- Leveling suspended ceilings
- Leveling and aligning doors and windows
- Transferring reference heights
- Aligning pipes or conduit

PM 2-P

- Transferring points from the floor to the ceiling
- Checking vertical alignment of columns

Outperform

- Small pocket size design for use in tight spots
- Free calibration service for highest tool accuracy with Hilti Tool Fleet Management

PM 2-L

- Two laser lines to perform a multitude of applications for maximum versatility
- Laser lines with ideal shape and brightness for maximum visibility

PM 2-P

- Fixed foot with integrated magnets to attach to drywall tracks for greatest ease of use
- Two laser points for plumb applications

Outlast

- Large rubberized tool body to protect laser aperture and tool edges for increased durability
- Improved protection against dropping for the toughest jobsite conditions



Hilti. Outperform. Outlast.

Hilti, Inc. (U.S.) | 1-800-879-8000 | en español 1-800-879-5000 | www.us.hilti.com | Hilti (Canada) Corp. | 1-800-363-4458 | www.hilti.ca

