

RUGGED AND RELIABLE.

Plumb and square laser PMP 45

With one-button tool operation and Pulse Power technology, the Hilti Plumb and square laser PMP 45 drives productivity and maximizes versatility. Hilti's innovative Impact Protection System provides assurance that your PMP 45 will outperform – even under the toughest jobsite conditions. And since Hilti offers the industry's best service, including laser calibration, you can be confident that your Hilti laser is both rugged and reliable.



Outperform

- Ideal shape and brightness of beam provides maximum visibility
- Fixed foot with integrated magnets attach to drywall tracks
- Hilti calibration service for highest tool accuracy
- Five laser beams for maximum versatility

Outlast

- Rugged housing for greater durability
- Impact Protection System helps protect the core of the tool and maximizes durability; laser module protected 100% of the time
- Supported by Hilti Lifetime Service (Visit Hilti Online for more information)



Order Information

Description	Package Contents	Item No.
Plumb and square laser PMP 45	Includes: tool, removable foot, pouch, (4) AA batteries and operating instructions in a cardboard box	00411279

Technical Data	PMP 45
Laser functions	Transferring vertical and horizontal points, plumbing, and squaring
Self-leveling range	±5°
Dimensions (L x W x H)	4-1/5" x 2-1/2" x 3-3/4" (107mm x 65mm x 96mm)
Weight	14.56 ounces (413 grams)
Battery type	Alkaline
Operating time with alkaline battery	30 h
IP protection class (except battery compartment)	IP 54
Laser class	Class II
Measuring distance	Min / max 3' (1m)/100' (30m)
Accuracy at 30' (10m)	± 1/8" (3mm)
Self-leveling time	<3 sec
Operating temperature range	14° F to + 122° F (-10° C to + 50° C)

Hilti. Outperform. Outlast.

