

Applications

- Quickly set and check slopes digitally
- Easily create control lines with the batter board adapter
- Efficiently install curtain wall with the facade adapter

Outperform

- Shock absorbing casing, improved internal damping system and four shock-absorbing handles allow for drop-resistance from standard working height
- Simple and intuitive to use with best in class leveling time
- Digital slope measurement and slope e-targeting provides high accuracy and fast results

Outlast

- Rugged and durable



Accessories

PRA 90 Automatic Tripod Kit  03508190

PUA 20 Tripod  00400934

PRA 760 Facade Adapter  ① 00435439

PRA 750 Batter Board Adapter  ② 00435441

PRA 751 Batter Board Receiver Holder  ② 00435442

PRA 20 Laser Receiver  02071121



Jobsite tough.

PR 30-HVS Rotating Laser

From leveling formwork and setting digital slopes outdoors, to aligning and layout work indoors, the PR 30-HVS does it all. Designed to resist a drop from a tripod at standard working height, the PR 30-HVS brings reliability and durability to a new level. Improved keypads and an integrated remote/laser receiver allow for maximum convenience and efficiency. The optional PUA 90 Automatic Tripod can be controlled with the same remote/laser receiver and makes automatic horizontal alignment a fast and easy one person task.



*Some limitations apply. Contact Hilti for details.



PULSE III POWER

Technical Data	PR 30-HVS
Accuracy (at 75°F / 24°C)	±1/8 inch at 100 ft (±2.3 mm at 30 m)
Operating range with laser receiver	Diameter: 7 ft – 1,640 ft (2 – 500 m)
Operating range of radio remote	Distance: up to 246 ft (75 m)
Digital slope range (single)	-15% to +8.6%
Battery Life (at 73°F / 23°C)	Li-Ion rechargeable (tool): 25 hours
Laser class (red visible beam)	<4.85mW, 620-690nm, Class 2 (IEC 60825-1:2007), class II (FDA CFR 21 art. 1040)
IP protection	IP 66 (IEC 529)
Operating temperature	-4°F to 122°F (-20°C to 50° C)
Dimensions (L x W x H)	7.9 x 7.9 x 9.1 in (200 x 200 x 230mm)
Weight	5.5 lb (2500 g)

Order Information

Description	Package Contents	Item No.
PR 30-HVS Rotating Laser	Includes tool, Li-Ion battery, charger, remote/laser receiver with holder, and operating instructions in an impact-resistant plastic case	02068483
PR 30-HVS Contractor Kit	Includes tool, Li-Ion battery, charger, remote/laser receiver with holder and operating instructions in an impact-resistant plastic case, plus PRA 79 slope adapter and PUA 20 tripod	03508189
PR 30-HVS with Automatic Tripod PRA 90	Includes tool, Li-Ion battery, charger, remote/laser receiver with holder and operating instructions in an impact-resistant plastic case, plus PRA 90 Automatic Tripod Kit (including battery and charger)	03508188

Hilti. Outperform. Outlast.