High visibility just got better. PRI 36 Green Rotating Laser

The beam from the PRI 36 Green Rotating Laser shines four times brighter than a conventional red laser beam, ensuring significantly better visibility over long distances. Hilti Pulse Power Technology delivers highly reliable readings even under bright light conditions. The PRI 36 laser receiver and remote control are combined into one device for convenient access to tool functions from afar. This tough tool is designed to be used horizontally and vertically, making it the pros' choice for a wide variety of applications.



PULSE **III POWER**

Technical Data	PRI 36	
Accuracy (at 75°F / 24°C)	±1/8 inch at 100 ft (±3 mm at 30 m)	
Operating range with laser receiver	Diameter: 7 ft - 984 ft (2 m - 300 m)	
Operating range of radio remote	Distance: up to 328 ft (100 m)	
Battery Life (at 73°F / 23°C)	Li-Ion rechargeable (tool): 24 hours	
Laser class (green visible beam)	< 4.5 mW, 532 nm, Class 3R (IEC 825- 1:2007), Class IIIa (FDA CFR 21 art. 1040)	
IP protection	IP 56 (IEC 529)	
Operating temperature	-4°F to 113°F (-20°C to 45°C)	
Dimensions (L x W x H)	9.9 x 9.9 x 8.2 in (252 x 252 x 209 mm)	
Weight	5.3 lb (2400 g)	

Order Information

Description	Package Contents	Item No.
PRI 36 Green Rotating Laser	Includes tool, Li-Ion battery, charger, remote/laser receiver, green target plates and operating instructions in an impact-resistant plastic case	02044076
PRI 36 with PRA 71 Wall Mount Bracket	Includes tool Li-Ion battery, charger, remote/laser receiver, green target plates PRA 71 wall mount bracket and operating instructions in an impact-resistant plastic case	03508186

Hilti. Outperform. Outlast.

Hilti, Inc. (U.S.) 1-800-879-8000 **www.us.hilti.com** • en español 1-800-879-5000 Hilti (Canada) Corporation 1-800-363-4458 • **www.hilti.ca**

Applications

- Transferring reference heights
- Leveling suspended ceiling
- Positioning drywall track
- Installing pipes and cable trays

Outperform

- Green laser provides up to four times better visibility and a finer, more accurate line compared to a conventional red beam
- Auto-alignment function for quick, automatic laser alignment at the touch of a button

Outlast

- Rugged and reinforced housing material with four handles
- A fully enclosed rotating head for indoor and outdoor protection



Accessories

f

You Tube

REPAIR COST LIMIT

*Some limitations apply. Contact Hilti for details

MANUFACTURE

