



Fire Finish 120+ CFP-SP WB

Approved Topcoat List

For interior applications, a topcoat is not required for our Hilti Fire Finish 120+ CFP-SP WB . For exterior conditions, a UL exterior approved topcoat is required for our Hilti Fire Finish 120+ CFP-SP WB which is highlighted below. Reference our application guide for cure times prior applying an approved top coat. **Please verify before use. "✓" means approved for use.**

Revised September 2025

Manufacturer	Brand Name	Resin Type	FF 120+
BEHR	Interior/ Exterior Alkyd Semi-Gloss NO. 3900	Alkyd	✓
BEHR	MARQUEE Interior Semi-Gloss Enamel 3400 Series	Enamel	✓
Benjamin Moore	Impervex Latex High Gloss Enamel 309	Acrylic	✓
Benjamin Moore	Moorglo	Acrylic Latex	✓
Benjamin Moore	Ultra Spec 500 N538	Waterborne Acrylic	✓
Cardinal	Elite Metallic X6S23-99-2 Acrylic Urethane	Acrylic Polyurethane	✓
Cardinal	X Guard Epoxy Primer 7067-4702	Epoxy	✓
DOWSIL	758 Silicone Weather Barrier Sealant	Silicone Weather Barrier Sealan	✓
Dulux	Liftmaster Interior 100% Acrylic 59311	Waterborne Acrylic	✓
International Paint/ Akzo Nobel	Interthane 900	Acrylic Polyurethane	✓
Jotun	Hardtop XP	Acrylic Polyurethane	✓
Kelly-Moore	1050 Premium Professional Latex Interior Semi-	Latex Enamel	✓
Kelly-Moore	1520 EnviroCoat 100% Acrylic Interior Semi-Gloss	Acrylic Enamel	✓
Kelly-Moore	1610 AcryPlex 100% Acrylic Interior Eggshell Enamel	Acrylic Enamel	✓
Kelly-Moore	1685 DuraPoxy 100% Acrylic Interior Semi-Gloss Enamel	Acrylic Enamel	✓
Mascoat	Industrial AC	Ceramic Insulation	✓
PPG	Pitthane Ultra 95-812 Series	Acrylic Aliphatic Urethane	✓
PPG	PSX 700	Engineered Siloxane	✓
PPG	Speedhide 6-500 Series	Acrylic Latex	✓
PPG	Speedhide Series 6-70	Vinyl Acrylic Latex	✓
PPG	SPEEDHIDE Zero 6-4310 Series	Vinyl Acrylic Latex	✓
PPG	SPPEDHIDE Zero Latex Eggshell 6-411	Enamel	✓
PPG	Ultra Hide 150 1210-0100G Series	Vinyl-Acrylic Resin	✓
Sherwin Williams	Acrolon 218 HS Acrylic Polyurethane B65-600 Series	Acrylic Polyurethane	✓
Sherwin Williams	Armorseal Rexthane I Floor Coating B65-60 Series	Aliphatic Urethane	✓
Sherwin Williams	Armorseal Tread-Plex B90 Series	Acrylic	✓
Sherwin Williams	Envirolastic 980 PA B65-940 Series	Polyaspartic Urethane	✓
Sherwin Williams	Hi-Solids Polyurethane 250 (UL Exterior Approved)	Acrylic Polyurethane	✓
Sherwin Williams	Metalatex Semi-Gloss B42-100 Series	100% Acrylic Emulsion	✓
Sherwin Williams	Pro Ind. Acrolon 100 B65-700 Series (UL Exterior Approved)	Waterbased Urethane	✓
Sherwin Williams	Pro Industrial Acrylic Gloss B66-600 Series	Acrylic	✓
Sherwin Williams	Pro Industrial DTM Acrylic Primer B66 Series	Acrylic	✓
Sherwin Williams	ProMar 200 B31-2600 Series	Acrylic Latex	✓
Sherwin Williams	Sher-Cryl HPA	Acrylic	✓
Sherwin Williams	Steel Master 9500 B56-300 Series	Silicone Alkyd	✓
Sherwin Williams	Pro Industrial WB Catalyzed B73-300 Series	Epoxy	✓
Tnemec	Enduralume Series 1077	Aliphatic Acrylic Polyurethane	✓
Tnemec	Endura-Shield Series 73	Aliphatic Acrylic Polyurethane	✓
Tnemec	Endura-Shield Series 1095	Aliphatic Acrylic Polyurethane	✓
Tnemec	Enduratone Series 1028	HDP Acrylic Polymer	✓
Tnemec	F.C. Typoxy Series 27	Epoxy	✓
Tnemec	Floronar Metallic Series 1078	Fluoropolymer	✓
Tnemec	Uni-Bond DF Series 115	Hydrophobic Acrylic	✓