



MT-50 C / MT-75 C / MT-100 G

MT-50 U / MT-75 U

8x M10-SN      8x M10x20

15

MT-50 U / MT-75 U

MT-50 C / MT-75 C

MT-100 G

min. 4 mm  
max. 9 mm

**3**

	MT-50 C	MT-75 C	MT-100 G
MT-50 U			
MT-75 U			

2x

2x

2x

2x

**4**

15

40 Nm  
 $T_{inst}$  (30 ft-lbs)

40 Nm  
 $T_{inst}$  (30 ft-lbs)