

Измервателна техника

Лазерни далекомири

 PD 38	300.00 лв.
PD 4	100.00 лв.
PD 40	145.00 лв.
PD 42	263.00 лв.
PD 5	70.00 лв.

Комбиниранни лазерни уреди

 PMC 36	475.00 лв.
PMC 46	325.00 лв.

Линейни лазерни уреди

PML 42	167.00 лв.
--------	------------

Точкови лазерни уреди

Означение	
PMP 34	350.00 лв.
PMP 45	167.00 лв.

Оптични уреди

POL 10	120.00 лв.
POL 15	148.00 лв.
 POT 10 e-mail to RCS	938.00 лв.

Лазерни ротационни уреди

 PR 25	913.00 лв.
PR 35	938.00 лв.
PRI 2	738.00 лв.

Уреди за сканиране

PS 200	5,389.00лв.
PS 30	113.00 лв.
PS 35	250.00 лв.
PS 38	375.00 лв.
PX 10	250.00 лв.

Рязане и шлифование

Шлайф машини

WFE 380	122.00 лв.
WFE 450	150.00 лв.
WFO 280	147.00 лв.

Циркуляри

 WSC 255	189.00 лв.
WSC 255 KE	234.00 лв.
 WSC 265	244.00 лв.
WSC 265 KE	266.00 лв.
 WSC 55 generation II+ only	187.00 лв.
WSC 55-A	169.00 лв.
WSC 70	214.00 лв.
WSC 70-A	155.00 лв.
WSC 85	310.00 лв.
SCW 22-A	110.00 лв.

Триони

WSJ 750	163.00 лв.
WSJ 850	188.00 лв.
 WSR 1000 generation II+ only	244.00лв.
WSR 1250	268.00 лв.
WSR 1400	351.00 лв.
WSR 22-A	105.00 лв.
WSR 36-A	250.00 лв.
WSR 650-A	181.00 лв.
 WSR 900	221.00 лв.

Ударно-пробивна къртеща техника

Къртачи

TE 104	325.00 лв.
TE 500	563.00 лв.
 TE 504	448.00 лв.
TE 505	488.00 лв.
TE 700	538.00 лв.
 TE 704	724.00 лв.
TE 705	651.00 лв.
TE 706	713.00 лв.
TE 805	729.00 лв.
TE 905	859.00 лв.
TE 1000	835.00 лв.
TE 1500	988.00 лв.
TE 3000	1,225.00 лв.

Ударно-пробивни машини

TE 1	68.00 лв.
TE 2	126.00 лв.
TE 2-M	185.00 лв.
TE 2-S	136.00 лв.
TE 5	180.00 лв.
TE 6-C	201.00 лв.
TE 6-S	193.00 лв.
TE 7	119.00 лв.
TE 7-C	211.00 лв.
TE 15	290.00 лв.
TE 15-C	358.00 лв.
TE 16	277.00 лв.
TE 16-C	340.00 лв.
TE 30	285.00 лв.
TE 30-C	350.00 лв.
TE 30-M	475.00 лв.
TE 35	484.00 лв.
TE 40	488.00 лв.

Акумулаторни ударно-пробивни машини

TE 4-A	150.00 лв.
TE 5-A	217.00 лв.
TE 6-A	217.00 лв.
TE 7-A	220.00 лв.

Комбиниранни ударно-пробивни машини

TE 46	521.00 лв.
 TE 50	521.00 лв.
TE 55	599.00 лв.
TE 56	599.00 лв.
TE 56-ATC	703.00 лв.
 TE 60 generation II only	625.00 лв.
TE 60-ATC	703.00 лв.
TE 70	754.00 лв.
TE 70-ATC	862.00 лв.
 TE 75	736.00 лв.
TE 76	798.00 лв.
TE 76-ATC	833.00 лв.

Директен монтаж

Газови уреди за директен монтаж

GX 100	595.00 лв.
GX 120 (ME)	533.00 лв.

Уреди за директен монтаж

DX 351	410.00 лв.
DX 450	309.00 лв.
DX 460	404.00 лв.
DX 462	727.00 лв.
DX 600 N	300.00 лв.
DX 750	680.00 лв.
DX 76	730.00 лв.
 DX-A 40	354.00 лв.
 DX-A 41	404.00 лв.

Диамантна техника

Диамантно-пробивни системи

DD EC-1	1,005.00 лв.
DD100	1,008.00 лв.
DD 110	734.00 лв.
DD 120	876.00 лв.
DD 130-M	972.00 лв.
DD 150-U	975.00 лв.
DD 160-E	966.00 лв.
DD 200	1,220.00 лв.
DD 250-E	1,241.00 лв.
DD 350	1,700.00 лв.
DD 400	1,839.00 лв.
DD 500	2,175.00 лв.
DD 750-HY 16	4,718.00 лв.
DD 80-E	681.00 лв.

Стенорезни машини

DS-TS 20-E	18,875.00 лв.
DS-TS 22	17,750.00 лв.
DS-TS 30	5,171.00 лв.
DS-TS 32	27,250.00 лв.
DS-TS 5	11,775.00 лв.
DS-TS 5-SE	11,204.00 лв.
DS-WS 15	25,750.00 лв.
DS-WSS 30	10,063.00 лв.
LP 15 400-V	5,157.00 лв.
LP 30 380-V	12,316.00 лв.
TS 30-54	4,846.00 лв.
TS 32	22,641.00 лв.
D RC - LP 32	1,042.00 лв.
DST 10-E	13,800.00 лв.
D RC - LP 15	2,347.00 лв.

Ъглошлайфи

AG 125-S	101.00 лв.
AG 230-S	143.00 лв.
DAG 125	78.00 лв.
DAG 230	105.00 лв.
 DC 180-S	139.00 лв.
 DC 230-S	195.00 лв.
DCG 125	153.00 лв.
DCG 180	155.00 лв.
DCG 230	188.00 лв.
DEG 125	127.00 лв.
DEG 150	132.00 лв.

Уреди за рязане на канали

DCH 180	505.00 лв.
DCH 230	345.00 лв.
DCH 300	408.00 лв.
DC-SE 20	525.00 лв.
DG 150	918.00 лв.
DSH 700	556.00 лв.
DSH 900	600.00 лв.

Праходмукачки

VC 20	255.00 лв.
VC 40	310.00 лв.
VC 40-UM	340.00 лв.
VC 60	464.00 лв.
VCD 50	461.00 лв.
VCU 40	294.00 лв.
VC 20-UM	310.00 лв.

Инжекционни уреди

ED 3500	238.00 лв.
P 3000 – F	392.00 лв.
P 8000	738.00 лв.

Винтонавивна техника

Винтонавивни машини за сухото строителство

SD 5000	88.00 лв.
SD 5000-A	80.00 лв.
SF 4000	93.00 лв.
SF 4000-A	385.00 лв.

Винтонавивни машини за метални конструкции

ST 1800	158.00 лв.
ST 2500	119.00 лв.

Винтонавивна техника

SF 121	150.00 лв.
SF 151	333.00 лв.
SI 100	254.00 лв.

Акумулаторни винтонавивни машини

SF 14-A	73.00 лв.
SF 144-A	80.00 лв.
SF 22-A	90.00 лв.
SFC 14-A	62.00 лв.
SFC 22-A	68.00 лв.
SFH 14-A	83.00 лв.
SFH 144-A	94.00 лв.
SFH 22-A	98.00 лв.
SID 14-A	73.00 лв.
SID 144-A	88.00 лв.
SIW 14-A	73.00 лв.
SIW 144-A	88.00 лв.
SIW 22T-A	130.00 лв.

Бормашини

TKI 2500	224.00 лв.
UD 16	158.00 лв.
UD 30	158.00 лв.
SR 16	146.00 лв.

Стативи

DD-ST 120	445.00 лв.
DD-HD	806.00 лв.
DD REC-1	945.00 лв.
DD-ST 130	562.00 лв.
DD-ST 150-U	533.00 лв.
DD-ST 160	413.00 лв.

Обявените цени са без ДДС.

Легенда:



- 2-ри период за ремонт!



- ВНИМАНИЕ!