

Direct Fastening

Hilti. Outperform. Outlast.





Gas Systems

Gas-actuated tool GX 120
Gas can and nails for GX 120

Page 87
Page 88

Gas-actuated tool GX 120



Applications

- Repetitive fastening in drywall installation on concrete, screed, sand-lime block, rendered masonry and steel
- Drywall profiles on floors, walls and ceilings

Advantages

- No battery to charge so no need for a charger
- Magazine for 40 nails: very fast when used for repetitive fastening
- Very economical system for fastenings in the lower load range
- Wide range of nails: the right nail for a variety of materials



Technical data

Power (max.)	100 J
Weight	3.9 kg
Base materials	Concrete, Steel, Block, Masonry, Brick (sand-lime)
Automatic piston return	Yes
Noise (power) level: LWA, 1s	105 dB (A)
Dimensions (LxWxH)	431 x 134 x 392 mm
Max. fastener driving rate	1200 / h
Fastener intake	40 nails
Fastener length range	14 - 39 mm

¹⁾ Declared measured values of noise characteristics according to 2006/42/EC Machinery Directive in conjunction with E DIN EN 15895



Direct
Fastening

Ordering designation	Package contents	Sales pack quantity	Item number
GX 120 + X-EGN 14 Combo	1x Gas actuated tool GX 120, 1x Gas can GC21 + 750x Nails X-EGN 14 MX, 1x Drift punch X-120 NP, 1x Ear protectors, 1x Case	1	3498063
GX 120 + X-GN20 MX Combo	1x Gas actuated tool GX 120, 1x Gas can GC21 + 750x Nails X-GN20 MX, 1x Drift punch X-120 NP, 1x Ear protectors, 1x Case	1	3497722
GX 120 + X-GN27 MX Combo	1x Gas actuated tool GX 120, 1x Gas can GC21 + 750x Nails X-GN27 MX, 1x Drift punch X-120 NP, 1x Ear protectors, 1x Case,	1	3498064
GX 120 + X-GN32 MX Combo	1x Gas actuated tool GX 120, 1x Gas can GC21 + 750x Nails X-GN32 MX, 1x Drift punch X-120 NP, 1x Ear protectors, 1x Case	1	3498065
GX 120 + X-GN39 MX Combo	1x Gas actuated tool GX 120, 1x Gas can GC21 + 750x Nails X-GN39 MX, 1x Drift punch X-120 NP, 1x Ear protectors, 1x Case	1	3498066
GX 120 + X-GHP18 Combo	1x Gas actuated tool GX 120, 1x Gas can GC21 + 750x Nails X-GHP18 MX, 1x Drift punch X-120 NP, 1x Ear protectors, 1x Case	1	3498067
GX 120 + X-GHP20 Combo	1x Gas actuated tool GX 120, 1x Gas can GC21 + 750x Nails X-GHP20 MX, 1x Drift punch X-120 NP, 1x Ear protectors, 1x Case	1	3498068

GX 120 gas can GC 21

Applications

- For use with GX 120 tool



Advantages

- Maximum performance and reliability with the Hilti GX 120 systems

Technical data

For use with	GX 120, GX 120-ME
--------------	-------------------

Ordering designation	Sales pack quantity	Item number
GC 21	1	38865

Nail for use with gas-actuated tools X-GN MX



Advantages

- Robust nail with low driving failure rate

Technical data

For use with	GX 100, GX 100-E, GX 120, GX 120-ME
--------------	-------------------------------------

Ordering designation	Sales pack quantity	Item number
Gas nail X-GN20MX	750	340232
Gas nail X-GN27MX	750	340230
Gas nail X-GN32MX	750	340233
Gas nail X-GN39MX	750	340234

Nail for use with gas-actuated tools X-GHP MX



Applications

- Fastening to hard concrete

Advantages

- Robust nail with low driving failure rate

Technical data

For use with	GX 100, GX 100-E, GX 120, GX 120-ME
--------------	-------------------------------------

Ordering designation	Sales pack quantity	Item number
Gas nail X-GHP18MX	750	340228
Gas nail X-GHP 20MX	750	285724

Nail for use with gas-actuated tools X-EGN MX

Applications

- Fastening drywall track to steel



Advantages

- Ballistic point and high hardness for excellent performance on steel

Technical data

For use with	GX 100, GX 100-E, GX 120, GX 120-ME
--------------	-------------------------------------

Ordering designation	Sales pack quantity	Item number
Gas nail X-EGN 14MX	750	340231