



SHIPPING LABEL INSTRUCTIONS


Please carefully read the instructions below. Not every situation will apply to every package, so please follow what does apply. **Labels in color must be printed in color or it will not comply with USDOT regulations.**

General Shipping Guideline – Returns and Repairs to Hilti

In order to ensure your package arrives quickly to the Hilti facility, please follow the steps below. Please remove all consumables and material from the tool kit box before shipping. Hilti will not be responsible for items shipped with the tool. Failure to follow these steps could result in delayed or misplaced shipments and subject to fines from UPS.

Limited Quantity Products – Booster, Gas Canisters

1. Before placing the UPS label on the box, double check that no diamond label marking or any other hazard identifying labels are visible anywhere on the box.
2. If a diamond label is on the box please remove or cover up the label unless specifically instructed to do otherwise. In this case you will be provided a label.





SHIPPING LABEL INSTRUCTIONS

Gas Saw Shipping Instructions

Gas saws cannot be shipped in the air without special approval. When shipped on the ground (i.e. parcel, LTL, or courier), gas saws must follow the below instructions:

1. Check gas tank for any liquid.
2. Drain all gas.
3. Purge fumes until tank is dry.
4. Replace gas cap and tighten securely.
5. Place saw in a plastic bag and seal.
6. Place bagged saw in a sturdy box.
7. Provide plenty of packaging material.

When gas tank is dry, shipping gas saws requires no special labeling or documentation.

Hilti Vacuum Shipping Instructions

The waste container of the vacuum may or may not contain hazardous materials and must be removed as a precaution to avoid any hazardous goods shipping.

1. Remove the bottom waste container from the vacuum.
2. Enclose the vacuum head in a plastic bag or trash bag.
3. Place the plastic bag in a sturdy box.
4. Provide plenty of packaging material.

When the waste container is removed from the vacuum, shipping requires no special labeling or documentation.

Hilti Lithium Battery Shipping Instructions

DOT regulations require that the proper label be placed on the outside of the box when shipping lithium ion batteries that are not greater than 300 watt hours.


Shipping instructions for ground only, air restricted

1. Always pack the battery in a strong and sturdy box.
2. When shipping the battery inside the tool kit box, ensure that the kit box is placed inside another cardboard box.
3. The total weight of the box cannot exceed 65 pounds.
4. Cut the below label and tape near the UPS label with clear tape.
5. Shipment may only be sent via ground services.
6. Use UN3480 label for individual batteries by themselves
7. Use UN3481 if the battery is either contained in equipment or packed with equipment (internal in a laser or packed in a case with a tool, not attached)
8. Forbidden label must accompany whichever UN battery marking you are using for the return shipment

Label Instructions

Cut the below label and tape near the UPS label with clear tape

**LITHIUM BATTERIES
FORBIDDEN FOR
TRANSPORT ABOARD
AIRCRAFT AND VESSEL**



OR



UN3481

For emergencies only. Call: CHEMTREC
1-800-424-9300 NORTH AMERICA
1-703-527-3887 INTERNATIONAL