

## **Product Information**

# FIRESTOP TOP TRACK SEAL CFS-TTS MD P FLUTE PLUG & CFS-TTS MD C FLUTE COVER

## **Product description**

 Preformed firestop solution for top-of-wall drywall joints in metal deck construction – helps eliminate the need for time consuming methods such as stuffing & spraying. No mess, zero waste

#### Applications for use

- Firestop, smoke and sound seal for head-of-wall joints between gypsum walls to corrugated metal deck
- CFS-TTS MD is designed as a flexible solution for various track sizes, applications and joints around the beam

## **Advantages**

- Quick and simple installation designed to help increase your productivity and reduce labor costs fewer working steps (one and done)
- Significantly boosts your productivity vs. traditional methods: stuff & spray and castle cut drywall allowing you to meet your critical construction time-lines
- · No spray, no mess, no equipment, no power needed & zero waste
- Hilti foil protected plugs and covers are easy to install and provide a tight smoke and sound seal with no itchy mineral wool exposed to the installer
- Hilti-branded foils allow for easy inspections
- · Preformed firestop solutions make 3rd party destructive testing easier to pass

#### Installation instructions

See Hilti Literature or third-party listings for complete application and installation details

## **Technical Data**

loomiou Dulu			
Color	Silver/Red		
Surface burning characteristics	Flame Spread: Plug = 10 & Cover = 0 Smoke Development: Plug = 40 & Cover = 15 ASTM E 84		
	Flame Spread: Plug = 0 & Cover = 0 Smoke Development: Plug = 10 & Cover = 35 CAN/ULC-S102		
Tested in accordance with	UL 2079 (5th Edition), ASTM E1966 & CAN/ULC-S115	FM	ASSIFIC
Paintable	Yes Vi /	APPROVED	
Mold and mildew performance	Class 1 (ASTM G21-96)		
Acoustics performance	59 (relates to specific construction)		
Shelf Life	Unlimited		
LEEDv4.1 Compliant	CDPH Standard Method v1.2-2017		
LEED VOC	0 g/L		

Description	Flute Dimensions (H)	Qty	Item No.	
CFS-TTS MD P1.5 - Plug	1.5"	360	2226879	
CFS-TTS MD P2 - Plug	2"	250	2226878	
CFS-TTS MD P3 - Plug	3"	100	2226877	
CFS-TTS MD C1.5 - Cover	1.5" - 48" length	36	2226873	
CFS-TTS MD C2 - Cover	2" - 48" length	18	2246240	
CES-TTS MD C3 - Cover		9	2227000	



Hilti Firestop Saving lives through innovation and education



f y 🛅 🖸