

The following excerpt are pages from the <u>North American</u> <u>Product Technical Guide Volume 3: Modular Support Systems</u> Technical Guide, Edition 1.

Please refer to the publication in its entirety for complete details on this product including load values, approvals/listings, general suitability, finishes, quality, etc.

To consult directly with a team member regarding our modular support system products, contact Hilti's team of technical support specialists between the hours of 7:00am – 6:00pm CST.

US: 877-749-6337 or <u>HNATechnicalServices@hilti.com</u> CA: 1-800-363-4458, ext. 6 or <u>CATechnicalServices@hilti.com</u>

> Hilti, Inc. 7250 Dallas Parkway, Suite 1000 Plano, TX 75024

> > 1-800-879 - 8000 www.hilti.com



3.0 MODULAR SUPPORT SYSTEM 3.2.3 MT SYSTEM CONNECTORS MT-C-T 3D/2/HL OC

Description

3D connector for channel-to-channel connections on rooftop applications.

Material Specifications

Standard ¹	Grade ¹	F _y , ksi (MPa)	F _u , ksi (MPa)
EN 10025-2	S235 JR	34.08 (235)	53.66 (370)

1. Mechanical properties of EN 10025-2 Grade S235 JR meet or exceed the mechanical properties of ASTM A1011 SS Grade 33.

Corrosion Protection


Hot-Dipped Galvanized (HDG)

MT-C-T 3D/2/HL OC

Ordering Information

Description	Weight Per Piece Ibs (kg)	Quantity Piece(s)	Item No.
MT-C-T 3D/2/HL OC	0.45 (0.21)	8	2320181

Figure 60 - MT Channel Connection








Table 177 - Allowable Strength Design (ASD) Load Data^{1,2,3}

F _x Ib (kN)	F _y lb (kN)	F _z lb (kN)	M _x ft lb (kN m)	M _y ft lb (kN m)
965	965	1,315	60	115
(4.31)	(4.31)	(5.87)	(0.084)	(0.156)

1. Minimum safety factor, Ω, for tabulated values is 2.0.

 Multiply tabulated values by 1.5 to obtain minimum Load and Resistance Factor Design (LRFD) values.

3. See Figure 60.

Table 178 - Limit State Design (LSD) Load Data^{1,2}

F _x	F _y	F _z	M _x	M _y
Ib (kN)	Ib (kN)	Ib (kN)	ft lb (kN m)	ft lb (kN m)
1,455	1,375	1,985	90	180
(6.48)	(6.12)	(8.83)	(0.126)	(0.250)

1. Maximum resistance factor, $\varphi,$ for tabulated values is 0.75.

2. See Figure 60.