

MIC-C90-DH 2174661

Hilti North America Installation Technical Manual Technical Data MI System

Version 1.2 08.2017





Terms of common cooperation / Legal disclaimer

The product technical data published in these Technical Data Sheets are only valid for the mentioned codes or technical data generation methods and the defined application conditions (e.g. ambient temperature load capacity not valid in case of fire, data not valid in support structures when mixed with third party products, values only apply to static loading conditions). Technical data applies to the component only — suitability and capacity of all other components must be checked separately by the responsible engineer (e.g., other assembly components, attachments, base materials, and building structures).

Suitability of structures combining different products for specific applications needs to be verified by conducting a system design and calculation, using for example Hilti PROFIS software. In addition, it is crucial to fully respect the Instructions for Use and to assure clean, unaltered and undamaged state of all products at any time in order to achieve optimum performance (e.g. avoid misuse, modification, overload, corrosion).

As products but also technical data generation methodologies evolve over time, technical data might change at any time without prior notice. We recommend to use the latest technical data sheets published by Hilti.

In any case the suitability of structures combining different products for specific applications need to be checked and cleared by an expert, particularly with regard to compliance with applicable norms, codes, and project specific requirements, prior to using them for any specific facility. This book only serves as an aid to interpret the capacity of the components listed, without any guarantee as to the absence of errors, the correctness and the relevance of the results or suitability for a specific application. User must take all necessary and reasonable steps to prevent or limit damage. The suitability of structures combining different products for specific applications need to be confirmed with a professional designer and/or structural engineers to ensure compliance with User's specific jurisdiction and project requirements.



Designation Item number MIC-C90-DH 2174661

Corrosion protection:

Hot dipped galvanized per DIN EN ISO 1461:


Connector: 2.2 mils (55 µm) 1.8 mils (45 µm) Bolt: 1.8 mils (45 µm) Nut:

Weight:

18.14lb (8228g) incl. components

Description:

Hilti Hot-dipped galvanized baseplate connector, used for anchoring an MI-90 girder to concrete. Four round anchor holes of baseplate enable anchoring, and girder is connected using bolts through fixed holes.



Material properties Material Connector and Toothed plate: S235JR - DIN EN10025-2 2005.4 One hand screw, prevail torque hex nut $f_y = 92.82 \text{ ksi } (640 \frac{N}{mm^2})$ $f_u = 116.03 \text{ ksi } (800 \frac{N}{mm^2})$ Class 8.8 - DIN EN 1993-1-8

Ultimate strength Yield strength

 $f_y = 34.08 \text{ ksi } (235 \frac{N}{mm^2})$ $f_u = 52.21 \text{ ksi } (360 \frac{N}{mm^2})$


E-modulus **29000** ksi (200000 $\frac{N}{mm^2}$)


Shear modulus 11000 ksi (75845 $\frac{N}{mm^2}$)


29000 ksi (200000 $\frac{N}{mm^2}$)


11000 ksi (75845 $\frac{N}{mm^2}$)

Instruction For Use:











Approved loading cases			
Standard			

Governing Conditions

Methodology:

Connection strength values are determined with a combination of simulation (ANSYS®), calculation (Microsoft Excel and Mathcad) and testing.

Standards and codes:

ANSI/AISC 360-10 Specification for Structural Steel Buildings

ANSI/AISC 360-10 – Appendix 1 Inelastic analysis
 AISC Steel Design Guide Series 1 Column Base Plates

• AISI S100-2007/2010 North American Specification for the Design

of cold formed Steel Structural Members

ACI 318-08/11 Building Code Requirement for Structural Concrete
 EN 1993-1-1 Eurocode 3: Design of steel structures – Part 1-1:

General rules and rules for buildings 03.2012

Eurocode 3: Design of steel structures – Part 1-8:

Design of joints 03.2012


EN 10025-2
 Hot rolled products of structural steels- Part 2:

technical delivery conditions for non-alloy structural steels 02.2005


Validity:

Temperature limits: -22°F (-30°C) to 200°F (+93°C).

Published allowable loads for applications are based on static loading conditions. Non-static forces, including those resulting from thermal or other expansion must be taken into account during design.







Loading case: Standard Bill of Material for this loading case:		Combinations covered by loading case	
		Baseplate connector used for a perpendicular connection of	
1x MIC-C90-DH	2174661	an MI-90 girder to concrete	

Usage of Values for Design Strength and Allowable Strength


The Design Strength and Allowable Strength tables on the following pages include strength reduction factors:


- 1. ASD: Safety Factor (omega) > 1.0 as per AISC specifications.
- 2. <u>LRFD:</u> Strength Reduction Factor (phi) < 1.0 as per AISC specifications. $\Omega = \frac{1.5}{\phi}$ (Reference AISC 360 C-B3-5)

Factored loads are required for input to the given interaction equations. Factored loads are the responsibility of the user. Factored loads are noted as P, V and M

Limiting components of capacity evaluated in following tables:

 Connection system, including connector, hardware and affected portion of MI-90 girder, per FEA simulation







Anchor strength must be calculated separately using PROFIS ANCHOR.




Standard	

Values for Design Strength and Allowable Strength

1/2

NOTE: Calculate interaction separately for each group only using values from that group. Limiter is defined by highest interaction. Use absolute values. Values refer to the coordinate system shown.

1. Connection system, including connector, hardware and affected portion of MI-90 girders, per FEA simulation



LRFD*	+Fx [kip]	-Fx [kip]	+Fy [kip]	-Fy [kip]	+Fz [kip]	-Fz [kip]
	21.35	25.62	9.00	9.00	9.00	9.00
	+Mx [kip*ft]	-Mx [kip*ft]	+My [kip*ft]	-My [kip*ft]	+Mz [kip*ft]	-Mz [kip*ft]
	2.58	2.58	2.07	2.07	2.07	2.07
ASD*	+Fx	-Fx	+Fy	-Fy	+Fz	-Fz
	[kip]	[kip]	[kip]	[kip]	[kip]	[kip]
	14.23	17.08	6.00	6.00	6.00	6.00
	+Mx [kip*ft]	-Mx [kip*ft]	+My [kip*ft]	-My [kip*ft]	+Mz [kip*ft]	-Mz [kip*ft]
	1.72	1.72	1.38	1.38	1.38	1.38

Interaction for LRFD

$$\frac{P_{ux}}{F_x} + \frac{V_{uv}}{F_y} + \frac{V_{uz}}{F_z} + \frac{M_{ux}}{M_x} + \frac{M_{uv}}{M_y} + \frac{M_{uz}}{M_z} \leq 1$$
 Interaction for ASD:

$$\frac{P_{ax}}{F_x} + \frac{V_{av}}{F_y} + \frac{V_{az}}{F_z} + \frac{M_{ax}}{M_x} + \frac{M_{av}}{M_y} + \frac{M_{az}}{M_z} \le 1$$

*Values already include LRFD strength reduction (Φ) or ASD safety (Ω) factors in accordance with AISC, and are based on nominal geometry.




Standard	

Values for Design Strength and Allowable Strength

NOTE: Calculate interaction separately for each group only using values from that group. Limiter is defined by highest interaction. Use absolute values. Values refer to the coordinate system shown.

2. Welds - per analytical calculation



LRFD*	+Fx [kip]	-Fx [kip]	+Fy [kip]	-Fy [kip]	+Fz [kip]	-Fz [kip]
	49.72	49.72	10.81	10.81	10.81	10.81
	+Mx [kip*ft]	-Mx [kip*ft]	+My [kip*ft]	-My [kip*ft]	+Mz [kip*ft]	-Mz [kip*ft]
	4.61	4.61	2.45	2.45	2.45	2.45
	+Fx	-Fx	+Fy	-Fy	+Fz	-Fz
ASD*	[kip]	[kip]	[kip]	[kip]	[kip]	[kip]
	33.14	33.14	7.21	7.21	7.21	7.21
	+Mx	-Mx	+My	-My	+Mz	-Mz
	[kip*ft]	[kip*ft]	[kip*ft]	[kip*ft]	[kip*ft]	[kip*ft]

Interaction for LRFD

3.08

$$\frac{P_{ux}}{F_x} + \frac{V_{uy}}{F_y} + \frac{V_{uz}}{F_z} + \frac{M_{ux}}{M_x} + \frac{M_{uy}}{M_y} + \frac{M_{uz}}{M_z} \leq 1$$
 Interaction for ASD:

3.08 1.63

$$\frac{P_{ax}}{F_x} + \frac{V_{ay}}{F_y} + \frac{V_{az}}{F_z} + \frac{M_{ax}}{M_x} + \frac{M_{ay}}{M_y} + \frac{M_{az}}{M_z} \le 1$$

*Values already include LRFD strength reduction (Φ) or ASD safety (Ω) factors in accordance with AISC, and are based on nominal geometry.



In the US:

Hilti, Inc. (U.S.)

P.O. Box 21148 Tulsa, OK 74121 Customer Service: 1-800-879-8000 en español: 1-800-879-5000

Fax: 1-800-879-7000

www.us.hilti.com

Hilti is an equal opportunity employer Hilti is a registered trademark of Hilti, Corp. ©Copyright 2017 by Hilti, Inc. (U.S.)

In Canada:

Hilti (Canada) Corporation 2360 Meadowpine Blvd. Mississauga, Ontario, L5N 6S2 Customer Service: 1-800-363-4458

Fax: 1-800-363-4459

www.hilti.ca

The data contained in this literature was current as of the date of publication. Updates and changes may be made based on later testing. If verification is needed that the data is still current, please contact the Hilti Technical Support Specialists at 1-800-879-8000 (U.S.) or 1-800-363-4458 (Canada). All published load values contained in this literature represent the result of testing by Hilti or test organizations. Local base materials were used. Because of variations in materials, on-site testing is necessary to determinate performance at any specific site.