

Hilti Firestop Systems

eproduced by HIL II, Inc. Courtesy o Underwriters Laboratories, Inc. July 22, 2022

## System No. F-C-2389

2. Chase Wall — The through penetrant (Item No. 3) shall be routed through a single, double or staggered wood studs/gypsum board chase wall and shall include the following construction features:

- A. Studs Nom 2 by 4 in. (51 by 102 mm) or nom 2 by 6 in. (51 by 152 mm) lumber studs.
- B. Sole Plate Nom 2 by 4 in. (51 by 102 mm) or 2 by 6 in. (51 by 152 mm) lumber plates. Max diam of opening is 4 in. (102 mm) when nom 3 in. (76 mm) diam penetrants are used. Max diam of opening is 3 in. (76 mm) when nom 2 in. (51 mm) or smaller diam penetrants are used.
- C. Top Plate The double top plate shall consist of two nom 2 by 4 in. (51 by 102 mm) or 2 by 6 in. (51 by 152 mm) lumber plates. Max diam of opening is 4 in. (102 mm) when nom 3 in. (76 mm) diam penetrants are used. Max diam of opening is 3 in. (76 mm) when nom 2 in. diam penetrants are used.
- C. Gypsum Board Min 1/2 in. (13 mm) thick, classified or unclassified, gypsum board.
- E. Steel Straps (Not shown) Steel straps to be used when top and sole plates are discontinuous and shall meet the structural requirements of the wall. Min 1-1/2 in. (38 mm) wide by 20 gauge (or heavier) galvanized steel straps used to bridge opening on both sides of wall at sole plate when sole plate is discontinuous at opening in plywood floor. Steel straps to be cut to overlap a min of 2 in. (51 mm) onto sole plate on each side of opening and secured to sole plate with a min of two nails or screws on each side of opening on both sides of wall. Min 3 in. (76 mm) wide by 20 gauge (or heavier) galvanized steel straps used to bridge opening on both sides of wall. Min 3 in. (76 mm) wide by 20 gauge (or heavier) galvanized steel straps used to bridge opening on both sides of opening and secured to plate is discontinuous at opening. Steel straps to be cut to overlap a min of 2 in. (51 mm) onto top plate on each side of opening and secured to top plates with a min of two nails or screws on each side of opening and secured to top plates with a min of two nails or screws on each side of opening and secured to top plates with a min of two nails or screws on each side of opening and secured to top plates with a min of two nails or screws on each side of opening on both sides of wall.
- 3. Through Penetrants One nonmetallic pipe to be installed either eccentrically or concentrically within the firestop system. The annular space between the through penetrant and the periphery of the opening shall be a min 0 in. (point contact) to a max of 5/8 in.(16 mm) Pipe to be rigidly supported on both sides of the floor-ceiling assembly. The following types and sizes of nonmetallic pipes may be used.
  - A. Polyvinyl Chloride (PVC) Pipe Nom 3 in. (76 mm) diam (or smaller) Schedule 40 solid or cellular core PVC for use in closed (process or supply) or vented (drain, waste or vent) piping systems.
  - B. Chlorinated Polyvinyl Chloride (CPVC) Pipe Nom 3 in. (76 mm) diam (or smaller) SDR13.5 CPVC for use in closed (process or supply) piping systems.
  - C. Acrylonitrile Butadiene Styrene (ABS) Pipe Nom 3 in. (76 mm) diam (or smaller) Schedule 40 solid-core or cellular-core ABS pipe for use in closed (process or supply) or vented (drain, waste or vent) piping system.
  - D. Electrical Nonmetallic Tubing (ENT+) Nom 2 in. (51 mm) diam (or smaller) corrugated-wall electrical nonmetallic tubing (ENT) constructed of polyvinyl chloride (PVC) and installed in accordance with the National Electrical Code (NFPA No. 70).
  - See Electrical Nonmetallic Tubing (FKHU) category in the Electrical Construction Materials Directory for names of manufacturers.
- 4. Fill, Void or Cavity Material\* Sealant Min 3/4 in. (19 mm) thickness of fill material applied within the annulus, flush with top surface of floor or sole plate. Min 3/4 in. (19 mm) thickness of fill material applied within the annulus, flush with bottom surface of lower top plate. At point contact location out to 1/8 in. (3.2 mm) annular space,, a min 1/2 in. (13 mm) diam bead of fill material shall be applied at bottom surface of lower top plate. In addition, at top of floor, a min 1/2 in. (13 mm) diam bead of fill material shall be applied at the point contact location out to 1/8 in. (3.2 mm) annular space at top of sole plate or subfloor.

HILTI CONSTRUCTION CHEMICALS, DIV OF HILTI INC - FS-ONE-MAX Intumescent Sealant

\* Indicates such products shall bear the UL or cUL Certification Mark for jurisdictions employing the UL or cUL Certification (such as Canada), respectively.



Reproduced by HILTI, Inc. Courtesy of Underwriters Laboratories, Inc. July 22, 2022

Page: 2 of 2