

## 5.0 Installation System Hangers

### 5.3 Split rings

#### Split rings — electro galvanized

##### Product Features

- For suspending uninsulated stationary pipe. Allows for piping runs close to ceilings or walls

##### Material Specifications


<b>Material</b>	Malleable iron body, carbon steel rivet and bolt
<b>Finish</b>	Electro-galvanized
<b>Conforms with</b>	<ul style="list-style-type: none"> <li>• Federal specification WW-H-171 (Type 25)</li> <li>• Manufacturers Standardization Society MSS-SP-58 (Type 12)</li> </ul>
<b>Installation</b>	Install in accordance with ANSI/MSS-SP-58



##### Ordering Information / Technical Data

Description	Weight/ Piece (lb)	Pipe Size	Rod Size (RS)	Center Line (CL)	Min. Rod Insertion (MR)	Qty	Item No.	Maximum Allowable Load (lb) <sup>1</sup>
SR-EG 1/2"	0.18	1/2"	3/8"	16/16"	3/8"	100	306630	180
SR-EG 3/4"	0.22	3/4"	3/8"	1-5/16"	3/8"	100	306631	180
SR-EG 1"	0.23	1"	3/8"	1-1/16"	3/8"	100	306632	180
SR-EG 1-1/2"	0.34	1-1/2"	3/8"	1-3/16"	3/8"	50	306633	180
SR-EG 2"	0.37	2"	3/8"	1-7/16"	3/8"	50	306634	180

<sup>1</sup> Based on a safety factor of 3.5



#### Split Rings — Copper

##### Product Features

- For suspending uninsulated stationary copper tubing. Allows for piping runs close to ceilings or walls

##### Material Specifications

<b>Material</b>	Malleable iron body, carbon steel rivet and bolt with copper electroplate finish
<b>Finish</b>	Copper
<b>Conforms with</b>	<ul style="list-style-type: none"> <li>• Federal specification WW-H-171 (Type 25)</li> <li>• Manufacturers Standardization Society MSS-SP-58 (Type 12)</li> </ul>
<b>Installation</b>	Install in accordance with ANSI/MSS-SP-58

Note: This pipe support is not designed for corrosion or electrolysis resistance. Copper plating is for identification purposes only



##### Ordering Information / Technical Data

Description	Weight/ Piece (lb)	Pipe Size	Rod Size (RS)	Center Line (CL)	Min. Rod Insertion (MR)	Qty	Item No.	Maximum Allowable Load (lb) <sup>1</sup>
Copper SR 1/2"	0.18	1/2"	3/8"	11/16"	3/8"	100	306623	180
Copper SR 3/4"	0.22	3/4"	3/8"	13/16"	3/8"	100	306624	180
Copper SR 1"	0.23	1"	3/8"	15/16"	3/8"	100	306625	180
Copper SR 1-1/4"	0.25	1-1/4"	3/8"	1-1/16"	3/8"	100	306626	180
Copper SR 1-1/2"	0.34	1-1/2"	3/8"	1-3/16"	3/8"	100	306627	180
Copper SR 2"	0.37	2"	3/8"	1-7/16"	3/8"	50	306628	180

<sup>1</sup> Based on a safety factor of 3.5

