

HILTI TECHNICAL BULLETIN

April 12, 2022

Subject: Design parameters for Hilti HIT-HY 200 V3 for concrete strengths up to 10,000 psi (70 MPa)

ACI 318 Chapter 17 and CSA A23.3 Annex D limit the design of post-installed anchors to concrete strengths to a maximum of 8,000 psi and 55 MPa, respectively. ESR-4868 and ELC-4868 provide data with the same concrete strength limitations for design in accordance with ACI 318 and CSA A23.3.

Hilti has performed tests of HIT-HY 200 V3 in external test laboratories in concrete strengths up to 10,000 psi (70 MPa). Tests have shown no decrease in bond strength in concretes between 8,000 psi (55 MPa) and 10,000 psi (90 MPa) concrete. Tests have also shown the concrete strength up to 10,000 psi (70 MPa) can be used for concrete breakout failure modes, similar to cast-in anchors. This document expands the relevant design parameters in ACI 318 and CSA A23.3 for Hilti HIT-HY 200 V3 up to concrete strengths of 10,000 psi (70 MPa).

Tensile loading parameters for f_c' between 8,000 psi and 10,000 psi (between 55 MPa and 70 MPa for CSA A23.3 design)

Parameter	ACI 318-19	CSA A23.3-19	Recommendation
Steel capacity	§17.4.1	§D.6.1	Independent of concrete strength
Concrete breakout capacity	§17.4.2	§D.6.2	k_c factors in ESR-4868 and ELC-4868 valid using f_c' up to 10,000 psi (70 MPa) for calculation.
Bond capacity	§17.4.5	§D.6.5	Increase factors in ESR-4868 and ELC-4868 limited to 8,500 psi (ACI 318 design) and 55 MPa (CSA A23.3 design) concrete.
ϕ (ACI and CSA) R (CSA only)	§17.3.3	§D.5.3	Factors in ESR-4868 and ELC-4868 valid.

Shear loading parameters for f_c' between 8,000 psi and 10,000 psi (between 55 MPa and 70 MPa for CSA A23.3 design)

Parameter	ACI 318-19	CSA A23.3-19	Recommendation
Steel capacity	§17.5.1	§D.7.1	Independent of concrete strength
Concrete breakout capacity	§17.5.2	§D.7.2	Calculations valid using f'_c up to 10,000 psi (70 MPa).
Concrete pryout capacity	§17.5.3	§D.7.3	k_c factors in ESR-4868 and ELC-4868 valid using f_c' up to 10,000 psi (70 MPa) for calculation.
ϕ (ACI and CSA) R (CSA only)	§17.3.3	§D.5.3	Factors in ESR-4868 and ELC-4868 valid.

Treatment of other parameters for f_c' between 8,000 psi and 10,000 psi (between 55 MPa and 70 MPa for CSA A23.3 design)

Parameter	ACI 318-19	CSA A23.3-19	Recommendation		
Minimum edge distances, spacings, and concrete thicknesses	§17.7	§D.9	Equivalent to published values in ESR-4868 and ELC-4868.		
Installation	n/a	n/a	Same as ESR-4868 and ELC-4868, but the only installation conditions permitted are in dry and water-saturated concrete.		

Please feel free to contact our Engineering Technical Services department for more information or any questions.

Hilti Engineering Technical Services – United States (877) 749-6337 toll free hnatechnicalservices@hilti.com

Hilti Engineering Technical Services – Canada (800) 363-4458 toll free CATechnicalServices@hilti.com