

# CFS-CID P 8" AND 10" CFS-CID M 8" AND 10"

## Product description

- Firestop cast-in device for 8" and 10" metallic pipes, and plastic or insulated metal
- Five heights available (6", 8", 10", 12" and 14")

## Product features

- Increased productivity and reduced labor costs
- Simple and quick installation
- No need for large firestop collars requiring two pairs of hands to install
- Meets OSHA part 1926 lid requirements
- Single manufacturer covering most vertical pipe applications

## Advantages


- One-step firestop solution for 8" and 10" plastic pipes and 4", 6" and 8" metal pipes with insulation
- One-step firestop solution for 8" and 10" metal pipes
- Increased productivity helps reduce cost
- Quick and simple installation
- Reduces the chance of project delays due to failed inspections
- UL and FM approved firestop device
- Available in five different heights

## Applications

- For use with new building construction (flat concrete)
- For use with PVC pipe (CFS-CID P 8" and CFS-CID P 10")
- For use with metal pipes with insulation (CFS-CID P 8" and CFS-CID P 10")
- For use with metal pipes (CFS-CID M 8" and 10")
- Available in 6", 8", 10", 12", 14" heights


## Installation instructions

- See Hilti literature or third-party listings for complete application and installation details



## Technical Data

<b>Base Material</b>	Concrete
<b>Approvals</b>	UL and FM
<b>Tested in accordance with</b>	ASTM E814, UL 1479 and CAN/ULC-S115
<b>Application temperature range</b>	-40 °F to 120 °F
<b>Intumescent</b>	Yes
<b>Mold and Mildew resistance</b>	Yes
<b>Mold and Mildew performance</b>	Class 0 (ASTM G21-96)
<b>Reusable (and removable)</b>	Not possible
<b>Smoke and gas resistant</b>	Yes
<b>W-rating</b>	Yes (additional steps required)



Product	Footprint	Max pipe OD
CFS-CID P 8"	14.6"	8.625"
CFS-CID P 10"	18.7"	10.750"
CFS-CID M 8"	11.6"	8.625"
CFS-CID M 10"	14.0"	10.750"



**Hilti Firestop**  
Saving lives  
through innovation  
and education