



Reproduced by HILTI, Inc. Courtesy of Underwriters Laboratories, Inc. April 29, 2020

System No. W-L-3441

4
34
_
≥

- 2. Metallic Sleeve Nom 1 in. (25 mm) diam (or smaller) rigid steel conduit installed flush with wall surfaces. The annular space between steel sleeve and periphery of opening shall be min 0 in. (point contact) to max 1/8 in. (3 mm). When opening dimension exceeds 1 in. (25 mm), max annular space is 3/8 in. (10 mm). The sleeve shall extend up to 12 in. (305 mm) beyond one or both wall surfaces. As an option, sleeve may extend continuously beyond one wall surface. The conduit sleeve shall be secured to the adjacent stud within the wall cavity with a steel conduit strap attached to web of stud with min two no. 8 sheet metal screws with washers or shall be rigidly supported on those sides of the wall where the sleeve is extended. As an option, the sleeve may be provided with a plastic grommet at the ends of the sleeve.
- 3. Cables Within the sleeve (Item 2), the cables may represent a 0 to 100 percent visual fill. Cables to be tightly bundled within the sleeve and rigidly supported on both sides of wall assembly. Any combination of the following types of cables may be used:
 - A. Max 3/C No. 8 AWG NM copper conductor cable (Romex) with PVC insulation and jacket.
 - B. Type RG 6/U coaxial cable with fluorinated ethylene or PVC insulation and jacketing.
 - C. Max 24 fiber optic cable with polyvinyl chloride (PVC) or polyethylene (PE) jacket and insulation.
 - D. Max 4 pr No. 22 AWG (or smaller) Cat 5 or Cat 6 computer cables with PVC or plenum rated insulation and jacketing.
 - E. Maximum 3/C No. 10 AWG copper conductor metal-clad cable.
 - F. Through Penetrating Product* Max two copper conductor No. 18 AWG (or smaller) Power or Non-Power Limited Fire Alarm Cable with or without a jacket under a metal armor.
 - AFC CABLE SYSTEMS INC
 - G. Max 7/C-No. 12 AWG copper conductor control cable with PVC or XLPE insulation and jacket.
 - H. Max 100 pair No. 24 AWG (or smaller) copper conductor telecommunication cable with PVC or plenum rated insulation and jacketing.
- 4. Fill, Void or Cavity Material* Nom 60 mm diam by 3 mm thick putty disc with one seam at radius. Paper-backer of disc to be removed and disc firmly pressed around the sleeve at each surface of wall to lap min 5 mm onto sleeve and firmly pressed to lap onto the wall around periphery of opening. Disc seams to be firmly pressed and sealed tight, Discs to be installed at both sides of wall opening. HILTI CONSTRUCTION CHEMICALS, DIV OF HILTI INC CFS-D 1" Firestop Cable Disc
- 5. Fill, Void or Cavity Material* Nom 60 mm diam by 3 mm thick putty disc with one seam at radius. Paper-backer of disc to be removed and disc firmly pressed around the cable/cable bundle at exit from each end of sleeve, lapping min 5 mm onto cables to completely cover opening and firmly pressed to lap onto the sleeve periphery. Disc seam to be firmly pressed and sealed tight, Discs to be installed at both sides of wall opening.

HILTI CONSTRUCTION CHEMICALS, DIV OF HILTI INC - CFS-D 1" Firestop Putty Disc

6. Fill, Void or Cavity Material*— Sealant — As an alternate to Item 4, a min 1/2 in. (13 mm) diam bead of fill material shall be applied at the sleeve/wall interface. Fill material installed symmetrically on both sides of the wall.

HILTI CONSTRUCTION CHEMICALS, DIV OF HILTI INC - CP 606 or FS-ONE MAX Intumescent Sealant

* Indicates such products shall bear the UL or cUL Certification Mark for jurisdictions employing the UL or cUL Certification (such as Canada), respectively.



Reproduced by HILTI, Inc. Courtesy of Underwriters Laboratories, Inc. April 29, 2020