FINISH BIG WITH OUR EXPANDED GRINDER OFFERING

Cordless angle grinder AG 4S-A22-5

Delivering exceptional precision for cutting, grinding, smoothing, and finishing, the angle grinder AG 4S-A22 is now available with a 5" disc option for your metal working jobs, making it the perfect addition to your tool crib.



Ultimate gearing, variable speed dial, and a brushless motor make this grinder ideal for use on a variety of materials such as stainless steel, aluminum, brass, copper, titanium, concrete, and other mineral surfaces. With its comfortable grip, Active Torque Control, and blade brake, you can count on the AG 4S-A22 to get the job done safer and more efficiently.

Technical data		
Disc diameter	5"	
No load speed	8500 RPM	
Battery platform	22V	
Arbor	5/8"	
Rated voltage		

Order information		
Description	Item number	
AG 4S-A22 (5") w/ Kwik Lock	3660956	

Accessories		
Description	Item number	
Kwik lock	2149275	
5" grinding hood	2126539	
5" Tuck Point/Cutting Kit	3564395	
Protective grinding cover	341429	



APPLICATIONS AND ADVANTAGES

Applications

- · Cutting and grinding ferrous and non-ferrous metals
- Cutting and grinding mineral such as concrete, block, and brick
- Finishing metals
- Metal surface preparation

Advantages

- Brushless motor
- Slim design
- Variable speed dial (3500-8500 RPM)
- Active Torque Control
- Blade brake





