
## **UL SYSTEM NO. F-A-2315**

## PLASTIC PIPE THROUGH CONCRETE FLOOR OVER METAL DECKING ASSEMBLY F-RATING = 2-HR.



- 1. LIGHTWEIGHT OR NORMAL WEIGHT CONCRETE FLOOR ASSEMBLY (MINIMUM 4-1/2" THICK) OVER METAL DECKING (UL CLASSIFIED D900 SERIES) WITH 2" OR 3" FLUTED DECKS (2-HR. FIRE-RATING).
- 2. HILTI CFS-CID MD PLT [W2" OR W3"] METAL DECK PLATFORM SECURED TO DECK WITH ONE FASTENER IN EACH CORNER (SEE NOTE BELOW).
- 3. HILTI CFS-CID MD [P OR PX] [2", 3", OR 4"]/[2.5"/4"] FIRESTOP CAST-IN DEVICE FOR METAL DECK SECURED TO HILTI CFS-CID MD PLT METAL DECK PLATFORM WITH SCREWS.
- 4. NONMETALLIC PIPE OR CONDUIT BUNDLE TO CONSIST OF ANY OF THE FOLLOWING (MAX. QTY. = 3):
  - A. MAXIMUM 2" NOMINAL DIAMETER PVC PLASTIC PIPE (SCHEDULE 40) (CELLULAR AND SOLID CORE) (CLOSED OR VENTED PIPING SYSTEM).
  - B. MAXIMUM 2" NOMINAL DIAMETER CPVC PLASTIC PIPE (SDR 13.5) (CLOSED PIPING SYSTEM ONLY).
  - C. MAXIMUM 1" NOMINAL DIAMETER ELECTRICAL NONMETALLIC TUBING (ENT).
- 5. MINIMUM 4" THICKNESS MINERAL WOOL (MIN. 4 PCF DENSITY) TIGHTLY PACKED INTO DEVICE, COMPLETELY FILLING ANNULAR SPACE AROUND NONMETALLIC PIPES OR CONDUITS.

NOTES: FOR HILTI CFS-CID MD P ONLY, AS AN ALTERNATIVE TO CFS-CID MD PLT METAL DECK PLATFORM (ITEM 2), THE HILTI METAL DECK ADAPTOR KIT MAY BE USED.



HILTI, Inc. Plano, Texas USA (800) 879-8000

Sheet	1 of 1
Scale	7/64" = 1"
Date	Sept. 18, 2025

FA 2315d

Saving Lives through Innovation and Education