

SPEED SLEEVE CP 653

Product description

- Cable pass-through device used to provide fire protection for cables and cable bundles through rated wall and floor assemblies

Product features

- Quicker and easier to install and inspect
- Can be opened and closed for new and existing cable installations
- Unique smoke fabric provides industry’s leading air flow control
- Low air leakage (L) ratings
- Robust construction designed to withstand the life of the project without any maintenance
- Can be installed in wall and floor applications
- May be ganged together for optimal flexibility, efficiency and productivity

Areas of application

- Cable and cable bundles through fire-rated assemblies

For use with

- Concrete floor rated up to 3 hours
- Gypsum walls rated up to 4 hours

Examples

- Mid-voltage electrical wiring
- Low voltage and datacom wiring
- Security and fire alarm wiring

Installation instructions

- See Hilti literature or third-party listings for complete application and installation details



Technical Data

	2" (50 mm)	4" (102 mm)
Item number	2365150	2365151
BA Item number*	2097882	2097883
OD (device only)	2.3" (60 mm)	4.3" (110 mm)
OD (flange)	4.7" (120 mm)	6.7" (170 mm)
ID	1.7" (48 mm)	3.6" (92 mm)
Total length	12.4" (315 mm)	12.4" (315 mm)
Weight (device and flanges)	1.5 lbs	2.6 lbs
Temperature resistance	-22° F to 212° F (-6° C to 100° C)	
Intumescent activation	Approx. 320° F (160° C)	
Expansion ratio (unrestricted)	1:40	
VOC Content	7.6 g/L	
Metal	Steel with zinc coating	
Plastic	ABS	
Fabric	Glass-fiber	
Tested in accordance with	UL 1479 ASTM E 814 CAN/ULC-S115	

*Compliant with Buy American act of 2021

