

**System No. F-A-5015**  
F Rating — 2 Hr  
T Ratings — 1/2 and 3/4 Hr (See Item 3)

1. Floor Assembly — Min 2-1/2 in. (64 mm) thick reinforced lightweight or normal weight (100-150 pcf or 1600-2400 kg/m<sup>3</sup>) concrete.  
1A. Floor Assembly - (Optional - Not Shown) — The fire rated unprotected concrete and steel floor assembly shall be constructed of the materials and in the manner specified in the individual D900 Series Designs in the Fire Resistance Directory and as summarized below:  
A. Steel Floor and Form Units\* — Composite or non-composite max 3 in. (76 mm) deep galv steel fluted units as specified in the individual Floor-Ceiling Design.  
B. Concrete — Min 2-1/2 in. (64 mm) thick reinforced lightweight or normal weight (100-150 pcf or 1600-2400 kg/m<sup>3</sup>) concrete.  
2. Firestop Device\* — Cast in place firestop device permanently embedded during concrete placement or grouted in concrete floor assembly in accordance with accompanying installation instructions with a max 2 in. (51 mm) projection above the top surface of the concrete.  
HILTI CONSTRUCTION CHEMICALS, DIV OF HILTI INC. — CP 680-75/2.5"N, CP 680-110/4"N, CP 680-160/6"N, CP 682-75/2.5", CP 682-110/4", CP 680-M 2", CP 680-M 3", CP 680-M 4", CP 680-P 2", CP 680-P 3", CP 680-P 4", CP 680-P 6"  
3. Through Penetrants — One metallic pipe, conduit or tubing to be installed within the firestop device. Pipe, conduit or tubing to be rigidly supported on both sides of floor assembly. The following types of pipe, conduit or tubing may be used:  
A. Steel Pipe — Nom 4 in. (102 mm) diam (or smaller) Schedule 10 (or heavier) steel pipe.  
B. Copper Tubing — Nom 4 in. (102 mm) diam (or smaller) Type L (or heavier) copper tubing.  
C. Copper Pipe — Nom 4 in. (102 mm) diam (or smaller) Regular (or heavier) copper pipe.  
The firestop device and metallic penetrant shall be sized as follows:

Nom Pipe Diam. in. (mm)	Nom Thick. Of Pipe Insul. in. (mm)	Firestop Device	T-Rating, Hr
1/2 (13)	1 (25)	CP 680-75/2.5"N, CP 682-75/2.5", CP 680-M 2", CP 680-P 2"	3/4
1 (25)	3/4 (19)	CP 680-75/2.5"N CP 680-P 3"	1/2
1 (25)	1 (25)	CP 680-M 3", CP 680-P 3"	1/2
1 (25) (see Item 5)	1 (25)	CP 682-110/4" CP 680-M 4"	1/2
2 (51)	1 (25)	CP 680-110/4"N, CP 682-110/4" CP 680-M 4", CP 680-P 4"	1/2
2 (51)	3/4 (19)	CP 680-100/4"NCP 680-P 4"	1/2
4 (102)	3/4 (19)	CP 680-160/6"NCP 680-P 6"	1/2

4. Tube Insulation - Plastics\* — Nom 1/4 in. (19 or 25 mm) thick acrylonitrile butadiene/polyvinyl chloride (AB/PVC) flexible foam furnished in the form of tubing.  
See Plastics\* (DMFZ2) Category in the Plastics Recognized Component Directory for names of manufacturers. Any Recognized Component tube insulation material meeting the above specifications and having a UL94 Flammability Classification of 94-V0 may be used.  
5. Packing Material — (Not Shown) — When using a 1 in. (25 mm) diam pipe with 1 in. (25 mm) thick AB/PVC pipe insulation in a 4 in. (102 mm) device, and a min 2 in. (51 mm) thickness of min 4 pcf (64 kg/m<sup>3</sup>) mineral wool batt insulation shall be firmly packed into top of devices, flush with the top of the device.  
\*Bearing the UL Classification Mark

Reproduced by HILTI, Inc. Courtesy of Underwriters Laboratories, Inc. December 14, 2006  
**Hilti Firestop Systems**

**System No. F-A-5016**  
F Rating — 3 Hr  
T Ratings — 0, 3/4, 1, 3 Hr (See Item 3)

1. Floor Assembly — Min 4-1/2 in. (114 mm) thick reinforced lightweight or normal weight (100-150 pcf or 1600-2400 kg/m<sup>3</sup>) concrete.  
1A. Floor Assembly - (Optional - Not Shown) — The fire rated unprotected concrete and steel floor assembly shall be constructed of the materials and in the manner specified in the individual D900 Series Designs in the UL Fire Resistance Directory and as summarized below:  
A. Concrete — Min 4-1/2 in. (114 mm) thick reinforced lightweight or normal weight (100-150 pcf or 1600-2400 kg/m<sup>3</sup>) concrete.  
B. Steel Floor and Form Units\* — Composite or non-composite max 3 in. (76 mm) deep galv steel fluted units as specified in the individual Floor-Ceiling Design.  
2. Firestop Device\* — Cast in place firestop device permanently embedded during concrete placement or grouted in concrete floor assembly in accordance with accompanying installation instructions with a max 2 in. (51 mm) projection above the top surface of the concrete.  
HILTI CONSTRUCTION CHEMICALS, DIV OF HILTI INC. — CP 680-110/4"N, CP 680-160/6"N, CP 682-75/2.5", CP 682-110/4", CP 680-M 3", CP 680-M 4", CP 680-P 2", CP 680-P 3", CP 680-P 4", CP 680-P 6"  
3. Through Penetrants — One metallic pipe or tubing to be installed within the firestop device. Pipe or tubing to be rigidly supported on both sides of floor assembly. The following types of pipe or tubing may be used:  
A. Steel Pipe — Nom 4 in. (102 mm) diam (or smaller) Schedule 10 (or heavier) steel pipe.  
B. Copper Tubing — Nom 4 in. (102 mm) diam (or smaller) Type L (or heavier) copper tubing.  
C. Copper Pipe — Nom 4 in. (102 mm) diam (or smaller) Regular (or heavier) copper pipe.  
The firestop device and metallic penetrant shall be sized as follows:

Nom Pipe Diameter*	Nom Pipe Cover-in. (mm)	Firestop	T Rating-Hr
1/2 in. (13 mm)	1 (25)	CP 680-75/2.5"N, CP 682-75/2.5", CP 680-M 2", CP 680-P 2"	3
1 in. (25 mm)	1 (25)	CP 680-110/4"N, CP 682-110/4", CP 680-M 3", CP 680-P 3", CP 680-M 4", CP 680-P 4"	3/4
2 in. (51 mm)	3/4 (19)	CP 680-110/4"N	1
4 in. (102 mm)	3/4 (19)	CP 680-160/6"N	3/4
		CP 680-P 6"	3/4

\* When pipe diameter smaller than shown in above table is used, the insulated pipe shall be installed in conjunction with Item 5 and the T Ratings are 0 hr.  
4. Tube Insulation - Plastics\* — Nom 3/4 in. (19 or 25 mm) thick acrylonitrile butadiene/polyvinyl chloride (AB/PVC) flexible foam furnished in the form of tubing.  
See Plastics\* (DMFZ2) Category in the Plastics Recognized Component Directory for names of manufacturers. Any Recognized Component tube insulation material meeting the above specifications and having a UL94 Flammability Classification of 94-V0 may be used.  
5. Packing Material — (Not Shown) — When pipe sizes are less than those shown in the table in Item 3, min 4 in. (102 mm) thickness of min 4 pcf (64 kg/m<sup>3</sup>) mineral wool insulation shall be firmly packed to the fullest extent possible within the device flush with top surface of device.  
\*Bearing the UL Classification Mark

Reproduced by HILTI, Inc. Courtesy of Underwriters Laboratories, Inc. December 14, 2006  
**Hilti Firestop Systems**

**System No. F-A-5017**  
F Rating — 2 Hr  
T Ratings — 3/4 and 1 Hr (See Item 3)

1. Floor Assembly — Min 2-1/2 in. (38 mm) thick reinforced lightweight or normal weight (100-150 pcf or 1600-2400 kg/m<sup>3</sup>) concrete.  
1A. Floor Assembly - (Optional - Not Shown) — The fire rated unprotected concrete and steel floor assembly shall be constructed of the materials and in the manner specified in the individual D900 Series Designs in the Fire Resistance Directory and as summarized below:  
A. Concrete — Min 2-1/2 in. (38 mm) thick reinforced lightweight or normal weight (100-150 pcf or 1600-2400 kg/m<sup>3</sup>) concrete.  
B. Steel Floor and Form Units\* — Composite or non-composite max 3 in. (76 mm) deep galv steel fluted units as specified in the individual Floor-Ceiling Design.  
2. Firestop Device\* — Cast in place firestop device permanently embedded during concrete placement or grouted in concrete floor assembly in accordance with accompanying installation instructions with a max 2 in. (51 mm) projection above the top surface of the concrete.  
HILTI CONSTRUCTION CHEMICALS, DIV OF HILTI INC. — CP 680-75/2.5"N, CP 680-110/4"N, CP 680-160/6"N, CP 682-75/2.5", CP 682-110/4", CP 680-M 2", CP 680-M 3", CP 680-M 4", CP 680-P 2", CP 680-P 3", CP 680-P 4", CP 680-P 6"  
3. Through Penetrants — One metallic pipe or tubing to be installed within the firestop device. Pipe or tubing to be rigidly supported on both sides of floor assembly. The following types of pipe or tubing may be used:  
A. Steel Pipe — Nom 4 in. (102 mm) diam (or smaller) Schedule 10 (or heavier) steel pipe.  
B. Copper Tubing — Nom 4 in. (102 mm) diam (or smaller) Type L (or heavier) copper tubing.  
C. Copper Pipe — Nom 4 in. (102 mm) diam (or smaller) Regular (or heavier) copper pipe.  
The firestop device, metallic penetrant and pipe covering shall be sized as follows:

Nom Pipe Diam. in. (mm)	Nom Pipe Covering Thickness, in. (mm)	Firestop Device	T Rating, Hr
1/2 (13)	1 (25)	CP 680-75/2.5"N, CP 682-75/2.5", CP 680-M 2", CP 680-P 2"	3/4
1 (25)	1 (25)	CP 680-M 3", CP 680-P 3"	3/4
1 (25) (See Item 5)	1-1/2 (38)	CP 682-110/4", CP 680-M 4", CP 680-P 4"	3/4
2 (51)	1 (25)	CP 680-110/4"N, CP 682-110/4", CP 680-M 4", CP 680-P 4"	1
2 (51)	2 (51)	CP 680-160/6"N	3/4
4 (102)	1 (25)	CP 680-160/6"N	3/4
		CP 680-P 6"	3/4

4. Pipe Covering\* — Nom 1, 1-1/2 and 2 in. (25, 38 and 51 mm) thick hollow cylindrical heavy density (min 3.5 pcf or 56 kg/m<sup>3</sup>) glass fiber units, jacketed on the outside with an adhesive jacket. Longitudinal joints sealed with metal fasteners or factory-applied SSL tape. Transverse joints secured with metal fasteners or with butt tape applied with the product.  
See Pipe and Equipment Covering-Materials (BRGU) category in the Building Materials Directory for names of manufacturers. Any pipe covering material meeting the above specifications and bearing the UL Classification Marking with a Flame Spread Index of 25 or less and a Smoke Developed Index of 50 or less may be used.  
5. Packing Material — When using a 1 in. (25 mm) diam pipe with 1-1/2 in. (38 mm) thick glass fiber pipe insulation in a 4 in. (102 mm) device, a min 2 in. (51 mm) thickness of min 4 pcf (64 kg/m<sup>3</sup>) mineral wool batt insulation shall be firmly packed into top of device, flush with the top of the device.  
\*Bearing the UL Classification Mark

Reproduced by HILTI, Inc. Courtesy of Underwriters Laboratories, Inc. December 14, 2006  
**Hilti Firestop Systems**

**System No. F-A-2053**  
F Rating — 2 Hr  
L Rating At Ambient — Less Than 1 CFM/sq ft (See Item 3)  
L Rating At 400 F — Less Than 1 CFM/sq ft (See Item 3)  
W Ratings — Class 1 (See Items 3, 4 and 4A)

1. Floor Assembly — Min 2-1/2 in. (64 mm) thick reinforced lightweight or normal weight (100-150 pcf or 1600-2400 kg/m<sup>3</sup>) concrete.  
1A. Floor Assembly - (Optional - Not Shown) — The fire rated unprotected concrete and steel floor assembly shall be constructed of the materials and in the manner specified in the individual D900 Series Designs in the UL Fire Resistance Directory and as summarized below:  
A. Concrete — Min 2-1/2 in. (64 mm) thick reinforced lightweight or normal weight (100-150 pcf or 1600-2400 kg/m<sup>3</sup>) concrete.  
B. Steel Floor and Form Units\* — Composite or non-composite max 3 in. (76 mm) deep galv steel fluted units as specified in the individual Floor-Ceiling Design.  
2. Firestop Device\* — Cast in place firestop device permanently embedded during concrete placement or grouted in concrete assembly in accordance with accompanying installation instructions. The 3, 4 and 6 in. devices may extend a max 2 in. (51 mm) above the top surface of the concrete. The max extension above the slab for the 2 and 2.5 in. devices is not restricted.  
HILTI CONSTRUCTION CHEMICALS, DIV OF HILTI INC. — CP 680-75/2.5"N, CP 680-110/4"N, CP 680-160/6"N, CP 682-75/2.5", CP 682-110/4", CP 680-M 2", CP 680-M 3", CP 680-M 4", CP 680-P 2", CP 680-P 3", CP 680-P 4", CP 680-P 6"  
3. Through Penetrants — One nonmetallic pipe or conduit to be installed within the firestop system. Pipe or conduit to be rigidly supported on both sides of floor assembly. For W Rating with Water Barrier Module, pipe shall be installed from bottom of device. The following types and sizes of nonmetallic pipes or conduits may be used:  
A. Polyvinyl Chloride (PVC) Pipe — Nom 6 in. (152 mm) diam (or smaller) Schedule 40 solid or cellular core PVC pipe for use in closed (process or supply) or vented (drain, waste or vent) piping systems.  
B. Chlorinated Polyvinyl Chloride (CPVC) Pipe — Nom 6 in. (152 mm) diam (or smaller) SDR11.5 CPVC pipe for use in closed (process or supply) piping systems.  
C. Rigid Nonmetallic Conduit\* — Nom 6 in. (152 mm) diam (or smaller) Schedule 40 PVC conduit installed in accordance with the National Electrical Code (NFPA No. 70).  
The firestop devices and nonmetallic penetrants shall be sized as follows:

Nom Pipe Diameter	Firestop Device
1/2 in. to 2 in. (19 mm to 51 mm)	CP 680-75/2.5"N CP 680-P 2"
3 in. (76 mm)	CP 680-P 3"
3 in. to 4 in. (76 mm to 102 mm)	CP 680-110/4"N
6 in. (152 mm)	CP 680-160/6"N CP 680-P 6"

++ L Rating applies only to CP 680-P devices and only when the nom diam of pipe equals size of device (2 in. diam pipe in 2" device etc.). L Rating does not apply to CP 680N devices.  
4. Firestop Device\* — (Not shown) — Top seal plug for use with CP 680-75/2.5"N devices and nom pipe or conduit sizes 3/4 in. (19 mm) to 2 in. (51 mm), installed in accordance with the manufacturer's instructions. The top seal plug is optional for nom 1-1/2 in. (38 mm) pipes and conduits. Top seal plugs are required for all pipes and conduits less than nom 1-1/2 in. (38 mm). W Rating applies only when the CPS or IPS Top Seal Plugs are used.  
HILTI CONSTRUCTION CHEMICALS, DIV OF HILTI INC. — CPS and IPS Top Seal Plugs  
4A. Firestop Device\* — Water Barrier Module — (Optional, Not Shown) — Applies to nom 2", 3" and 4" water barrier modules used in combination with the CP 680-P 2", CP 680-P 3" and CP 680-P 4" devices, respectively, and supplied by device manufacturer. Module is threaded onto top of device. W Rating applies only when water barrier module is used.  
HILTI CONSTRUCTION CHEMICALS, DIV OF HILTI INC. — Water Barrier Module  
\*Bearing the UL Classification Mark

Reproduced by HILTI, Inc. Courtesy of Underwriters Laboratories, Inc. February 27, 2008  
**Hilti Firestop Systems**

**System No. C-AJ-1421**

ANSI/UL1479 (ASTM E814)	CANULC S115
F Rating — 2 or 3 Hr	F Rating — 2 or 3 Hr
T Rating — 0 Hr	FT Rating — 0 Hr
L Rating at Ambient — Less Than 1 CFM/sq ft	FH Rating — 2 or 3 Hr
L Rating at 400 F — Less Than 1 CFM/sq ft	FTH Rating — 0 Hr
	L Rating at Ambient — Less Than 1 CFM/sq ft
	L Rating at 400 F — Less Than 1 CFM/sq ft

1. Floor or Wall Assembly — Min 4-1/2 in. (114 mm) thick reinforced lightweight or normal weight (100-150 pcf or 1600-2400 kg/m<sup>3</sup>) concrete. Wall may also be constructed of any UL Classified Concrete Blocks\*. Max diam of opening is 32 in. (813 mm).  
See Concrete Blocks (CAZT) category in the Fire Resistance Directory for names of manufacturers.  
2. Metallic Sleeve — (Optional) Nom 32 in. (813 mm) diam (or smaller) Schedule 40 (or heavier) steel sleeve cast or grouted into floor or wall assembly, flush with floor or wall surface.  
3. Through-Penetrant — One metallic pipe or conduit to be installed either concentrically or eccentrically within the firestop system. The annular space between pipe, tube or conduit and periphery of opening shall be min 0 in. (point contact) to max 5-3/8 in. (137 mm). Pipe or conduit to be rigidly supported on both sides of floor or wall assembly. The following types and sizes of metallic pipes or conduits may be used:  
A. Steel Pipe — Nom 4 in. (102 mm) diam (or smaller) Schedule 10 (or heavier) steel pipe.  
B. Iron Pipe — Nom 4 in. (102 mm) diam (or smaller) cast or ductile iron pipe.  
C. Copper Pipe — Nom 4 in. (102 mm) diam (or smaller) Regular (or heavier) copper pipe.  
D. Copper Tubing — Nom 4 in. (102 mm) diam (or smaller) Type L (or heavier) copper tubing.  
E. Conduit — Nom 4 in. (102 mm) diam (or smaller) steel conduit.  
F. Conduit — Nom 4 in. (102 mm) diam (or smaller) steel electrical metallic tubing (EMT).  
4. Firestop System — The firestop system shall consist of the following:  
A. Packing Material — Min 4 in. (102 mm) thickness of min 4 pcf (64 kg/m<sup>3</sup>) mineral wool batt insulation firmly packed into opening as a permanent form. Packing material to be recessed from top surface of floor or from both surfaces of wall to accommodate the required thickness of fill material.  
B. Fill, Void or Cavity Material\* — Sealant — Min 1/4 in. (6 mm) thickness of fill material applied within the annulus, flush with top surface of floor or with both surfaces of wall. For 1 Hr-rated assemblies, a min 1/4 in. (6 mm) diam bead of fill material shall be applied at the concrete/pipe interface at the point contact location on the top surface of floor on both surfaces of wall.  
HILTI CONSTRUCTION CHEMICALS, DIV OF HILTI INC. — CFS-S SIL, CFS-G SIL, CFS-S SIL, FS-ONE Sealant, FS-ONE MAX Intumescent Sealant or CP80 Self-Levelling Firestop Sealant. CP80A, CFS-S SIL, FS-ONE Sealant or FS-ONE MAX Intumescent Sealant shall be used in floor applications only. When CP80A, CFS-S SIL or CFS-S SIL, FS-ONE Sealant is used, F Rating is 2 Hr.  
\*Indicates such products shall bear the UL or cUL Certification Mark for jurisdictions employing the UL or cUL Certification (such as Canada), respectively.

Reproduced by HILTI, Inc. Courtesy of Underwriters Laboratories, Inc. January 28, 2015  
**Hilti Firestop Systems**

**System No. C-AJ-1226**

ANSI/UL1479 (ASTM E814)	CANULC S115
F Rating — 3 Hr	F Rating — 3 Hr
T Rating — 0 Hr	FT Rating — 0 Hr
L Rating at Ambient — Less Than 1 CFM/sq ft	FH Rating — 3 Hr
L Rating at 400 F — 4 CFM/sq ft	FTH Rating — 0 Hr
	L Rating at Ambient — Less Than 1 CFM/sq ft
	L Rating at 400 F — 4 CFM/sq ft

1. Floor or Wall Assembly — Min 4-1/2 in. (114 mm) thick reinforced lightweight or normal weight (100-150 pcf or 1600-2400 kg/m<sup>3</sup>) concrete. Wall may also be constructed of any UL Classified Concrete Blocks\*. Max diam of opening is 32 in. (813 mm).  
2. Metallic Sleeve — (Optional) Nom 32 in. (813 mm) diam (or smaller) Schedule 40 (or heavier) steel sleeve cast or grouted into floor or wall assembly, flush with floor or wall surface or extending a max of 1 in. (25 mm) above floor or beyond both surfaces of wall.  
2A. Sheet Metal Sleeve — (Optional) Max 6 in. (152 mm) diam, min 26 ga. galv steel provided with a 26 ga galv steel square flange spot welded to the sleeve at approx mid-height, or flush with bottom of sleeve in floors, and sized to be a min of 2 in. (51 mm) larger than the sleeve diam. The sleeve is to be cast in place and may extend a max of 4 in. (102 mm) below the bottom of the deck and a max of 1 in. (25 mm) above the top surface of the concrete floor.  
2B. Sheet Metal Sleeve — (Optional) — Max 12 in. (305 mm) diam, min 24 ga galv steel provided with a 24 ga galv steel square flange spot welded to the sleeve at approx mid-height, or flush with bottom of sleeve in floors, and sized to be a min of 2 in. (51 mm) larger than the sleeve diam. The sleeve is to be cast in place and may extend a max of 4 in. (102 mm) below the bottom of the deck and a max of 1 in. (25 mm) above the top surface of the concrete floor.  
3. Through-Penetrant — One metallic pipe, tube or conduit to be installed either concentrically or eccentrically within the firestop system. The annular space between penetrant and periphery of opening shall be min 0 in. (point contact) to max 1-7/8 in. (46 mm). Penetrant may be installed with continuous point contact. Penetrant to be rigidly supported on both sides of floor or wall assembly. The following types and sizes of metallic penetrants may be used:  
A. Steel Pipe — Nom 30 in. (762 mm) diam (or smaller) Schedule 10 (or heavier) steel pipe.  
B. Iron Pipe — Nom 30 in. (762 mm) diam (or smaller) cast or ductile iron pipe.  
C. Copper Pipe — Nom 6 in. (152 mm) diam (or smaller) Regular (or heavier) copper pipe.  
D. Copper Tubing — Nom 6 in. (152 mm) diam (or smaller) Type L (or heavier) copper tubing.  
E. Conduit — Nom 6 in. (152 mm) diam (or smaller) steel conduit.  
F. Conduit — Nom 6 in. (152 mm) diam (or smaller) steel electrical metallic tubing (EMT).  
4. Firestop System — The firestop system shall consist of the following:  
A. Packing Material — Min 4 in. (102 mm) thickness of min 4 pcf (64 kg/m<sup>3</sup>) mineral wool batt insulation firmly packed into opening as a permanent form. Packing material to be recessed from top surface of floor or sleeve or from both surfaces of wall or sleeve as required to accommodate the required thickness of fill material.  
B. Fill, Void or Cavity Material\* — Sealant — Min 1/4 in. (6 mm) thickness of fill material applied within the annulus, flush with top surface of floor or sleeve or with both surfaces of wall or sleeve. At the point or continuous contact locations between penetrant and concrete or sleeve, a min 1/4 in. (6 mm) diam bead of fill material shall be applied at the concrete or sleeve/pipe penetrant interface on the top surface of floor and on both surfaces of wall.  
HILTI CONSTRUCTION CHEMICALS, DIV OF HILTI INC. — FS-ONE Sealant or FS-ONE MAX Intumescent Sealant  
\*Indicates such products shall bear the UL or cUL Certification Mark for jurisdictions employing the UL or cUL Certification (such as Canada), respectively.

Reproduced by HILTI, Inc. Courtesy of Underwriters Laboratories, Inc. January 07, 2015  
**Hilti Firestop Systems**

**System No. W-L-1249**  
F Ratings - 1 and 2 Hr (See Items 1 and 3)  
T Rating - 1/2 Hr

1. Wall Assembly The 1 or 2 hr fire-rated gypsum board/stud wall assembly shall be constructed of the materials and in the manner described in the individual U400 Series Wall or Partition Design in the UL Fire Resistance Directory and shall include the construction features:  
A. Studs Steel studs 3-1/2 in. deep, fabricated from 25 MSG galv steel, spaced max 24 in. OC.  
B. Gypsum Boards\* The gypsum board type, number of layers, fastener type and sheet orientation shall be as specified in the individual Wall and Partition Design. Max area of opening is 360 sq in. with max dimension of 30 in.  
The hourly F Rating of the firestop system is equal to the hourly fire rating of the wall assembly in which it is installed.  
2. Through Penetrants One or more nom 2 in. diam (or smaller) rigid steel conduit or electrical metallic tubing (EMT) to be installed within the opening. The annular space between conduits or tubing shall be min 0 in. (point contact) to max 3-3/8 in. The annular space between conduits or tubing and periphery of opening shall be min 0 in. (point contact) to max 3 in. Conduit or tubing to be rigidly supported on both sides of wall assembly.  
3. Fill Void or Cavity Material - Foam\* Fill material applied within annulus flush with both surfaces of the wall. Min fill material thickness for 1 Hr F Rating is 4-3/4 in. Min fill material thickness for 2 Hr F Rating is 6 in.  
HILTI CONSTRUCTION CHEMICALS, DIV OF HILTI INC. — IC-200 Fire Foam  
\*Bearing the UL Classification Mark

Reproduced by HILTI, Inc. Courtesy of Underwriters Laboratories, Inc. December 7, 2001  
**Hilti Firestop Systems**

Notes:

- Refer to section 15084 of the specifications. For Quality Control requirements, refer to the Quality Control portion of the specification.
- Details shown are typical details. If field conditions do not match requirements of typical details, approved alternate details shall be utilized. Field conditions and dimensions need to be verified for compliance with the details, including but not limited to the following:
  - Minimum and maximum Width of Joints
  - Type and thickness of fire-rated construction. The minimum assembly rating of the firestop assembly shall meet or exceed the highest rating of the adjacent construction.
- If alternate details matching the field conditions are not available, manufacturer's engineering judgment drawings are acceptable. Drawings shall follow the International Firestop Council (IFC) Guidelines for Evaluating Firestop Systems Engineering Judgments.
- References:
  - 2013 Underwriter's Laboratories Fire Resistance Directory, Volume 2
  - NFPA 101 Life Safety Code
  - All governing local and regional building codes
- Firestop System installation must meet requirements of ASTM E-814 (UL 1479) tested assemblies that provide a fire rating equal to that of construction being penetrated.
- All rated through-penetrations shall be prominently labeled with the following information:
  - ATTENTION: Fire Rated Assembly
  - UL System #
  - Product(s) used
  - Hourly Rating (F-Rating)
  - Installation Date

\*Notes to designer (delete this note after reading and replace with title block information)  
 1. Any modification to these details could result in an application/system not meeting the UL or Intertek Classification or the intended temperature or fire ratings.  
 2. Details shown are up to date as of February 2015.  
 3. For additional information on the details, refer to the most current "Underwriter's Laboratories Fire Resistance Directory (volume 2)."

JOB NUMBER: \_\_\_\_\_

DRAWN: \_\_\_\_\_

CHECKED: \_\_\_\_\_

ISSUE DATE: \_\_\_\_\_

REVISIONS: \_\_\_\_\_

TYPICAL FIRESTOP DETAILS

SHEET NUMBER: \_\_\_\_\_

**System No. W-L-2078**  
**F Ratings — 1 and 2 Hr (See Item 1)**  
**T Ratings — 0, 1 and 2 Hr (See Items 2 and 3)**  
**L Rating At Ambient — 3 CFM/Sq Ft**  
**L Rating At 400 F — Less Than 1 CFM/Sq Ft**

1. Wall Assembly — The fire-rated gypsum board/wall assembly shall be constructed of the materials and in the manner specified in the individual U300, U400, V400 or W400 Series Wall and Partition Designs in the UL Fire Resistance Directory and shall include the construction features noted below.  
A. Studs — Wall framing may consist of either wood studs or steel channel studs. Wood studs to consist of nom 2 by 4 in. (51 by 102 mm) lumber spaced max 16 in. (406 mm) OC. Steel studs to be min 2-1/2 in. (64 mm) wide and spaced max 24 in. (610 mm) OC.  
B. Gypsum Board — Nom 5/8 in. (16 mm) thick gypsum board, as specified in the individual Wall and Partition Design. Max diam of opening is 11-1/2 in. (292 mm).  
The hourly F Rating of the freestop system is equal to the hourly fire rating of the wall assembly in which it is installed.  
2. Through-Penetrants — One nonmetallic pipe, conduit or tubing to be installed within the freestop system. The annular space between pipe and periphery of opening shall be min 0 in. (point contact) to max 1/2 in. (13 mm). Pipe or conduit to be rigidly supported on both sides of the wall assembly. The following types and sizes of metallic pipes, conduits or tubing may be used:  
A. Polyvinyl Chloride (PVC) Pipe — Nom 10 in. (254 mm) diam (or smaller) Schedule 40 solid-core or cellular core PVC pipe for use in closed (process or supply) or vented (drain, waste or vent) piping system.  
B. Chlorinated Polyvinyl Chloride (CPVC) Pipe — Nom 10 in. (254 mm) diam (or smaller) SDR11.5 CPVC pipe for use in closed (process or supply) piping systems.  
C. Acrylonitrile Butadiene Styrene (ABS) Pipe — Nom 6 in. (152 mm) diam (or smaller) Schedule 40 solid-core or cellular core ABS pipe for use in closed (process or supply) or vented (drain, waste or vent) piping systems.  
D. Polypropylene Fluoride (PVDF) Pipe — Nom 4 in. (102 mm) diam (or smaller) PVDF pipe for use in closed (process or supply) or vented (drain, waste or vent) piping system.  
E. Polyethylene Glycol (PE) Pipe — Nom 4 in. (102 mm) diam (or smaller) PE pipe for use in closed (process or supply) or vented (drain, waste or vent) piping system.  
When max 6 in. diam pipe is used, T Rating is equal to the hourly fire rating of the wall. When nom 8 in. (203 or 254 mm) diam pipe is used, T Rating is 0 Hr.  
3. Firestop Device — Firestop collar — Firestop collar shall be installed in accordance with the accompanying installation instructions. Collar to be installed and latched around the pipe and secured to both sides of the wall using the anchor hooks provided with the collar. (Minimum two anchor hooks for 1-1/2 and 2 in. (38 and 51 mm) diam pipes, three anchor hooks for 3 and 4 in. (76 and 102 mm) diam pipes, four anchor hooks for 6 in. (152 mm) diam pipes, two anchor hooks for 8 in. (203 mm) diam pipes and leave anchor hooks for 10 in. (254 mm) diam pipes). The anchor hooks are to be secured to the surface of the wall with 3/16 in. (4.8 mm) diam by 2-1/2 in. (64 mm) long toggle bolts along with washers. As an alternate for pipe sizes of nom 4 in. diam, min No. 10 by 1-1/2 in. (25.4 by 38 mm) long drywall or laminate screws with min 3/4 in. (19 mm) steel washers may be used. When the device is used, T Rating shall not exceed 1 Hr.  
4. Fill, Void or Cavity Material — Sealant — Min 1/2 in. (13 mm) thickness of sealant applied within the annular space for nom 8 in. (203 mm) and 10 in. (254 mm) diam pipes, flush with each side of wall. Sealant in annular space is optional for max 6 in. (152 mm) diam pipes. A min 1/4 in. (6 mm) thickness of sealant is required within the annular space, flush with each side of wall, to attain the L Ratings for max 6 in. (152 mm) diam pipes.  
HILTI CONSTRUCTION CHEMICALS, DIV OF HILTI INC. — FS-One Sealant or FS-ONE MAX Intumescent Sealant  
\* Indicates such products shall bear the UL or cUL Certification Mark for jurisdictions employing the UL or cUL Certification (such as Canada), respectively.

**HILTI** Firestop Systems  
Reproduced by HILTI, Inc. Courtesy of Underwriters Laboratories, Inc. January 28, 2015

**System No. C-AJ-5091**  
**F Rating — 2 Hr**  
**T Ratings — 0 and 1 Hr (See Items 2 and 4)**  
**L Rating At Ambient — 4 CFM/Sq Ft**  
**L Rating At 400 F — Less Than 1 CFM/Sq Ft**  
**L Rating At Ambient — 4 CFM/Sq Ft**  
**L Rating At 400 F — Less Than 1 CFM/Sq Ft**

1. Floor or Wall Assembly — Min 4-1/2 in. (114 mm) thick reinforced lightweight or normal weight (100-150 pcf or 1600-2400 kg/m<sup>3</sup>) concrete. Wall may also be constructed of any UL Classified Concrete Blocks\*. Max diam of opening is 29 in. (737 mm).  
See Concrete Blocks (CAZT) category in the Fire Resistance Directory for names of manufacturers.  
2. Metallic Sleeve — (Optional) — Nom 3 in. (76.2 mm) diam (or smaller) Schedule 10 (or heavier) steel pipe sleeve cast or grouted into floor or wall assembly, flush with floor or wall surface or extending a max of 3 in. (76 mm) above floor or beyond both surfaces of wall. If the steel sleeve extends beyond the top surface of the floor or both surfaces of the wall, the F Rating of the freestop system is 0 Hr.  
3. Steel Metal Sleeve — (Optional) — Max 6 in. (152 mm) diam, min 26 gaw steel provided with a 26 gaw steel square flange spot welded to the sleeve at approximately mid-height, or flush with bottom of sleeve in floors, and sized to be a min of 2 in. (51 mm) larger than the sleeve diam. The sleeve is to be cast in place flush with bottom surface of floor and may extend a max of 1 in. (25 mm) above the top surface of the floor.  
4. Steel Metal Sleeve — (Optional) — Max 12 in. (305 mm) diam, min 24 gaw steel provided with a 24 gaw steel square flange spot welded to the sleeve at approximately mid-height, or flush with bottom of sleeve in floors, and sized to be a min of 2 in. (51 mm) larger than the sleeve diam. The sleeve is to be cast in place flush with bottom surface of floor and may extend a max of 1 in. (25 mm) above the top surface of the floor.  
3. Through Penetrants — One metallic pipe, conduit or tubing to be installed either concentrically or eccentrically within the freestop system. Pipe or tubing to be rigidly supported on both sides of floor or wall assembly. The following types and sizes of metallic pipes, conduits or tubing may be used:  
A. Steel Pipe — Nom 12 in. (305 mm) diam (or smaller) Schedule 10 (or heavier) steel pipe.  
B. Iron Pipe — Nom 10 in. (254 mm) diam (or smaller) cast or ductile iron pipe.  
C. Copper Tubing — Nom 6 in. (152 mm) diam (or smaller) Regular (or heavier) copper pipe.  
D. Pipe Covering — Min 1/2 in. (13 mm) to max 2 in. (51 mm) thick hollow cylindrical heavy density (min 3.5 pcf or 56 kg/m<sup>3</sup>) glass fiber units jacketed on the outside with an all-service jacket. Longitudinal joints sealed with metal fasteners or factory-applied self-sealing lap tape. Transverse joints secured with metal fasteners or with but tape supplied with the product. The annular space between the insulated pipe and the edge of the periphery of the opening shall be max 1/2 in. (13 mm) to max 1/2 in. (13 mm), (305 mm) diam. When thickness of pipe covering is less than 2 in. (51 mm), the F Rating for the freestop system is 1 Hr.  
See Pipe Equipment Covering — Materials — (BRGU) category in the Building Materials Directory for names of manufacturers. Any pipe covering material meeting the above specifications and bearing the UL Classification Marking with a Flame Spread Index of 25 or less and a Smoke Developed Index of 50 or less may be used.  
4A. Pipe Covering — (Not Shown) — As an alternate to Item 4, max 2 in. (51 mm) thick cylindrical calcium silicate (min 14 pcf or 224 kg/m<sup>3</sup>) units sized to the outside diam of the pipe or tube may be used. Pipe insulation secured with stainless steel bands or min 18 AWG stainless steel wire spaced max 12 in. (305 mm) OC. The annular space shall be max 1/2 in. (13 mm) to max 1/2 in. (13 mm).  
5. Firestop System — The freestop system shall consist of the following:  
A. Packing Material — Min 4 in. (102 mm) thickness of min 4 pcf (64 kg/m<sup>3</sup>) mineral wool batt insulation firmly packed into opening as a permanent form. Packing material to be recessed from top surface of floor or from both surfaces of wall as required to accommodate the required thickness of fill material.  
B. Fill, Void or Cavity Material — Sealant — Min 1/2 in. (13 mm) thickness of fill material applied within the annulus, flush with top surface of floor or both surfaces of wall.  
HILTI CONSTRUCTION CHEMICALS, DIV OF HILTI INC. — FS-One Sealant or FS-ONE MAX Intumescent Sealant  
\* Indicates such products shall bear the UL or cUL Certification Mark for jurisdictions employing the UL or cUL Certification (such as Canada), respectively.

**HILTI** Firestop Systems  
Reproduced by HILTI, Inc. Courtesy of Underwriters Laboratories, Inc. January 13, 2015

**System No. W-L-5029**  
**ANSIUL1479 (ASTM E814)**  
**F Ratings — 1, 2 and 3 Hr (See Items 1, 3 and 4)**  
**T Ratings — 0, 1/2, 1 and 1-1/4 Hr (See Item 3)**  
**L Rating At Ambient — 4 CFM/Sq Ft**  
**L Rating At 400 F — Less Than 1 CFM/Sq Ft**  
**ANSIUL1479 (ASTM E814)**  
**F Ratings — 1, 2 and 3 Hr (See Items 1, 3 and 4)**  
**T Ratings — 0, 1/2, 1 and 1-1/4 Hr (See Item 3)**  
**L Rating At Ambient — 4 CFM/Sq Ft**  
**L Rating At 400 F — Less Than 1 CFM/Sq Ft**

1. Wall Assembly — The 1, 2 or 3 hr fire-rated gypsum board/wall assembly shall be constructed of the materials and in the manner specified in the individual U300, U400, V400 or W400 Series Wall and Partition Designs in the UL Fire Resistance Directory and shall include the following construction features:  
A. Studs — Wall framing may consist of either wood studs or steel channel studs. Wood studs to consist of nom 2 by 4 in. (51 by 102 mm) lumber spaced max 16 in. (406 mm) OC. Steel studs to be min 2-1/2 in. (64 mm) wide and spaced max 24 in. (610 mm) OC. Additional framing members shall be used to completely frame around opening.  
B. Gypsum Board — Nom 5/8 in. (16 mm) thick with square or tapered edges. The gypsum board type, thickness, number of layers, fastener type and orientation shall be as specified in the individual Wall and Partition Design. Max diam of opening is 19-5/8 in. (473 mm).  
C. Steel Pipe — Nom 6 in. (152 mm) diam (or smaller) Regular (or heavier) copper pipe.  
D. Iron Pipe — Nom 12 in. (305 mm) diam (or smaller) cast or ductile iron pipe.  
E. Copper Tubing — Nom 6 in. (152 mm) diam (or smaller) Type L (or heavier) copper tubing.  
When the hourly F or FH Rating of the freestop system is equal to the hourly fire rating of the wall assembly in which it is installed, the hourly F or FH Rating of the freestop system is equal to the hourly fire rating of the wall assembly in which it is installed.  
2. Through Penetrants — One metallic pipe or tubing to be installed within the freestop system. Pipe or tubing to be rigidly supported on both sides of wall assembly. The following types and sizes of metallic pipes or tubing may be used:  
A. Steel Pipe — Nom 12 in. (305 mm) diam (or smaller) Schedule 10 (or heavier) steel pipe.  
B. Iron Pipe — Nom 12 in. (305 mm) diam (or smaller) cast or ductile iron pipe.  
C. Copper Tubing — Nom 6 in. (152 mm) diam (or smaller) Type L (or heavier) copper tubing.  
When the hourly F or FH Rating of the freestop system is equal to the hourly fire rating of the wall assembly in which it is installed, the hourly F or FH Rating of the freestop system is equal to the hourly fire rating of the wall assembly in which it is installed.  
3. Pipe Covering — Nom 1 in. (25.4 mm) thick hollow cylindrical heavy density (min 3.5 pcf or 56 kg/m<sup>3</sup>) glass fiber units jacketed on the outside with an all-service jacket. Longitudinal joints sealed with metal fasteners or factory-applied self-sealing lap tape. Transverse joints secured with metal fasteners or with but tape supplied with the product. For 1 and 2 hr F and FH Ratings, the annular space between insulated penetrant and periphery of opening shall be min 0 in. (point contact) to max 1/8 in. (4 mm). For 3 hr F and FH Ratings, the annular space shall be min 0 in. (point contact) to max 1/4 in. (6 mm).  
See Pipe and Equipment Covering — Materials — (BRGU) category in the Building Materials Directory for names of manufacturers. Any pipe covering material meeting the above specifications and bearing the UL Classification Marking with a Flame Spread Index of 25 or less and a Smoke Developed Index of 50 or less may be used.  
The hourly T, FT, FTH Ratings of the freestop system are 1/2 hr for 1 hr rated walls and 1 hr for 2 hr rated walls. For 3 hr rated walls, the hourly T, FT and FTH Ratings when steel and iron pipes are used are 1 Hr. For 3 hr rated walls, the hourly T, FT and FTH Ratings when copper penetrants are used are 1-1/4 hr for 2 in. (51 mm) thick pipe covering and 0 hr for pipe covering thickness less than 2 in. (51 mm).  
3A. Pipe Covering — (Not Shown) — As an alternate to Item 3, max 2 in. (51 mm) thick cylindrical calcium silicate (min 14 pcf) units sized to the outside diam of the pipe or tube may be used. Pipe insulation secured with stainless steel bands or min 18 AWG stainless steel wire spaced max 12 in. (305 mm) OC. When the alternate pipe covering is used, the T and FT Rating shall be as specified in Item 3 above.  
See Pipe and Equipment Covering — Materials — (BRGU) category in the Building Materials Directory for names of manufacturers. Any pipe covering material meeting the above specifications and bearing the UL Classification Marking with a Flame Spread Index of 25 or less and a Smoke Developed Index of 50 or less may be used.  
4. Fill, Void or Cavity Material — Sealant — Min 1/2 in. (13 mm) thickness of fill material applied within the annulus, flush with both surfaces of wall. For 3 hr F and FH Rating, min 1 in. (25 mm) thickness of fill material applied within the annulus, flush with both surfaces of wall. At the point contact location between pipe covering and gypsum board, a min 1/2 in. (13 mm) diam bead of fill material shall be applied at the pipe covering board interface on both surfaces of wall.  
HILTI CONSTRUCTION CHEMICALS, DIV OF HILTI INC. — FS-One Sealant or FS-ONE MAX Intumescent Sealant  
\* Indicates such products shall bear the UL or cUL Certification Mark for jurisdictions employing the UL or cUL Certification (such as Canada), respectively.

**HILTI** Firestop Systems  
Reproduced by HILTI, Inc. Courtesy of Underwriters Laboratories, Inc. March 18, 2015

**System No. C-AJ-1184**  
**ANSIUL1479 (ASTM E814)**  
**F Rating — 3 Hr**  
**T Rating — 0 Hr**  
**ANSIUL1479 (ASTM E814)**  
**F Rating — 3 Hr**  
**T Rating — 0 Hr**

1. Floor or Wall Assembly — Min 4-1/2 in. (114 mm) thick reinforced lightweight or normal weight (100-150 pcf or 1600-2400 kg/m<sup>3</sup>) concrete. Wall may also be constructed of any UL Classified Concrete Blocks\*. Floor may also be constructed of any UL Classified 1-1/2 in. (38 mm) thick UL Classified hollow core Precast Concrete Units\*. Max diam of opening is 19 in. (395 mm) when concrete floor or wall is used and max 7 in. (178 mm) when precast concrete units are used.  
See Concrete Blocks (CAZT) and Precast Concrete Units (CPTU) categories in the Fire Resistance Directory for names of manufacturers.  
2. Through-Penetrants — One metallic pipe, conduit or tubing to be installed either concentrically or eccentrically within the freestop system. The annular space between pipe, conduit or tubing and periphery of opening shall be min 0 in. (point contact) to max 3-1/4 in. (83 mm). Pipe, conduit or tubing to be rigidly supported on both sides of floor or wall assembly. The following types and sizes of metallic pipes, conduits or tubing may be used:  
A. Steel Pipe — Nom 10 in. (254 mm) diam (or smaller) Schedule 10 (or heavier) steel pipe.  
B. Iron Pipe — Nom 10 in. (254 mm) diam (or smaller) cast or ductile iron pipe.  
C. Conduit — Nom 4 in. (102 mm) diam (or smaller) steel electrical metallic tubing or steel conduit.  
D. Copper Tubing — Nom 4 in. (102 mm) diam (or smaller) Type L (or heavier) copper pipe.  
E. Copper Pipe — Nom 6 in. (152 mm) diam (or smaller) Regular (or heavier) copper pipe.  
3. Forms — (Not Shown, Optional) — Used as a form to prevent leakage of fill material during installation. Forms to be rigid steel material, cut to fit the contour of the penetrating item and positioned to accommodate the required thickness of fill material. Forms to be removed after fill material has cured. Additional forming material may be used concrete block wall is penetrated. A min 1/2 in. (13 mm) thickness of min 4 pcf (64 kg/m<sup>3</sup>) mineral wool batt insulation is firmly packed into the annulus as a permanent form and recessed from both surfaces of the wall as required to accommodate the required thickness of fill material.  
4. Fill, Void or Cavity Material — Sealant — Min 1 in. (25 mm) thickness of fill material applied within the annulus. At the point contact location between penetrant and concrete, a min 1/2 in. (13 mm) diam bead of fill material shall be applied at the concrete through penetrant interface. When precast concrete units are used, the fill material shall be installed within the annular space, flush with inner surface of floor. When concrete block wall is penetrated, a min 1 in. (25 mm) thickness of fill material shall be applied within the annulus flush with both surfaces of wall.  
HILTI CONSTRUCTION CHEMICALS, DIV OF HILTI INC. — FS-One Sealant or FS-ONE MAX Intumescent Sealant  
\* Indicates such products shall bear the UL or cUL Certification Mark for jurisdictions employing the UL or cUL Certification (such as Canada), respectively.

**HILTI** Firestop Systems  
Reproduced by HILTI, Inc. Courtesy of Underwriters Laboratories, Inc. January 07, 2015

**System No. W-L-7040**  
**ANSIUL1479 (ASTM E814)**  
**F Ratings — 1 and 2 Hr (See Items 1 and 3)**  
**T Ratings — 0 Hr**  
**L Rating At Ambient — Less Than 1 CFM/Sq Ft**  
**L Rating At 400° F — Less Than 1 CFM/Sq Ft**  
**ANSIUL1479 (ASTM E814)**  
**F Ratings — 1 and 2 Hr (See Items 1 and 3)**  
**T Ratings — 0 Hr**  
**L Rating At Ambient — Less Than 1 CFM/Sq Ft**  
**L Rating At 400° F — Less Than 1 CFM/Sq Ft**

1. Wall Assembly — The fire-rated gypsum board/wall assembly shall be constructed of the materials and in the manner specified in the individual U300, U400, V400 or W400 Series Wall and Partition Designs in the Fire Resistance Directory and shall include the following construction features:  
A. Studs — Wall framing may consist of either wood studs or steel channel studs. Wood studs to consist of nom 2 by 4 in. (51 by 102 mm) lumber spaced max 16 in. (406 mm) OC. Steel studs to be min 2-1/2 in. (64 mm) wide and spaced max 24 in. (610 mm) OC. Additional framing members shall be used to completely frame around opening.  
B. Gypsum Board — Nom 5/8 in. (16 mm) thick with square or tapered edges. The gypsum wallboard type, thickness, number of layers and orientation shall be as specified in the individual Wall and Partition Design. Max area of opening is 1300 in<sup>2</sup> (84 m<sup>2</sup>) with the dimension of 50 in. (127 mm). The hourly F and FH Ratings of the freestop system are equal to the hourly fire rating of the wall assembly in which it is installed.  
2. Steel Duct — Nom 3 in. (76.2 mm) by 48 in. (1219 mm) (or smaller) 24 gauge (or heavier) galv steel duct to be installed within the freestop system. The annular space shall be min 0 in. (point contact) to, a max 2 in. (51 mm) Duct to be rigidly supported on both sides of the wall assembly.  
3. Firestop System — The freestop system shall consist of the following:  
A. Fill, Void or Cavity Material — Sealant — Min 5/8 in. (16 mm) thickness of fill material applied within annulus flush with both surfaces of wall. At point contact location, a min 1/2 in. (13 mm) diam bead of fill material shall be applied to the wall/duct interface on both surfaces of wall.  
HILTI CONSTRUCTION CHEMICALS, DIV OF HILTI INC. — FS-One Sealant, FS-ONE MAX Intumescent Sealant, CP906 Flexible Sealant.  
B. Steel Retaining Angle — Nom 16 gauge (0.048 in.) galv steel angles cut to fit contour of duct with a 2 in. overlap on the duct and a min 1 in. overlap on the gypsum board assembly on both sides of wall. 2 in. leg of angle secured to duct with min No. 8 by 24 in. long steel metal screws, spaced a max of 6 in. OC. When fill of material is used at joint contact locations, angles shall be installed prior to full material curing.  
\* Indicates such products shall bear the UL or cUL Certification Mark for jurisdictions employing the UL or cUL Certification (such as Canada), respectively.

**HILTI** Firestop Systems  
Reproduced by HILTI, Inc. Courtesy of Underwriters Laboratories, Inc. January 27, 2015

**System No. W-L-7155**  
**ANSIUL1479 (ASTM E814)**  
**F Ratings — 1 and 2 Hr (See Item 1)**  
**T Ratings — 0 Hr**  
**L Rating At Ambient — Less Than 1 CFM/Sq Ft**  
**L Rating at 400° F — Less Than 1 CFM/Sq Ft**  
**ANSIUL1479 (ASTM E814)**  
**F Ratings — 1 and 2 Hr (See Item 1)**  
**T Ratings — 0 Hr**  
**L Rating At Ambient — Less Than 1 CFM/Sq Ft**  
**L Rating at 400° F — Less Than 1 CFM/Sq Ft**

1. Wall Assembly — The 1 or 2 hr fire-rated gypsum board/wall assembly shall be constructed of the materials and in the manner specified in the individual U300, U400, V400 or W400 Series Wall and Partition Designs in the UL Fire Resistance Directory and shall include the following construction features:  
A. Studs — Wall framing shall consist of min 3-1/2 in. (89 mm) wide steel channel studs spaced max 24 in. (610 mm) OC. Additional steel studs shall be used to completely frame the opening.  
B. Gypsum Board — 5/8 in. (16 mm) thick, 4 ft (1.22 m) thick with square or tapered edges. The gypsum board type, thickness, number of layers, fastener type and orientation shall be as specified in the individual Wall and Partition Design in the UL Fire Resistance Directory. The hourly F and FH Ratings of the freestop system are equal to the hourly fire rating of the wall assembly in which it is installed.  
2. Steel Duct — Max 100 in. by 100 in. (2.5 by 2.5 m) galv steel duct to be installed either concentrically or eccentrically within the freestop system. The duct shall be constructed and reinforced in accordance with SMACNA construction standards. The space between the steel duct and periphery of opening shall be min 0 in. (point contact) to max 2 in. (51 mm). Steel duct to be rigidly supported on both sides of the wall assembly.  
2A1. Through-Penetrating Product — As an alternate to Item 2, Fiber cement with galvanized steel facing, 14 in. (356 mm) thick, with a max cross-sectional area of 43.0 in<sup>2</sup> (4 m<sup>2</sup>) and a max individual dimension of 7.34 in. (187 mm). Duct to be installed either concentrically or eccentrically within the freestop system such that the annular space is min 0 in. (point contact) to max 2 in. (51 mm). Duct to be rigidly supported on both sides of wall assembly and installed in accordance. Refer to Ventilation Duct Assemblies in Vol. 2 of the Fire Resistance Directory.  
2A2. DURASYSTEMS BARRIERS INC. — Type DuraDuct HP.  
2A3. Through-Penetrating Product — As an alternate to Item 2, Fiber cement with galvanized steel facing, 14 in. (356 mm) thick, with a max cross-sectional area of 1764 in<sup>2</sup> (1.14 m<sup>2</sup>), and a max individual dimension of 42 in. (1067 mm). Duct to be installed either concentrically or eccentrically within the freestop system such that the annular space is min 0 in. (point contact) to max 2 in. (51 mm). Duct to be rigidly supported on both sides of wall assembly and installed in accordance. Refer to Ventilation Duct Assemblies in Vol. 2 of the Fire Resistance Directory.  
2A4. DURASYSTEMS BARRIERS INC. — Type DuraDuct SW.  
2A5. Through-Penetrating Product — As an alternate to Item 2, Galvanized steel faced duct panel, with a max cross-sectional area of 2400 sq in. (1.56 m<sup>2</sup>) and a max individual dimension of 48-1/2 in. (1238 mm) Duct to be installed either concentrically or eccentrically within the freestop system such that the annular space is min 0 in. (point contact) to max 2 in. (51 mm). Duct to be rigidly supported on both sides wall assembly. Refer to Ventilation Duct Assemblies in Vol. 2 of the Fire Resistance Directory.  
3. Firestop System — The freestop system shall consist of the following:  
A. Packing Material — (Optional, Not Shown) — Polyethylene backer rod, mineral wool batt insulation or fiberglass batt insulation friction fitted into annular space. Packing material to be recessed from both surfaces of wall as required to accommodate the required thickness of fill material.  
B. Fill, Void or Cavity Material — Sealant — Min 5/8 in. (16 mm) thickness of fill material applied within annulus, flush with both surfaces of wall.  
C. Steel Retaining Angles — Min No. 16 gauge (0.059 in. or 1.5 mm) galv steel angles sized to lap steel duct a min of 2 in. (51 mm) and lap wall surfaces a min of 1 in. (25 mm) from each end of steel duct and spaced a max of 6 in. (152 mm) OC. When max duct dimension does not exceed 48 in. (122 cm) and duct area does not exceed 1300 in<sup>2</sup> (837 cm<sup>2</sup>), angles may be spaced a max of 6 in. (152 mm) OC. When max 1-1/2 in. (38 mm) thick insulation is used, steel angles are optional for each side of steel duct that do not exceed the dimension specified in Table below, dependent on packing material and annular space as specified.

Max Duct Dimensi on	Duct Thickness	Annular Space	Packing Material	Angle (Item 3C) Require d
24 in. (610 mm)	24 ga or heavier	1/2 in. min to 1 in. max (13 to 25 mm)	Item 3A1	No

**HILTI** Firestop Systems  
Reproduced by HILTI, Inc. Courtesy of Underwriters Laboratories, Inc. January 27, 2015

**System No. C-AJ-7051**  
**ANSIUL1479 (ASTM E814)**  
**F Rating — 3 Hr**  
**T Rating — 1 Hr**  
**ANSIUL1479 (ASTM E814)**  
**F Rating — 3 Hr**  
**T Rating — 1 Hr**

1. Floor or Wall Assembly — Min 4-1/2 in. (114 mm) thick reinforced lightweight or normal weight (100-150 pcf or 1600-2400 kg/m<sup>3</sup>) concrete floor or min 5-1/2 in. (140 mm) thick lightweight or normal weight concrete wall. Wall may also be constructed of any UL Classified Concrete Blocks\*. Max area of opening is 1024 in. sq (6606 cm<sup>2</sup>) with a max dimension of 32 in. (813 mm).  
See Concrete Blocks (CAZT) category in the Fire Resistance Directory for names of manufacturers.  
2. Steel Duct — Nom 30 by 30 in. (762 by 762 mm) by No. 24 gauge (or heavier) galv steel duct. One steel duct to be positioned within the freestop system. The annular space shall be min 14 in. (356 mm) to max 1-3/4 in. (44 mm). Duct to be rigidly supported on both sides of floor or wall assembly.  
3. Firestop System — The freestop system shall consist of the following:  
A. Packing Material — Min 3-1/2 in. (89 mm) thickness of min 4 pcf (64 kg/m<sup>3</sup>) mineral wool batt insulation firmly packed into opening as a permanent form between the bare steel duct and the periphery of the opening. Packing material to be recessed from top surface of floor or both surfaces of wall as required to accommodate the required thickness of fill material.  
B. Fill, Void or Cavity Material — Sealant — Min 1 in. (25 mm) thickness of fill material applied within the annulus, flush with top surface of floor or both surfaces of wall.  
HILTI CONSTRUCTION CHEMICALS, DIV OF HILTI INC. — CP 060 Flexible Firestop Sealant, FS-ONE Sealant or FS-ONE MAX Intumescent Sealant.  
4. Steel Retaining Angle — Nom 2 in. by 2 in. (51 by 51 mm) by No. 16 gauge (or heavier) steel angles attached to all four sides of the steel duct on the top surface of the surface of the wall. The angles shall be attached with No. 8 (or larger) steel sheet metal screws spaced max of 1 in. (25 mm) from each end and a max of 3 in. (76 mm) OC.  
\* Indicates such products shall bear the UL or cUL Certification Mark for jurisdictions employing the UL or cUL Certification (such as Canada), respectively.

**HILTI** Firestop Systems  
Reproduced by HILTI, Inc. Courtesy of Underwriters Laboratories, Inc. January 14, 2015

**System No. W-L-7156**  
**ANSIUL1479 (ASTM E814)**  
**F Ratings — 1 and 2 Hr (See Item 1)**  
**T Rating — 0 Hr**  
**ANSIUL1479 (ASTM E814)**  
**F Ratings — 1 and 2 Hr (See Item 1)**  
**T Rating — 0 Hr**

1. Wall Assembly — The 1 or 2 hr fire-rated gypsum board/wall assembly shall be constructed of the materials and in the manner specified in the individual U300, U400, V400 or W400 Series Wall and Partition Designs in the UL Fire Resistance Directory and shall include the following construction features:  
A. Studs — Wall framing shall consist of either wood studs or steel channel studs. Wood studs to consist of nom 2 by 4 in. (51 by 102 mm) lumber spaced max 16 in. (406 mm) OC. Steel studs to be min 3-1/2 in. (89 mm) wide and spaced max 24 in. (610 mm) OC. Additional framing members shall be used to completely frame around opening.  
B. Gypsum Board — Min 5/8 in. (16 mm) thick with square or tapered edges. The gypsum board type, thickness, number of layers and orientation shall be as specified in the individual Wall and Partition Design. Max size of opening is 210 sq in. (1355 cm<sup>2</sup>) with a max width of 14-1/2 in. (368 mm) for wood studs. Max size of opening is 76.2 sq ft (7 m<sup>2</sup>) with a max width of 105-1/2 in. (2.7 m) for steel studs.  
The hourly F and FH Ratings of the freestop system are equal to the hourly fire rating of the wall in which it is installed.  
2. Steel Duct — Max 100 by 100 in. (2.5 by 2.5 m) galv steel duct to be installed within the framed opening. The duct shall be constructed and reinforced in accordance with SMACNA construction standards. Steel duct to be rigidly supported on both sides of wall assembly.  
3. Batts and Blankets — Nom 1-1/2 or 2 in. (38 or 51 mm) thick glass fiber batt or blanket (min 3/4 pcf or 12 kg/m<sup>3</sup>) jacketed on the outside with a foil-scrim-kraft facing. Longitudinal and transverse joints sealed with aluminum foil tape. During the installation of the fill material, the batt or blanket shall be compressed minimum 50% such that the annular space within the freestop system shall be min 1/2 in. (13 mm) to max 2 in. (51 mm).  
See Batts and Blankets (BKNV) category in the Building Materials Directory for names of manufacturers. Any batt or blanket meeting the above specifications and bearing the UL Classification Marking with a Flame Spread Index of 25 or less and a Smoke Developed Index 50 or less may be used.  
4. Firestop System — The freestop system shall consist of the following:  
A. Packing Material — Min 3-5/8 (92 mm) or 4-7/8 in. (124 mm) thickness of min 4 pcf (64 kg/m<sup>3</sup>) mineral wool batt insulation firmly packed into opening as a permanent form for 1 or 2 hr fire-rated walls, respectively. Packing material to be recessed from both surfaces of wall to accommodate the required thickness of fill material.  
B. Fill, Void or Cavity Material — Sealant — Min 5/8 in. (16 mm) thickness of fill material applied within annulus, flush with both surfaces of wall.  
HILTI CONSTRUCTION CHEMICALS, DIV OF HILTI INC. — FS-ONE Sealant or FS-ONE MAX Intumescent Sealant  
C. Steel Retaining Angles — Min No. 16 gauge (0.059 in. or 1.5 mm) galv steel angles sized to lap steel duct a min of 2 in. (51 mm) and lap wall surfaces a min of 1 in. (25 mm) from each end of steel duct and spaced a max of 6 in. (152 mm) OC. When max duct dimension does not exceed 48 in. (122 cm) and duct area does not exceed 1300 in<sup>2</sup> (837 cm<sup>2</sup>), angles may be spaced a max of 6 in. (152 mm) OC. When max 1-1/2 in. (38 mm) thick insulation is used, steel angles are optional for each side of steel duct that do not exceed the dimension specified in Table below, dependent on packing material and annular space as specified.

Max Duct Dimensi on	Duct Thickness	Annular Space	Packing Material	Angle (Item 3C) Require d
24 in. (610 mm)	24 ga or heavier	1/2 in. min to 1 in. max (13 to 25 mm)	Item 3A1	No

**HILTI** Firestop Systems  
Reproduced by HILTI, Inc. Courtesy of Underwriters Laboratories, Inc. January 07, 2015

**Notes:**

- Refer to section 15084 of the specifications. For Quality Control requirements, refer to the Quality Control portion of the specification.
- Details shown are typical details. If field conditions do not match requirements of typical details, approved alternate details shall be utilized. Field conditions and dimensions need to be verified for compliance with the details, including but not limited to the following:
  - Minimum and maximum Width of Joints
  - Type and thickness of fire-rated construction. The minimum assembly rating of the firestop assembly shall meet or exceed the highest rating of the adjacent construction.
- If alternate details matching the field conditions are not available, manufacturer's engineering judgment drawings are acceptable. Drawings shall follow the International Firestop Council (IFC) Guidelines for Evaluating Firestop Systems Engineering Judgments.
- References:
  - 2013 Underwriter's Laboratories Fire Resistance Directory, Volume 2
  - NFPA 101 Life Safety Code
  - All governing local and regional building codes
- Firestop System installation must meet requirements of ASTM E-814 (UL 1479) tested assemblies that provide a fire rating equal to that of construction being penetrated.
- All rated through-penetrations shall be prominently labeled with the following information:
  - ATTENTION: Fire Rated Assembly
  - UL System #
  - Product(s) used
  - Hourly Rating (F-Rating)
  - Installation Date

\*Notes to designer (delete this note after reading and replace with title block information)  
 1. Any modification to these details could result in an application/system not meeting the UL or Intertek Classification or the intended temperature or fire ratings.  
 2. Details shown are up to date as of February 2015.  
 3. For additional information on the details, refer to the most current "Underwriter's Laboratories Fire Resistance Directory (volume 2)."

**JOB NUMBER:** \_\_\_\_\_

**DRAWN:** \_\_\_\_\_

**CHECKED:** \_\_\_\_\_

**ISSUE DATE:** \_\_\_\_\_


**REVISIONS:**

**TYPICAL FIRESTOP DETAILS**

**SHEET NUMBER:** \_\_\_\_\_

**SHEET NUMBER:** \_\_\_\_\_

System No. F-A-1105	
ANSI/UL1479 (ASTM E814)	CANULC S115
F Rating - 2 Hr	F Rating - 2 Hr
T Rating - 2 Hr	FT Rating - 2 Hr
L Rating At Ambient - Less Than 1 CFM/sq ft	FH Rating - 2 Hr
L Rating At 400 F - 4 CFM/sq ft	FTH Rating - 2 Hr
W Rating - Class 1 (See Item 3B)	L Rating At Ambient - Less Than 1 CFM/sq ft
	L Rating At 400 F - 4 CFM/sq ft




1. Floor Assembly — Min 4-1/2 in. (114 mm) thick reinforced lightweight or normal weight (100-150 pcf or 1600-2400 kg/m<sup>3</sup>) concrete. As an alternate, any min 2 hr fire rated D700, D800 or D900 Series Floor-Ceiling Design in the UL Fire Resistance Directory having a min 2-1/2 in. (64 mm) thickness of lightweight or normal weight (100-150 pcf or 1600-2400 kg/m<sup>3</sup>) concrete topping over the steel deck may be used. Max diam of opening is 12/34 in. (254 mm).
2. Through-Penetrant — One metallic pipe installed concentrically or eccentrically within opening. Annular space between penetrant and periphery of opening shall be min 0 in. (point contact) to max 2 in. (51 mm). Penetrant to be rigidly supported on both sides of floor assembly. The following types and sizes of penetrants may be used:
  - A. Steel Pipe — Nom 10 in. (254 mm) diam (or smaller) Schedule 40 (or heavier) steel pipe.
  - B. Iron Pipe — Nom 10 in. (254 mm) diam (or smaller) cast or ductile iron pipe.
  - C. Conduit — Nom 4 in. (102 mm) diam (or smaller) steel electrical metallic tubing or nom 6 in. (152 mm) diam (or smaller) rigid steel conduit.
3. Firestop System — The firestop system shall consist of the following:
  - A. Packing Material — Min 2 in. (51 mm) thickness of min 4 pcf (64 kg/m<sup>3</sup>) mineral wool batt insulation firmly packed into opening as a permanent form. When CP 604, CFS-S SIL, GO or CFS-S SIL, SL Sealant is used (see Item 3B), min thickness of packing material is 4 in. (102 mm) and min thickness of fire is 4-1/2 in. (114 mm).
  - B. Fire "Void or Cavity Material" Sealant — Min 1/2 in. (13 mm) thickness of sealant applied within the annulus, flush with top surface of floor.
  - C. Firestop Sealant, CFS-S SIL GO or CFS-S SIL, SL Sealant.

W Rating applies only when CP 604, CFS-S SIL, GO or CFS-S SIL, SL Sealant is used.  
 C. Duct Wrap Material — Encapsulated duct wrap tightly wrapped around penetrant to extend 24 in. (610 mm) above the floor for penetrants of nom 4 in. (102 mm) diam or smaller, and 36 in. (914 mm) above floor for penetrants greater than a nom 4 in. (102 mm) diam. An additional layer of encapsulated duct wrap tightly wrapped around the first layer of duct wrap to extend 12 in. (305 mm) (914 mm) above floor. All longitudinal seams of both layers of duct wrap and joints between layers of duct wrap are sealed with foil tape. One of the following types and thicknesses of duct wrap may be used:  
 C1. Nom 1-1/2 in. (38 mm) or 2 in. (51 mm) thick encapsulated duct wrap.  
 C2. Nom 1-1/2 in. (38 mm) thick encapsulated duct wrap.  
 C3. Nom 1-1/2 in. (38 mm) thick encapsulated duct wrap.  
 THERMAL CERAMICS INC. — FireMaster FastWrap XL Duct Insulation  
 \* Indicates such products shall bear the UL or cUL Certification Mark for jurisdictions employing the UL or cUL Certification (such as Canada), respectively.



Reproduced by HILTI, Inc. Courtesy of Underwriters Laboratories, Inc. January 15, 2015

System No. F-A-2213	
ANSI/UL1479 (ASTM E814)	CANULC S115
F Ratings — 2 and 3 Hr (See Items 1 and 1A)	F Ratings — 2 and 3 Hr (See Items 1 and 1A)
T Ratings — 0, 1/4 and 1/2 Hr (See Items 2, 2A and 4)	FT Ratings — 0 and 1/2 Hr (See Item 2)
L Rating At Ambient — Less Than 1 CFM/sq ft (See Item 3A)	FH Ratings — 0 and 1/2 Hr (See Items 1 and 1A)
L Rating At 400 F — 4 CFM/sq ft (See Item 3A)	FTH Ratings — 0 and 1/2 Hr (See Item 2)
W Rating — Class 1 (See Item 3A)	



1. Floor Assembly — Min 2-1/2 in. (64 mm) to max 8 in. (203 mm) thick reinforced lightweight or normal weight (100-150 pcf or 1600-2400 kg/m<sup>3</sup>) concrete. When concrete thickness is min 4-1/2 in. (114 mm), F Rating is 3 hr.
- 1A. Floor Assembly — (Optional, Not Shown) — The fire rated concrete and steel deck floor assembly shall be constructed of the materials and in the manner specified in the individual D700, D800 or D900 Series designs in the UL Fire Resistance Directory and as summarized below:
  - A. Concrete — Min 2-1/2 in. (64 mm) to max 8 in. (203 mm) thick reinforced lightweight or normal weight (100-150 pcf or 1600-2400 kg/m<sup>3</sup>) concrete, as measured over crest of fluted steel deck. When concrete topping thickness is min 4-1/2 in. (114 mm), F Rating is 3 hr.
  - B. Steel Floor and Form Units — Composite or non-composite max 3 in. (76 mm) deep galv steel fluted units as specified in the individual Floor-Ceiling Design.
2. Metallic Sleeve — (Optional, Not Shown) — Nom 4, 5, 6 or 9 in. (102, 127, 152 or 229 mm) diam, min 26 ga galv steel provided with a 26 ga galv steel square flange spot welded to the sleeve at approx mid-height, or flush with bottom of sleeve in floors, and sized to be a min of 2 in. (51 mm) larger than the sleeve diam. The sleeve is to be cast in place and may extend a max of 4 in. (102 mm) below the bottom of the deck and flush with the top surface of the concrete floor. When sheet metal sleeve is used, T Rating is 0 Hr.
3. Firestop Device — Drop-in firestop device installed in core-drilled or sleeved opening in concrete floor assembly in accordance with accompanying installation instructions. The firestop device flange should be secured to the top surface of the floor with three 1/4 in. (6 mm) diam by min 1-1/4 in. (32 mm) long steel expansion bolts or screw anchors (installed in a triangular fashion through holes provided). As alternates to the anchors specified above, Hilti 1/4 in. (6 mm) diam by 1-1/4 in. (32 mm) long KWIK-BOLT 3 steel expansion anchor or Hilti 1/4 in. (6 mm) by 3/4 in. (19 mm) long Metal HIT Anchor may be used. In addition, for nom 2 in. (51 mm), 3 in. and 4 in. (102 mm) firestop devices, four 11/16 in. (18 mm) long Hilti X-GH P18 MX steel fasteners may be installed through the steel flange, two on each side. The firestop devices shall be installed as detailed in the following table:

Core Hole or Sleeve Diam, In. (mm)	Firestop Device	Nom Diam of Through Penetrant, In. (mm)
4 (102)	CFS-DID 2"MD	2 (51) or smaller*
5 (102)	CFS-DID 3"MD	3 (76)
6 (152)	CFS-DID 4"MD	4 (102)
9 (229)	CFS-DID 6"MD	6 (152)

\* For pipe smaller than nom 2 in. (51 mm) diam, Adapter and Top Seal Plug is required to be used.  
 HILTI CONSTRUCTION CHEMICALS, DIV OF HILTI INC. — CFS-DID 2"MD, CFS-DID 3"MD, CFS-DID 4"MD, CFS-DID 6"MD  
 3A. Firestop Device — Water Barrier Module — (Optional, Not Shown) — Used in combination with the CFS-DID device and supplied by device manufacturer. Module is threaded onto top of device.  
 W Rating and L Rating apply only when water barrier module is used.  
 HILTI CONSTRUCTION CHEMICALS, DIV OF HILTI INC. — Water Barrier Module  
 4. Through Penetrant — One nonmetallic pipe to be installed within the firestop device. Pipe to be rigidly supported on both sides of floor assembly. The following types of pipe may be used:  
 A. Polyvinyl Chloride (PVC) Pipe — Nom 6 in. (152 mm) diam (or smaller) Schedule 40 solid core or cellular core PVC pipe for use in closed (process or supply) or vented (drain, waste or vent) piping system.  
 B. Acrylonitrile Butadiene Styrene (ABS) Pipe — Nom 6 in. (152 mm) diam (or smaller) Schedule 40 solid core or cellular core ABS pipe for use in closed (process or supply) or vented (drain, waste or vent) piping system.  
 C. Chlorinated Polyvinyl Chloride (CPVC) Pipe — Nom 6 in. (152 mm) diam (or smaller) SDR 13.5 CPVC pipe for use in closed (process or supply) or vented (drain, waste or vent) piping system.  
 D. Flame Retardant Polypropylene (FRPP) Pipe — Nom 6 in. (152 mm) diam (or smaller) Schedule 40 (or heavier) FRPP pipe for use in closed (process or supply) or vented (drain, waste or vent) piping systems.  
 T Rating is 1/4 hr when Pipe D is used.  
 \*Bearing the UL Classification Mark



Reproduced by HILTI, Inc. Courtesy of Underwriters Laboratories, Inc. May 18, 2011

System No. F-A-1106	
ANSI/UL1479 (ASTM E814)	CANULC S115
F Rating - 2 Hr	F Rating - 2 Hr
T Rating - 2 Hr	FT Rating - 2 Hr
L Rating At Ambient - Less Than 1 CFM/sq ft	FH Rating - 2 Hr
L Rating At 400 F - 4 CFM/sq ft	FTH Rating - 2 Hr
W Rating - Class 1 (See Item 3B)	L Rating At Ambient - Less Than 1 CFM/sq ft
	L Rating At 400 F - 4 CFM/sq ft



1. Floor Assembly — Min 4-1/2 in. (114 mm) thick reinforced lightweight or normal weight (100-150 pcf or 1600-2400 kg/m<sup>3</sup>) concrete. As an alternate, any min 2 hr fire rated D700, D800 or D900 Series Floor-Ceiling Design in the UL Fire Resistance Directory having a min 2-1/2 in. (64 mm) thickness of lightweight or normal weight (100-150 pcf or 1600-2400 kg/m<sup>3</sup>) concrete topping over the steel deck may be used.
2. Firestop Device — Cast in place firestop device permanently embedded during concrete placement or grouted in concrete floor assembly in accordance with accompanying installation instructions. Device sized to nom diam of penetrant. Device is to be trimmed flush with the top surface of the floor.

2A. Firestop Device — Water Barrier Module — (Optional, Not Shown) — Used in combination with the CP 680-P device to achieve a W Rating. Module is threaded onto top of device. W Rating applies only when water barrier module is used and pipe is installed from bottom of device.  
 HILTI CONSTRUCTION CHEMICALS, DIV OF HILTI INC. — Water Barrier Module  
 3. Through-Penetrant — One metallic pipe installed concentrically or eccentrically within opening. Penetrant to be rigidly supported on both sides of floor assembly. The following types and sizes of penetrants may be used:
 

- A. Steel Pipe — Nom 6 in. (152 mm) diam (or smaller) Schedule 40 (or heavier) steel pipe.
- B. Iron Pipe — Nom 6 in. (152 mm) diam (or smaller) cast or ductile iron pipe.
- C. Iron Pipe — Nom 4 in. (102 mm) diam (or smaller) steel electrical metallic tubing or nom 6 in. (152 mm) diam (or smaller) rigid steel conduit.


- 4. Duct Wrap Material — Encapsulated duct wrap tightly wrapped around penetrant to extend 24 in. (610 mm) above the floor for penetrants of nom 4 in. (102 mm) diam, and 36 in. (914 mm) above floor for penetrants greater than a nom 4 in. (102 mm) diam. An additional layer of encapsulated duct wrap tightly wrapped around the first layer of duct wrap to extend 12 in. (305 mm) (914 mm) above floor. All longitudinal seams of both layers of duct wrap and joints between layers of duct wrap are sealed with foil tape. One of the following types and thicknesses of duct wrap material shall be used:
- A. Nom 2 in. (51 mm) or 1-1/2 in. (38 mm) thick encapsulated duct wrap.
- B. Nom 1-1/2 in. (38 mm) thick encapsulated duct wrap.
- C. Nom 1-1/2 in. (38 mm) thick encapsulated duct wrap.

THERMAL CERAMICS INC. — FireMaster FastWrap XL Duct Insulation  
 \*Bearing the UL Classification Mark



Reproduced by HILTI, Inc. Courtesy of Underwriters Laboratories, Inc. September 02, 2011

System No. F-A-5046	
ANSI/UL1479 (ASTM E814)	CANULC S115
F Ratings — 2 and 3 Hr (See Items 1 and 1A)	F Ratings — 2 and 3 Hr (See Items 1 and 1A)
T Ratings — 0 and 1/2 Hr (See Item 2)	FT Ratings — 0 and 1/2 Hr (See Item 2)
L Rating At Ambient — Less Than 1 CFM/sq ft (See Item 3A)	FH Ratings — 0 and 1/2 Hr (See Items 1 and 1A)
L Rating At 400 F — 4 CFM/sq ft (See Item 3A)	FTH Ratings — 0 and 1/2 Hr (See Item 2)



1. Floor Assembly — Min 2-1/2 in. (64 mm) to max 8 in. (203 mm) thick reinforced lightweight or normal weight (100-150 pcf or 1600-2400 kg/m<sup>3</sup>) concrete. When concrete thickness is min 4-1/2 in. (114 mm), F Rating is 3 hr.
- 1A. Floor Assembly — (Optional, Not Shown) — The fire rated concrete and steel deck floor assembly shall be constructed of the materials and in the manner specified in the individual D700, D800 or D900 Series designs in the UL Fire Resistance Directory and as summarized below:
  - A. Concrete — Min 2-1/2 in. (64 mm) to max 8 in. (203 mm) thick reinforced lightweight or normal weight (100-150 pcf or 1600-2400 kg/m<sup>3</sup>) concrete, as measured over crest of fluted steel deck. When concrete topping thickness is min 4-1/2 in. (114 mm), the F and FH Ratings are 3 hr.
  - B. Steel Floor and Form Units — Composite or non-composite max 3 in. (76 mm) deep galv steel fluted units as specified in the individual Floor-Ceiling Design.
2. Metallic Sleeve — (Optional, Not Shown) — Nom 4, 5 or 6 in. (102, 127 or 152 mm) diam Schedule 10 (or heavier) steel sleeve cast or grouted into floor assembly, flush with floor surfaces. When metallic sleeve is used, the T, FT and FTH Ratings are 0 Hr.
- 2A. Sheet Metal Sleeve — (Optional, Not Shown) — Nom 4, 5, 6 or 9 in. (102, 127, 152 or 229 mm) diam, min 26 ga galv steel provided with a 26 ga galv steel square flange spot welded to the sleeve at approx mid-height, or flush with bottom of sleeve in floors, and sized to be a min of 2 in. (51 mm) larger than the sleeve diam. The sleeve is to be cast in place and may extend a max of 4 in. (102 mm) below the bottom of the deck and flush with the top surface of the concrete floor. When sheet metal sleeve is used, the T, FT and FTH Ratings are 0 Hr.
3. Firestop Device — Drop-in firestop device installed in core-drilled or sleeved opening in concrete floor assembly in accordance with accompanying installation instructions. The firestop device flange should be secured to the top surface of the floor with three 1/4 in. (6 mm) diam by min 1-1/4 in. (32 mm) long steel expansion bolts or screw anchors (installed in a triangular fashion through holes provided). As alternates to the anchors specified above, Hilti 1/4 in. (6 mm) diam by 1-1/4 in. (32 mm) long KWIK-BOLT 3 steel expansion anchor or Hilti 1/4 in. (6 mm) by 3/4 in. (19 mm) long Metal HIT Anchor may be used. In addition, for nom 2 in. (51 mm), 3 in. and 4 in. (102 mm) firestop devices, four 11/16 in. (18 mm) long Hilti X-GH P18 MX steel fasteners may be installed through the steel flange, two on each side. The firestop devices shall be installed as detailed in the following table:

Nom Pipe or Tube (Item 4) Diam, In. (mm)	Insulation Type (Item 5 or 5A) In. (mm)	Firestop Device	Core Hole or Sleeve Diam, In. (mm)	
1/2 (13)	3/4 or 1 (19 or 25)	AB/PPVC	CFS-DID 2"MD	4 (102)
1 (25)	3/4 or 1 (19 or 25)	AB/PPVC	CFS-DID 3"MD	5 (127)
2 (51)	3/4 or 1 (19 or 25)	AB/PPVC	CFS-DID 4"MD	6 (152)
4 (102)	3/4 or 1 (19 or 25)	AB/PPVC	CFS-DID 6"MD	9 (229)
1/2 (13)	1-1/2 (38) Glass Fiber	CFS-DID 2"MD	CFS-DID 2"MD	4 (102)
1 (25)	1 (25) Glass Fiber	CFS-DID 3"MD	CFS-DID 3"MD	5 (127)
1 (25)	1-1/2 (38) Glass Fiber	CFS-DID 4"MD	CFS-DID 4"MD	6 (152)
2 (51)	1 (25) Glass Fiber	CFS-DID 4"MD	CFS-DID 4"MD	6 (152)
2 (51)	2 (51) Glass Fiber	CFS-DID 6"MD	CFS-DID 6"MD	9 (229)
4 (102)	1 (25) Glass Fiber	CFS-DID 6"MD	CFS-DID 6"MD	9 (229)

System No. F-A-5046 (cont.)	
ANSI/UL1479 (ASTM E814)	CANULC S115
F Ratings — 2 and 3 Hr (See Items 1 and 1A)	F Ratings — 2 and 3 Hr (See Items 1 and 1A)
T Ratings — 0 and 1/2 Hr (See Item 2)	FT Ratings — 0 and 1/2 Hr (See Item 2)
L Rating At Ambient — Less Than 1 CFM/sq ft	FH Ratings — 0 and 1/2 Hr (See Items 1 and 1A)
L Rating At 400 F — 4 CFM/sq ft	FTH Ratings — 0 and 1/2 Hr (See Item 2)


1. Floor Assembly — Min 2-1/2 in. (64 mm) to max 8 in. (203 mm) thick reinforced lightweight or normal weight (100-150 pcf or 1600-2400 kg/m<sup>3</sup>) concrete. When concrete thickness is min 4-1/2 in. (114 mm), the F and FH Ratings are 3 hr.
- 1A. Floor Assembly — (Optional, Not Shown) — The fire rated concrete and steel deck floor assembly shall be constructed of the materials and in the manner specified in the individual D700, D800 or D900 Series designs in the UL Fire Resistance Directory and as summarized below:
  - A. Concrete — Min 2-1/2 in. (64 mm) to max 8 in. (203 mm) thick reinforced lightweight or normal weight (100-150 pcf or 1600-2400 kg/m<sup>3</sup>) concrete, as measured over crest of fluted steel deck. When concrete topping thickness is min 4-1/2 in. (114 mm), the F and FH Ratings are 3 hr.
  - B. Steel Floor and Form Units — Composite or non-composite max 3 in. (76 mm) deep galv steel fluted units as specified in the individual Floor-Ceiling Design.
2. Metallic Sleeve — (Optional, Not Shown) — Nom 4, 5 or 6 in. (102, 127 or 152 mm) diam Schedule 10 (or heavier) steel sleeve cast or grouted into floor assembly, flush with floor surfaces. When metallic sleeve is used, the T, FT and FTH Ratings are 0 Hr.
- 2A. Sheet Metal Sleeve — (Optional, Not Shown) — Nom 4, 5, 6 or 9 in. (102, 127, 152 or 229 mm) diam, min 26 ga galv steel provided with a 26 ga galv steel square flange spot welded to the sleeve at approx mid-height, or flush with bottom of sleeve in floors, and sized to be a min of 2 in. (51 mm) larger than the sleeve diam. The sleeve is to be cast in place and may extend a max of 4 in. (102 mm) below the bottom of the deck and flush with the top surface of the concrete floor. When sheet metal sleeve is used, the T, FT and FTH Ratings are 0 Hr.
3. Firestop Device — Drop-in firestop device installed in core-drilled or sleeved opening in concrete floor assembly in accordance with accompanying installation instructions. The firestop device flange should be secured to the top surface of the floor with three 1/4 in. (6 mm) diam by min 1-1/4 in. (32 mm) long steel expansion bolts or screw anchors (installed in a triangular fashion through holes provided). As alternates to the anchors specified above, Hilti 1/4 in. (6 mm) diam by 1-1/4 in. (32 mm) long KWIK-BOLT 3 steel expansion anchor or Hilti 1/4 in. (6 mm) by 3/4 in. (19 mm) long Metal HIT Anchor may be used. In addition, for nom 2 in. (51 mm), 3 in. (76 mm) and 4 in. (102 mm) firestop devices, four 11/16 in. (18 mm) long Hilti X-GH P18 MX steel fasteners may be installed through the steel flange, two on each side. The firestop devices shall be installed as detailed in the following table:

4. Through Penetrant — One metallic pipe or tubing to be installed within the firestop device. Pipe or tubing may be rigidly supported on both sides of floor assembly. The following types of pipe or tubing may be used:  
 A. Steel Pipe — Nom 4 in. (102 mm) diam (or smaller) Schedule 10 (or heavier) steel pipe.  
 B. Iron Pipe — Nom 4 in. (102 mm) diam (or smaller) cast or ductile pipe.  
 C. Copper Tubing — Nom 4 in. (102 mm) diam (or smaller) Type L (or heavier) copper tubing.  
 D. Copper Pipe — Nom 4 in. (102 mm) diam (or smaller) Regular (or heavier) copper pipe.  
 E. Tube Insulation — Plastics — Nom 3/4 or 1 in. (19 or 25 mm) thick acrylonitrile butadiene/polyvinyl chloride (AB/PVC) flexible foam furnished in the form of tubing.  
 See Plastiso+ (GMFZ) Category in the Plastics Recognized Component Directory for names of manufacturers. Any Recognized Component tube insulation material meeting the above specifications and having a UL94 Flammability Classification of 94-5VA may be used.  
 5A. Pipe Covering — Nom 1, 1-1/2 or 2 in. (25, 38 or 51 mm) thick hollow cylindrical heavy density (min 3.5 pcf or 56 kg/m<sup>3</sup>) glass fiber units, jacketed on the outside with an all service jacket. Longitudinal joints sealed with metal fasteners or factory-applied SSL tape. Transverse joints secured with metal fasteners or with but tape supplied with the product.  
 See Pipe and Equipment Covering-Materials (BRCU) category in the Building Materials Directory for names of manufacturers. Any pipe covering material meeting the above specifications and bearing the UL Classification Marking with a Flame Spread Index of 25 or less and a Smoke Developed Index of 50 or less may be used.  
 \*Bearing the UL Classification Mark



Reproduced by HILTI, Inc. Courtesy of Underwriters Laboratories, Inc. December 21, 2011

System No. WJ-7130	
ANSI/UL1479 (ASTM E814)	CANULC S115
F Ratings - 1 and 2 Hr (See Item 1)	F Ratings - 1 and 2 Hr (See Item 1)
T Rating - 0 Hr	FT Rating - 0 Hr
L Rating - 0 Hr	FH Ratings - 1 and 2 Hr (See Item 1)
	FTH Rating - 0 Hr




1. Wall Assembly — The 1 or 2 hr fire-rated gypsum board/stud wall assembly shall be constructed of the materials and in the manner specified in the individual D300, D400, V400 or W400 Series Wall and Partition Designs in the UL Fire Resistance Directory and shall include the following construction features:
    - A. Studs — Wall framing may consist of either wood studs or steel channel studs. Wood studs to consist of nom 2 by 4 in. (51 by 102 mm) lumber spaced max 16 in. (406 mm) OC. Steel studs to be min 2-1/2 in. (64 mm) wide and spaced max 24 in. (610 mm) OC.
    - B. Gypsum Board — One or two layers of gypsum board, as specified in the individual Wall and Partition Design. Max area of rectangular opening is 15 sq in. (96 cm<sup>2</sup>) with max dimension of 5 in. (127 mm). In lieu of rectangular opening max diam of circular opening is 3 in. (76 mm).
  - The F and FH Ratings of the firestop system are equal to the hourly fire rating of the wall assembly.
  2. Through Penetrants — One metallic strut, cable, rod or angle service support to be installed within the firestop system. An annular space of min 1/8 in. (3 mm) to max 7/8 in. (22 mm) is required within the firestop system. Strut, cable, rod or angle service support to be rigidly supported on both sides of floor or wall assembly. The strut, cable, rod or angle service support may be installed at an angle not greater than 45 degrees from the perpendicular. The following types and sizes of metallic strut, cable, rod or angle service support may be used:
    - A. Steel Strut — Max 1-5/8 in. (41 by 41 mm) channel strut formed from min 0.105 in. (2.7 mm) thick galv or painted steel.
    - B. Steel Strut — Max 3/4 in. (19 mm) H stud formed from min 0.105 in. (2.7 mm) thick galv or painted steel.
    - C. Cable — Max 3/8 in. (9.5 mm) diam unjacketed galv steel cable.
    - D. Threaded Rod — Max 1 in. (25 mm) diam galv steel threaded rod.
    - E. Steel Angle — 2 by 1/8 in. (51 by 3 mm) thick steel angle.
  3. Firestop System — The firestop system shall consist of the following:
    - A. Packing Material — Min 1/2 in. (13 mm) thickness of min 4 pcf (64 kg/m<sup>3</sup>) mineral wool batt insulation firmly packed into opening as a permanent form. Packing material to be located between penetrant and periphery of opening, and within channels of studs. Packing material to be recessed from both surfaces of wall to accommodate the required thickness of fl material. When through penetrant is oriented perpendicular to wall or when Type FS-ONE Sealant (Item 3B) is used, packing material is optional.
    - B. Fire "Void or Cavity Material" Sealant — Min 5/8 in. (16 mm) thickness of fl material applied within the annulus and within the channel studs, flush with both surfaces of wall.
    - C. Firestop Sealant, CP 606 Sealant or FS-ONE MAX Intumescent Sealant.
- \*Indicates such products shall bear the UL or cUL Certification Mark for jurisdictions employing the UL or cUL Certification (such as Canada), respectively.



Reproduced by HILTI, Inc. Courtesy of Underwriters Laboratories, Inc. January 27, 2015

System No. F-A-1128	
ANSI/UL1479 (ASTM E814)	CANULC S115
F Ratings — 2 and 3 Hr (See Items 1 and 1A)	F Ratings — 2 and 3 Hr (See Items 1 and 1A)
T Ratings — 0 and 1/4 Hr (See Item 2)	FT Ratings — 0 and 1/4 Hr (See Item 2)
L Rating At Ambient — Less Than 1 CFM/sq ft (See Item 3A)	FH Ratings — 0 and 3 Hr (See Items 1 and 1A)
L Rating At 400 F — 4 CFM/sq ft (See Item 3A)	FTH Ratings — 0 and 1/4 Hr (See Item 2)
W Rating — Class 1 (See Item 3A)	L Rating At Ambient — Less Than 1 CFM/sq ft (See Item 3A)
	L Rating At 400 F — Less Than 1 CFM/sq ft (See Item 3A)



1. Floor Assembly — Min 2-1/2 in. (64 mm) to max 8 in. (203 mm) thick reinforced lightweight or normal weight (100-150 pcf or 1600-2400 kg/m<sup>3</sup>) concrete. When concrete thickness is min 4-1/2 in. (114 mm), the F and FH Ratings are 3 hr.
- 1A. Floor Assembly — (Optional, Not Shown) — The fire rated concrete and steel deck floor assembly shall be constructed of the materials and in the manner specified in the individual D700, D800 or D900 Series designs in the UL Fire Resistance Directory and as summarized below:
  - A. Concrete — Min 2-1/2 in. (64 mm) to max 8 in. (203 mm) thick reinforced lightweight or normal weight (100-150 pcf or 1600-2400 kg/m<sup>3</sup>) concrete, as measured over crest of fluted steel deck. When concrete topping thickness is min 4-1/2 in. (114 mm), the F and FH Ratings are 3 hr.
  - B. Steel Floor and Form Units — Composite or non-composite max 3 in. (76 mm) deep galv steel fluted units as specified in the individual Floor-Ceiling Design.
2. Metallic Sleeve — (Optional, Not Shown) — Nom 4, 5 or 6 in. (102, 127 or 152 mm) diam Schedule 10 (or heavier) steel sleeve cast or grouted into floor assembly, flush with floor surfaces. When metallic sleeve is used, the T, FT and FTH Ratings are 0 Hr.
- 2A. Sheet Metal Sleeve — (Optional, Not Shown) — Nom 4, 5, 6 or 9 in. (102, 127, 152 or 229 mm) diam, min 26 ga galv steel provided with a 26 ga galv steel square flange spot welded to the sleeve at approx mid-height, or flush with bottom of sleeve in floors, and sized to be a min of 2 in. (51 mm) larger than the sleeve diam. The sleeve is to be cast in place and may extend a max of 4 in. (102 mm) below the bottom of the deck and flush with the top surface of the concrete floor. When sheet metal sleeve is used, the T, FT and FTH Ratings are 0 Hr.
3. Firestop Device — Drop-in firestop device installed in core-drilled or sleeved opening in concrete floor assembly in accordance with accompanying installation instructions. The firestop device flange should be secured to the top surface of the floor with three 1/4 in. (6 mm) diam by min 1-1/4 in. (32 mm) long steel expansion bolts or screw anchors (installed in a triangular fashion through holes provided). As alternates to the anchors specified above, Hilti 1/4 in. (6 mm) diam by 1-1/4 in. (32 mm) long KWIK-BOLT 3 steel expansion anchor or Hilti 1/4 in. (6 mm) by 3/4 in. (19 mm) long Metal HIT Anchor may be used. In addition, for nom 2 in. (51 mm), 3 in. (76 mm) and 4 in. (102 mm) firestop devices, four 11/16 in. (18 mm) long Hilti X-GH P18 MX steel fasteners may be installed through the steel flange, two on each side. The firestop devices shall be installed as detailed in the following table:

Core Hole or Sleeve Diam, In. (mm)	Firestop Device	Nom Diam of Through Penetrant, In. (mm)
4 (102)	CFS-DID 2"MD	2 (51) or smaller*
5 (102)	CFS-DID 3"MD	3 (76)
6 (152)	CFS-DID 4"MD	4 (102)
9 (229)	CFS-DID 6"MD	6 (152)

\* For pipe smaller than nom 2 in. (51 mm) diam, Adapter and Top Seal Plug is required to be used.  
 H