

1. Wall Assembly —Min 6 in. (152 mm) thick reinforced lightweight or normal weight (100-150 pcf or 1600 - 2400 kg/m3) concrete wall. Wall may also be constructed of any UL Classified Concrete Blocks*. Max area of opening is 360 in2 (2323 cm2) with max dimension of 24-1/2 in. (622 mm).

See Concrete Blocks (CAZT) category in the Fire Resistance Directory for names of manufacturers.

- 2. Through Penetrants —One or more nom 2 in. (51 mm) diam (or smaller) rigid steel conduit or electrical metallic tubing (EMT) to be installed within the opening. The annular space between conduits or tubing shall be min 0 in. (point contact) to max 2 in. (51 mm). The annular space between conduits or tubing and periphery of opening shall be min ½ in. (13 mm) to max 2 in. (51 mm). Conduit or tubing to be rigidly supported on both sides of wall assembly.
- 3. Fill, Void or Cavity Material* Foam Fill material applied to completely fill annulus, flush with both surfaces of the wall. Min fill material thickness is 6 in. (152 mm).

HILTI CONSTRUCTION CHEMICALS, DIV OF HILTI INC - CP 660 Firestop Foam

* Indicates such products shall bear the UL or cUL Certification Mark for jurisdictions employing the UL or cUL Certification (such as Canada), respectively.



Reproduced by HILTI, Inc. Courtesy of Underwriters Laboratories, Inc. September 15, 2021