

UL/cUL SYSTEM NO. HW-D-0934

## TOP OF WALL JOINT : GYPSUM WALL ASSEMBLY

ASSEMBLY RATING = 1-HR. OR 2-HR.


CLASS II OR III MOVEMENT CAPABILITIES - 62% OR 86% COMPRESSION OR EXTENSION OR  
92% COMPRESSION ONLY (SEE TABLE BELOW)

L-RATING AT AMBIENT = 1 CFM / LIN FT


L-RATING AT 400°F = LESS THAN 1 CFM / LIN FT

HW-D0392d.100424

### BOTTOM VIEW



### SECTION A-A



Hilti, Inc.  
Plano, Texas USA (800) 879-8000

Sheet	1 of 3
Scale	1/8" = 1"
Date	Oct. 04, 2024

Drawing No.  
**HWD**  
**0934d**

*Saving Lives through Innovation and Education*

**TOP OF WALL JOINT : GYPSUM WALL ASSEMBLY**

ASSEMBLY RATING = 1-HR. OR 2-HR.

CLASS II OR III MOVEMENT CAPABILITIES - 62% OR 86% COMPRESSION OR EXTENSION OR  
92% COMPRESSION ONLY (SEE TABLE BELOW)

L-RATING AT AMBIENT = 1 CFM / LIN FT

L-RATING AT 400°F = LESS THAN 1 CFM / LIN FT

1. FLOOR OR ROOF ASSEMBLY (THE HOURLY RATING OF THE FLOOR OR ROOF ASSEMBLY SHALL BE EQUAL TO OR GREATER THAN THE HOURLY RATING OF THE WALL ASSEMBLY):

- A. REINFORCED CONCRETE (MIN. 2-1/2" THICK) OVER COMPOSITE METAL DECK (MAX. 4" DEEP FLUTES) (BY EPIC METALS).
  - A1. STEEL FLOOR AND FORM UNITS — COMPOSITE MAX 2 IN. (51 MM) AND MAX 3.5 IN. (89 MM) DEEP GALV STEEL FLUTED UNITS. (NEW MILLENNIUM BUILDING SYSTEMS L L C — VERSA-DEK®, VERSA-DEK® 3.5VLSC).
  - A2. STEEL FLOOR AND FORM UNITS — COMPOSITE MAX 2 IN. (51 MM) AND MAX 3.5 IN. (89MM) DEEP GALV STEEL FLUTED UNITS. (VERCO DECKING INC — A NUCOR CO — TYPE 2.0D FORMLOK, TYPE 3.5D FORMLOK).
  - A3. STEEL FLOOR AND FORM UNITS — COMPOSITE MAX 2 IN. (51 MM) AND MAX 3.5 IN. (89MM) DEEP GALV STEEL FLUTED UNITS. (VULCRAFT, DIV OF NUCOR CORP — TYPE 2.0D FORMLOK, TYPE 3.5D FORMLOCK).
- B. [NOT SHOWN] FLUTED STEEL ROOF DECK (UL/cUL CLASSIFIED P900 SERIES) CONSISTING OF INSULATING CONCRETE (MIN. 2-1/2" THICK) OVER COMPOSITE METAL DECK (MAX. 4" DEEP FLUTES) (BY EPIC METALS).
- C. REINFORCED CONCRETE (MIN. 2-1/2" THICK) OVER COMPOSITE METAL DECK (MAX. 2" DEEP FLUTES VERSA-DEK® OR MAX. 3-1/2" DEEP FLUTES VERSA-DEK® 3.5 VLSC) (BY NEW MILLENNIUM BUILDING SYSTEMS).

2. GYPSUM WALL ASSEMBLY (UL/cUL CLASSIFIED U400, V400, OR W400 SERIES) (1-HR. OR 2-HR. FIRE-RATING). THE HOURLY RATING OF THE JOINT SYSTEM IS DEPENDENT UPON THE HOURLY RATING OF THE WALL ASSEMBLY.

3. CEILING RUNNER (MIN. 25 GA., FLANGE HEIGHT OF CEILING RUNNER SHALL BE MINIMUM 1" GREATER THAN MAXIMUM EXTENDED JOINT WIDTH) INSTALLED AT AN ANGLE TO THE FLUTED STEEL DECK AND FASTENED TO UNDERSIDE OF DECK WITH STEEL MASONRY ANCHORS, STEEL FASTENERS, OR WELDS (SPACED MAX. 24" O.C.) (SEE NOTE BELOW).

4. STEEL STUDS (MIN. 3-5/8" WIDE), CUT 3/4" TO 1" LESS IN LENGTH THAN ASSEMBLY HEIGHT, NESTING IN CEILING RUNNER WITHOUT ATTACHMENT.

5. 5/8" OR 1-1/4" THICKNESS GYPSUM WALLBOARD AS SPECIFIED IN THE INDIVIDUAL UL DESIGN. TOP ROW OF SCREWS SHALL BE INSTALLED INTO STUDS 3-1/2" TO 5-1/2" BELOW THE BOTTOM OF THE CEILING RUNNER.

6. HILTI CFS-TTS MD OS OR CFS-TTS MD 600 TOP TRACK SEAL INSTALLED OVER CEILING RUNNER PRIOR TO ATTACHMENT TO UNDERSIDE OF STEEL FLOOR UNIT IN ACCORDANCE WITH THE ACCOMPANYING INSTALLATION INSTRUCTIONS.

7. HILTI CP 620 FIRE FOAM INSTALLED TO FILL FLUTES ABOVE WALL ASSEMBLY. FOR 1-HR. RATED WALLS, FIRE FOAM TO BE FLUSH WITH SURFACE OF WALL ON BOTH SIDES OF THE WALL. FOR 2-HR. RATED WALLS, FIRE FOAM TO BE FLUSH WITH OUTER WALL SURFACES AND MAY BE GRADUALLY RECESSED IN FROM FACE OF WALL BY 1/2" TO 1" AS IT RISES TO THE TOP OF THE FLUTES.

HW-D0392d.100424


 Hilti, Inc.  
 Plano, Texas USA (800) 879-8000

Sheet	2 of 3	Drawing No.
Scale	-	
Date	Oct. 04, 2024	

**HWD 0934d**

**TOP OF WALL JOINT : GYPSUM WALL ASSEMBLY**

ASSEMBLY RATING = 1-HR. OR 2-HR.

CLASS II OR III MOVEMENT CAPABILITIES - 62% OR 86% COMPRESSION OR EXTENSION OR  
92% COMPRESSION ONLY (SEE TABLE BELOW)

L-RATING AT AMBIENT = 1 CFM / LIN FT

L-RATING AT 400°F = LESS THAN 1 CFM / LIN FT

HW-D0392d.100424

MAX NOM JOINT WIDTH	MAX MOVEMENT CAPABILITIES		MAX MOVEMENT
7/8"	COMPRESSION	86%	3/4"
	EXTENSION	86%	3/4"
1"	COMPRESSION	62%	5/8"
	EXTENSION	62%	5/8"
1-5/8"	COMPRESSION	92%	1-1/2"
	EXTENSION	0%	0"

AS AN ALTERNATIVE TO THE MOVEMENT PERCENTAGES ABOVE, THE JOINT SYSTEM MAY MOVE FREELY WITHOUT RESTRICTION TO THE PERCENTAGE OF MOVEMENT WITHIN THE RANGE OF A MIN 1/8" TO MAX 1-5/8" JOINT WIDTH.

NOTE : AS AN ALTERNATE TO CEILING RUNNER IN ITEM 3, SLOTTED CEILING RUNNERS MAY BE USED. CONSULT THE UL FIRE RESISTANCE DIRECTORY FOR APPROVED MANUFACTURERS. WHEN SLOTTED CEILING RUNNERS ARE USED, STUDS TO BE SECURED TO CEILING RUNNERS WITH NO. 8 x 1/2" LONG STEEL SCREWS AT MID-HEIGHT OF SLOT ON EACH SIDE OF WALL.



Hilti, Inc.  
Plano, Texas USA (800) 879-8000

Sheet 3 of 3  
Scale -  
Date Oct. 04, 2024

Drawing No.  
**HWD 0934d**