

The following excerpt are pages from the <u>North American</u> <u>Product Technical Guide Volume 3: Modular Support Systems</u> Technical Guide, Edition 1.

Please refer to the publication in its entirety for complete details on this product including load values, approvals/listings, general suitability, finishes, quality, etc.

To consult directly with a team member regarding our modular support system products, contact Hilti's team of technical support specialists between the hours of 7:00am – 6:00pm CST.

US: 877-749-6337 or <u>HNATechnicalServices@hilti.com</u> CA: 1-800-363-4458, ext. 6 or <u>CATechnicalServices@hilti.com</u>

> Hilti, Inc. 7250 Dallas Parkway, Suite 1000 Plano, TX 75024

> > 1-800-879 - 8000 www.hilti.com

# 3.0 MODULAR SUPPORT SYSTEM3.2.2 MT BASE CONNECTORSMT-B-GL O4 OC

# Description

4-hole base plate for MT-90 girder-to-concrete.

## **Material Specifications**

Standard <sup>1</sup>	Grade <sup>1</sup>	F <sub>y</sub> , ksi (MPa)	F <sub>u</sub> , ksi (MPa)
GB/T 1591	Q355 B	51.49 (355)	68.17 (470)

1. Mechanical properties of GB/T 1591 Grade Q355 B meet or exceed the mechanical properties of ASTM A1011 SS Grade 50.

# **Corrosion Protection**


# Hot-Dipped Galvanized (HDG)


MT-B-GL 04 OC
---------------

# **Ordering Information**

Description	Weight Per Piece Ibs (kg)	Quantity Piece(s)	Item No.
MT-B-GL O4 OC	30.86 (14)	1	2272103

# Figure 16 - MT Girder Anchoring to Concrete





### Table 89 - Allowable Strength Design (ASD) Load Data<sup>1,2,3,4</sup>

F <sub>x</sub> Ib (kN)	F <sub>y</sub> lb (kN)	F <sub>z</sub> Ib (kN)	M <sub>y</sub> Ib ft (kN m)	M <sub>z</sub> Ib ft (kN m)
27,175	12,265	12,265	5,560	5,560
(120.9)	(54.56)	(54.56)	(7.54)	(7.54)

Minimum safety factor,  $\Omega$ , for tabulated values is 2.0.

2. Multiply tabulated values by 1.5 to obtain minimum Load and Resistance Factor Design (LRFD) values. 3 See Figure 16

See Figure 16.
Load values are for base connector only. Design professional is responsible for checking concrete and fastener strength.

### Table 90 - Limit State Design (LSD) Load Data<sup>1,2,3</sup>

F <sub>x</sub>	F <sub>y</sub>	F <sub>z</sub>	M	M <sub>z</sub>
lb (kN)	lb (kN)	lb (kN)	lb ft (kN m)	lb ft (kN m)
38,505	17,375	17,375	7,845	7,845
(171.3)	(77.29)	(77.29)	(10.64)	(10.64)

Maximum resistance factor, Φ, for tabulated values is 0.75.

2. See Figure 16.

 Load values are for base connector only. Design professional is responsible for checking concrete and fastener strength.