

The following excerpt are pages from the <u>North American</u> <u>Product Technical Guide Volume 3: Modular Support Systems</u> Technical Guide, Edition 1.

Please refer to the publication in its entirety for complete details on this product including load values, approvals/listings, general suitability, finishes, quality, etc.

To consult directly with a team member regarding our modular support system products, contact Hilti's team of technical support specialists between the hours of 7:00am – 6:00pm CST.

US: 877-749-6337 or <u>HNATechnicalServices@hilti.com</u> CA: 1-800-363-4458, ext. 6 or <u>CATechnicalServices@hilti.com</u>

> Hilti, Inc. 7250 Dallas Parkway, Suite 1000 Plano, TX 75024

> > 1-800-879 - 8000 www.hilti.com

3.0 MODULAR SUPPORT SYSTEM 3.2.3 MT SYSTEM CONNECTORS MT-C-L1

Description

2-hole angle connector for channel.

Material Specifications

Standard ¹	Grade ¹	F _y , ksi (MPa)	F _u , ksi (MPa)
GB/T 1591	Q355 B	51.49 (355)	68.17 (470)

1. Mechanical properties of GB/T 1591 Grade Q355 B meet or exceed the mechanical properties of ASTM A1011 SS Grade 50.

Corrosion Protection

Electro-Galvanized (EG)

MT-C-L1

Hot-Dipped Galvanized (HDG)


MT-C-L1 OC

Ordering Information


Description	Weight Per Piece Ibs (kg)	Quantity Piece(s)	Item No.
MT-C-L1	0.44 (0.20)	20	2271514
MT-C-L1 OC	0.44 (0.20)	20	2271516

A. MT-30/50/60/40D

Figure 27 - MT Channel Connection



Ø11 (7/16") ()57 (2-1/4") \bigcirc 57 42 (2-1/4") (1-5/8") **6** (1/4") mm (in)



F _x	F _z
Ib (kN)	Ib (kN)
1,005	1,005
(4.48)	(4.48)

1. Minimum safety factor, Ω , for tabulated values is 2.65.

Multiply tabulated values by 1.5 to obtain minimum Load and Resistance Factor Design (LRFD) values. 2.

3. See Figure 27.

Table 112 - Limit State Design (LSD) Load Data^{1,2}

F _x Ib (kN)	F _z Ib (kN)
1,295	1,295
(5.78)	(5.78)

Maximum resistance factor, Φ, for tabulated values is 0.5.
See Figure 27.

2023