

The following excerpt are pages from the North American

Product Technical Guide Volume 3: Modular Support Systems

Technical Guide, Edition 1.

Please refer to the publication in its entirety for complete details on this product including load values, approvals/listings, general suitability, finishes, quality, etc.

To consult directly with a team member regarding our modular support system products, contact Hilti's team of technical support specialists between the hours of 7:00am – 6:00pm CST.

US: 877-749-6337 or HNATechnicalServices@hilti.com

CA: 1-800-363-4458, ext. 6 or <a href="mailto:cATechnicalServices@hilti.com">CATechnicalServices@hilti.com</a>



# 3.0 MODULAR SUPPORT SYSTEM

# 3.2.8 MT CLAMPS AND CHANNEL TIES

## MT-CT-H2

# **Description**

Flat plate for channel-to-channel (same size) connections.

#### **Material Specifications**

Standard <sup>1</sup>	Grade <sup>1</sup>	F <sub>y</sub> , ksi (MPa)	F <sub>u</sub> , ksi (MPa)
GB/T 700	Q235 B	34.08 (235)	53.66 (370)

Mechanical properties of GB/T 700 Grade Q235 B meet or exceed the mechanical properties of ASTM A1011 SS Grade 33.

#### **Corrosion Protection**

Electro-Galvanized (EG)

MT-CT-H2


#### **Hot-Dipped Galvanized (HDG)**

MT-CT-H2 OC

#### **Ordering Information**

Description	Weight Per Piece Ibs (kg)	Quantity Piece(s)	Item No.
MT-CT-H2	0.31 (0.14)	15	2322405
MT-CT-H2 OC	0.31 (0.14)	15	2322409

Figure 92 - Single Plate Connection



A. MT-30/50/60/40D

MT-CT-H2




Table 233 - Allowable Strength Design (ASD) Load Data<sup>1,2,3</sup>

F <sub>x</sub> lb (kN)	F <sub>y</sub> lb (kN)	F <sub>z</sub> lb (kN)
350	350	495
(1.56)	(1.56)	(2.22)

- 1. Minimum safety factor,  $\Omega$ , for tabulated values is 2.65.
- Multiply tabulated values by 1.5 to obtain minimum Load and Resistance Factor Design (LRFD) values.
- 3. See Figure 92.


Table 234 - Limit State Design (LSD) Load Data<sup>1,2</sup>



F <sub>x</sub>	F <sub>y</sub>	F <sub>z</sub>
lb (kN)	lb (kN)	lb (kN)
490	490	640
(2.18)	(2.18)	(2.86)

- 1. Maximum resistance factor, φ, for tabulated values is 0.5.
- 2. See Figure 92.

Figure 93 - Double Plate Connection Table 235 - All



A. MT-40D

### Table 235 - Allowable Strength Design (ASD) Load Data 1,2,3,4

F <sub>x</sub>	F <sub>y</sub>	F <sub>z</sub>
lb (kN)	lb (kN)	lb (kN)
700	700	1,615
(3.12)	(3.12)	(7.19)

- 1. Minimum safety factor, Ω, for tabulated values is 3.50.
- Multiply tabulated values by 1.5 to obtain minimum Load and Resistance Factor Design (LRFD) values.
- 3. Tabulated values are based on plates being installed in pairs.
- 4. See Figure 93.

Table 236 - Limit State Design (LSD) Load Data<sup>1,2,3</sup>



F	F	F <sub>z</sub>
lb (kN)	lb (kN)	lb (kN)
975	975	2,100
(4.35)	(4.35)	(9.35)

- 1. Maximum resistance factor, φ, for tabulated values is 0.4.
- 2. Tabulated values are based on plates being installed in pairs.
- 3. See Figure 93.

2023