

MULTIPLE CABLE BUNDL	UL/cUL SYSTEM NO. W-J-3279 ES THROUGH CONCRETE OR BLO	OCK WALL ASSEMBLY			
	F-RATING = 2-HR.				
T-RA	TING = 1/2-HR. OR 1-HR. (SEE NOTE BELO)	<b>V)</b> 3279b.101022			
	ATING AT AMBIENT = SEE TABLE BELOW	9b.1			
L·	RATING AT 400°F = SEE TABLE BELOW	J327			
1. CONCRETE WALL ASSEMBLY (2-I					
B. ANY UL/CUL CLASSIFIED CON	VEIGHT CONCRETE WALL (MINIMUM 6" TH	IICK).			
	INATION OF ANY OF THE FOLLOWING :				
	VG TELEPHONE CABLE WITH PVC JACKE	T AND INSULATION.			
	OPPER CONDUCTOR CONTROL CABLE WI				
INSULATION.					
C. MAXIMUM 4/0 AWG TYPE RHH					
D. MAXIMUM 4 PAIR NO 23 AWG					
	ABLE WITH FLUORINATED ETHYLENE INS				
F. MAXIMUM 1/2" FIBER-OPTIC CABLE WITH PVC OR PE JACKET AND INSULATION. G. MAXIMUM 20/C NO. 22 AWG SHIELDED PRINTER CABLE WITH PVC JACKET.					
	IDEO CABLE CONSISTING OF 2 MAX 24 AV				
PAIR CABLE WITH PE INSULATION AND PVC JACKET					
I. MAXIMUM 2/C NO. 18 AWG POWER OR NON-POWER LIMITED FIRE ALARM CABLE WITH OR WITHOUT					
METAL JACKET (MANUFACTURED BY AFC CABLE SYSTEMS, INC.).					
J. MAXIMUM 3/C NO. 12 AWG METAL CLAD CABLE.					
K. ANY CABLES, METAL-CLAD CABLES, OR ARMORED CABLES CURRENTLY LISTED UNDER THE THROUGH PENETRATING PRODUCTS CATEGORY.					
3. TWO OR MORE HILTI CFS-MSL [S, M, OR L] MODULAR SLEEVES TO BE GANGED TOGETHER WITH					
GANGING CLIPS AND CENTERED IN THE WALL. DEVICES TO SECURED IN FLANGE USING A MINIMUM					
EVERY OTHER SCREW HOLE IN ADJUSTABLE FLANGE (ITEM 5).					
4. [NOT SHOWN] GASKET MATERIAL APPLIED TO BACK OF ADJUSTABLE FLANGE MATERIAL WITH					
INTEGRATED TAPE PRIOR TO FLANGE BEING INSTALLED TO WALL ASSEMBLY.					
5. HILTI CFS-MSL GPA ADJUSTABLE FLANGE [24" x 4" OR 24" x 8"] BOLTED TOGETHER INSTALLED					
AROUND GANGED DEVICES AND SECURED TO WALL WITH MIN 1-1/2" LONG MASONRY SCREWS OR ANCHORS.					
		Sheet 2 4 2			
	HILTI, Inc.	<b>2 of 3</b> Drawing No.			
	Plano, Texas USA (800) 879-8000	······································			
Hilti Firestop Systems	· · · · · · · · · · · · · · · · · · ·	Date Oct. 10, 2022 3279b			

## SystemsDateSaving Lives through Innovation and Education

## UL/cUL SYSTEM NO. W-J-3279 MULTIPLE CABLE BUNDLES THROUGH CONCRETE OR BLOCK WALL ASSEMBLY

## F-RATING = 2-HR. T-RATING = 1/2-HR. OR 1-HR. (SEE NOTE BELOW) L-RATING AT AMBIENT = SEE TABLE BELOW L-RATING AT 400°F = SEE TABLE BELOW

DEVICE	MAX CABLE	CABLE TYPE		L-RATING C	RATING CFM/DEVICE	
	FILL		AMBIENT	400°F		
CFS-MSL S	0%	-	LESS THAN 1	LESS THAN 1		
CFS-MSL S	1-25%	2B, 2D, 2E, 2G, 2H	1.1	1.45		
CFS-MSL S	26-50%	2B, 2D, 2E, 2G, 2H	1.1	LESS THAN 1		
CFS-MSL S	51-75%	2B, 2D, 2E, 2G, 2H	1.8	LESS THAN 1		
CFS-MSL S	76-100%	2B, 2D, 2E, 2G, 2H	1.8	1.2		
CFS-MSL M	0%	-	1.1	LESS THAN 1		
CFS-MSL M	1-25%	2B, 2D, 2E, 2G, 2H	1.8	LESS THAN 1		
CFS-MSL M	26-50%	2B, 2D, 2E, 2G, 2H	1.9	LESS THAN 1		
CFS-MSL M	51-75%	2B, 2D, 2E, 2G, 2H	1.9	LESS THAN 1		
CFS-MSL M	76-100%	2B, 2D, 2E, 2G, 2H	2.2	1.1		
CFS-MSL L	0%	-	1.2	LESS THAN 1		
CFS-MSL L	1-25%	2B, 2D, 2E, 2G, 2H	1.8	1.1		
CFS-MSL L	26-50%	2B, 2D, 2E, 2G, 2H	2.2	1.0		
CFS-MSL L	51-75%	2B, 2D, 2E, 2G, 2H	2.6	1.4		
CFS-MSL L	76-100%	2B, 2D, 2E, 2G, 2H	3.0	1.6		

NOTES : 1. MAXIMUM SIZE OF OPENING = 24-1/8" x 8-1/8".

2. ANNULAR SPACE = MINIMUM 0", MAXIMUM 1/8".

3. CABLES MAY REPRESENT 0% TO 100% VISUAL FILL OF EACH FIRESTOP DEVICE.

4. THE T-RATING EQUALS 1-HR. EXCEPT WHEN ITEM 2K IS USED THE T-RATING EQUALS 1/2-HR.

5. L-RATINGS ARE DEPENDENT ON TYPE AND NUMBER OF DEVICES WITHIN THE GANG PLATE AND THE CABLE TYPE AND FILL. A RATING OF LESS THAN ONE SHALL BE CONSIDERED 1 CFM WHEN MORE THAN ONE MODULE IS INSTALLED.



HILTI, Inc. Plano, Texas USA (800) 879-8000

Sheet	3 of 3	Drawing No.
Scale	-	WJ
Date	Oct. 10, 2022	3279b

Saving Lives through Innovation and Education