FD1125a 092313

UL/cUL SYSTEM NO. FF-D-1125

FIRE-RATED JOINT THROUGH CONCRETE FLOOR ASSEMBLY


ASSEMBLY RATING = 4-HR.


L-RATING AT AMBIENT = LESS THAN 1 CFM / LIN FT L-RATING AT 400°F = LESS THAN 1 CFM / LIN FT

CLASS II MOVEMENT CAPABILITIES - 12.5% COMPRESSION OR EXTENSION

TOP VIEW

SECTION A-A





- 1. LIGHTWEIGHT OR NORMAL WEIGHT CONCRETE FLOOR ASSEMBLY (MINIMUM 5-1/2" THICK) (4-HR. FIRE-RATING).
- 2. MINIMUM 5" THICKNESS MINERAL WOOL SAFING (MIN. 4 PCF DENSITY) COMPRESSED 50% AND RECESSED TO ACCOMMODATE FIRESTOP SEALANT.
- 3. MINIMUM 1/4" DEPTH HILTI CFS-S SIL GG OR CFS-S SIL SL FIRESTOP SILICONE SEALANT FLUSH WITH THE TOP SURFACE OF FLOOR.

NOTE: MAXIMUM WIDTH OF JOINT = 3".



HILTI, Inc. Tulsa, Oklahoma USA (800) 879-8000

Sheet	1 of 1
Scale	3/16" = 1"
Date	Sep. 23, 2013

FFD 1125a