

UL SYSTEM NO. C-AJ-2109 PLASTIC PIPE THROUGH FLOOR/WALL OR BLOCK WALL ASSEMBLY

F-RATING = 2-HR. OR 3-HR. T-RATING = 0-HR., 2-HR., OR 3-HR. L-RATING AT AMBIENT = LESS THAN 1 CFM / SQ FT (SEE NOTE NO. 9 BELOW) L-RATING AT 400°F = LESS THAN 1 CFM / SQ FT (SEE NOTE NO. 9 BELOW) W-RATING = CLASS I (SEE NOTES NO. 7 AND 8 BELOW)

5. HILTI CP 643N OR CP 644 FIRESTOP COLLAR WITH FASTENING HOOKS (SEE TABLE BELOW).

6. EACH FASTENING HOOK SECURED TO BOTTOM OF FLOOR WITH 1/4" x 1-1/4" LONG STEEL EXPANSION BOLTS, MIN. 0.145" x 1-1/4" POWDER ACTUATED FASTENERS WITH 1-7/16" DIAMETER STEEL WASHER, 1/4" x 1-1/4" HILTI KWIK-CON II+ CONCRETE SCREW ANCHOR, 1/4" x 1-3/4" HILTI KWIK-BOLT 3 STEEL EXPANSION ANCHOR, OR HILTI X-DNI 27 P8 S15 POWDER ACTUATED FASTENER WITH INTEGRATED WASHER.

PIPE TYPE	NOMINAL PIPE DIAMETER	PRODUCT DESCRIPTION	F-RATING	T-RATING
PVC, CPVC, ABS, FRPP	1-1/2"	CP 643 50/1.5" N	3	2
PVC, CPVC, ABS, FRPP	2"	CP 643 63/2" N	3	2
PVC, CPVC, ABS, FRPP	3"	CP 643 90/3" N	3	2
PVC, CPVC, ABS, FRPP	4"	CP 643 110/4" N	3	3
PVC, CPVC, ABS (SOLID CORE), FRPP	6"	CP 643 160/6" N	3	3
ABS (CELLULAR CORE)	6"	CP 643 160/6" N	3	0
PVC, CPVC	8"	CP 644 200/8"	2	0
PVC, CPVC	10"	CP 644 250/10"	2	0

NOTES : 1. HILTI FIRESTOP COLLARS, HILTI FS-ONE MAX INTUMESCENT FIRESTOP SEALANT OR HILTI CFS-S SIL GG FIRESTOP SILICONE SEALANT ARE REQUIRED ON BOTH SIDES OF A WALL ASSEMBLY.

- 2. MAXIMUM DIAMETER OF OPENING = 12".
- 3. ANNULAR SPACE ON PIPES NOMINAL 6" AND SMALLER = MINIMUM 0", MAXIMUM 1/2".
- 4. ANNULAR SPACE ON PIPES LARGER THAN NOMINAL 6" = MINIMUM 0", MAXIMUM 1-1/4".
- 5. CLOSED OR VENTED PIPING SYSTEM (PVC, ABS, & FRPP = SCHEDULE 40, CPVC = SDR 13.5).
- 6. HILTI FIRESTOP SEALANT IS OPTIONAL ON PIPES HAVING A MAXIMUM DIAMETER OF NOMINAL 6" INSTALLED IN UNSLEEVED OPENINGS.
- 7. W-RATING DOES NOT APPLY IN SLEEVED OPENINGS.
- 8. W-RATING APPLIES ONLY WHEN ANNULAR SPACE IS MINIMUM 0", MAXIMUM 1/2", AND HILTI CFS-S SIL GG FIRESTOP SILICONE SEALANT OR HILTI CFS-S SIL SL FIRESTOP SILICONE SEALANT IS USED.

9. L-RATING APPLIES ONLY WHEN HILTI CFS-S SIL GG FIRESTOP SILICONE SEALANT OR HILTI CFS-S SIL SL FIRESTOP SILICONE SEALANT IS USED.

10. WHEN HILTI CFS-S SIL SL FIRESTOP SILICONE SEALANT IS USED, A MINIMUM 1/2" THICKNESS OF MINERAL WOOL (MIN. 4 PCF DENSITY) TIGHTLY PACKED IS TO BE INSTALLED WITHIN THE ANNULAR SPACE AND RECESSED FROM THE TOP SURFACE OF CONCRETE FLOOR TO ACCOMMODATE SEALANT.

	HILTI, Inc. Plano, Texas USA (800) 879-8000	Sheet	2 of 2	Drawing No.		
		Scale		CAJ		
Hilti Firestop Systems	1 Iano, 16xas 03A (000) 073-0000		Sep. 13, 2022	2109w		
Saving Lives through Innovation and Education						