

The following excerpt are pages from the <u>North American</u> <u>Product Technical Guide Volume 3: Modular Support Systems</u> Technical Guide, Edition 1.

Please refer to the publication in its entirety for complete details on this product including load values, approvals/listings, general suitability, finishes, quality, etc.

To consult directly with a team member regarding our modular support system products, contact Hilti's team of technical support specialists between the hours of 7:00am – 6:00pm CST.

US: 877-749-6337 or <u>HNATechnicalServices@hilti.com</u> CA: 1-800-363-4458, ext. 6 or <u>CATechnicalServices@hilti.com</u>

> Hilti, Inc. 7250 Dallas Parkway, Suite 1000 Plano, TX 75024

> > 1-800-879 - 8000 www.hilti.com



3.0 MODULAR SUPPORT SYSTEM 3.2.3 MT SYSTEM CONNECTORS MT-C-GSP L OC

Description

Gusset plate for L-shaped connections with MT-70 and MT-80 girders.

Material Specifications

Standard ¹	Grade ¹	F _y , ksi (MPa)	F _u , ksi (MPa)
GB/T 1591	Q355 B	51.49 (355)	68.17 (470)

1. Mechanical properties of GB/T 1591 Grade Q355 B meet or exceed the mechanical properties of ASTM A1011 SS Grade 50.

Corrosion Protection


Hot-Dipped Galvanized (HDG)


MT-C-GSP L OC	

Ordering Information

Description	Weight Per Piece Ibs (kg)	Quantity Piece(s)	Item No.
MT-C-GSP L OC	0.93 (0.42)	10	2272073

Figure 47 - MT Girder Connection








Table 151 - Allowable Strength Design (ASD) Load Data^{1,2,3,4}

F _x	F _y	F _z	M _y	M _z
Ib (kN)	Ib (kN)	Ib (kN)	ft lb (kN cm)	ft lb (kN m)
3,035	785	2,415	560	300
(13.52)	(3.50)	(10.76)	(0.76)	(0.41)

1. Minimum safety factor, Ω , for tabulated values is 2.1.

2. Multiply tabulated values by 1.5 to obtain minimum Load and Resistance Factor Design (LRFD) values.

Tabulated values are based on brackets being installed in pairs.
See Figure 47.

Table 152 - Limit State Design (LSD) Load Data^{1,2,3}

		• •		
F _x	F _y	F _z	M _y	M _z
Ib (kN)	Ib (kN)	Ib (kN)	ft lb (kN cm)	ft lb (kN m)
4,310	1,180	3,435	815	455
(19.19)	(5.25)	(15.28)	(1.11)	(0.62)

1. Maximum resistance factor, ϕ , for tabulated values is 0.7.

Tabulated values are based on brackets being installed in pairs.
See Figure 47.