C1009u 041618

UL/cUL SYSTEM NO. F-C-1009


METAL PIPE THROUGH WOOD FLOOR/CEILING ASSEMBLY

F-RATING = 1-HR. OR 2-HR.

T-RATING = 1/4-HR.

L-RATING AT AMBIENT = LESS THAN 1 CFM / SQ FT

L-RATING AT 400° F = 4 CFM / SQ FT



- 1. WOOD FLOOR/CEILING ASSEMBLY (UL/cUL CLASSIFIED L500 SERIES) (1-HR. OR 2-HR. FIRE-RATING) (2-HR. SHOWN).
- 2. [OPTIONAL] FIRE-RATED OR NON-RATED SINGLE, DOUBLE, OR STAGGERED WOOD STUD/GYPSUM CHASE WALL ASSEMBLY CONSISTING OF NOMINAL 2" x 6" OR PARALLEL 2" x 4" LUMBER PLATES AND STUDS.
- 3. PENETRATING ITEM TO BE ONE OF THE FOLLOWING:
 - A. MAXIMUM 4" NOMINAL DIAMETER STEEL PIPE (SCHEDULE 10 OR HEAVIER).
 - B. MAXIMUM 4" NOMINAL DIAMETER CAST OR DUCTILE IRON PIPE.
 - C. MAXIMUM 4" NOMINAL DIAMETER COPPER PIPE OR TUBING.
 - D. MAXIMUM 4" NOMINAL DIAMETER STEEL CONDUIT OR EMT.
- 4. MINIMUM 3/4" DEPTH HILTI FS-ONE MAX INTUMESCENT FIRESTOP SEALANT, HILTI CP 606 FLEXIBLE FIRESTOP SEALANT, OR HILTI CFS-S SIL GG FIRESTOP SILICONE SEALANT FLUSH WITH TOP SURFACE OF FLOOR OR SOLE PLATE.
- 5. MINIMUM 5/8" DEPTH HILTI FS-ONE MAX INTUMESCENT FIRESTOP SEALANT, HILTI CP 606 FLEXIBLE FIRESTOP SEALANT, OR HILTI CFS-S SIL GG FIRESTOP SILICONE SEALANT FLUSH WITH BOTTOM SURFACE OF CEILING OR LOWER TOP PLATE.
 - NOTES: 1. DIAMETER OF OPENING TO BE MAXIMUM 1" LARGER THAN DIAMETER OF PIPE OR SQUARE-CUT WITH A MAXIMUM DIMENSION 1" GREATER THAN THE DIAMETER OF PIPE.
 - 2. WHEN LUMBER PLATES ARE DISCONTINUOUS, ATTACH A NOMINAL 1-1/2" WIDE 20 GA. (OR HEAVIER) GALVANIZED STEEL PLATE TO EACH END OF LUMBER PLATE. STEEL PLATES SHOULD OVERLAP 2" ONTO LUMBER, AND SECURED WITH STEEL SCREWS OR NAILS.
 - 3. ANNULAR SPACE = MINIMUM 0", MAXIMUM 1".
 - 4. L-RATINGS APPLY ONLY WHEN HILTI FS-ONE MAX INTUMESCENT FIRESTOP SEALANT IS USED.



HILTI, Inc. Plano, Texas USA (800) 879-8000

Sheet	1 of 1
Scale	3/32" = 1"
Date	Apr. 16, 2018

FC 1009u