


PLAN VIEW


BOLT DESCRIPTION	ITEM NUMBER	BOLT LENGTH, "L" IN. [MM]
HBC-C M12x40 8.8F	2095644	1.57 [40]
HBC-C M12x50 8.8F	2095645	1.97 [50]
HBC-C M12x60 8.8F	2095646	2.36 [60]
HBC-C M12x80 8.8F	2095647	3.15 [80]
HBC-C M12x100 8.8F	2095648	3.94 [100]

NOTE: NUT IS INCLUDED WITH T-BOLT


ITEM	WASHER DESCRIPTION	ITEM NUMBER
A	FLAT WASHER A 13/24-F	304771
B	M12 SPLIT WASHER DIN127 HDG	2150395




ELEVATION VIEW




SIDE VIEW




PLAN VIEW




SIDE VIEW




PLAN VIEW



SIDE VIEW



PLAN VIEW



SIDE VIEW


Note:
T-BOLTS AND HARDWARE ARE METRIC SIZES. DIMENSIONS ARE CONVERTED TO IMPERIAL UNITS TO THE NEAREST TWO DECIMAL PLACES.



ITEM NUMBER: VARIES	CHANNEL LIP: SMOOTH 
-------------------------------	---

ITEM DESCRIPTION:
HBC-C M12-T-BOLT, NUT & WASHERS






PLAN VIEW


BOLT DESCRIPTION	ITEM NUMBER	BOLT LENGTH, "L" IN. [MM]
HBC-C M16x50 8.8F	2095649	1.97 [50]
HBC-C M16x60 8.8F	2095650	2.36 [60]
HBC-C M16x80 8.8F	2095651	3.15 [80]
HBC-C M16x100 8.8F	2095652	3.94 [100]

NOTE: NUT IS INCLUDED WITH T-BOLT


ITEM	WASHER DESCRIPTION	ITEM NUMBER
A	FLAT WASHER A 17/30-F	304772
B	M16 SPLIT WASHER DIN127 HDG	2150396




ELEVATION VIEW




SIDE VIEW




PLAN VIEW




SIDE VIEW




PLAN VIEW



SIDE VIEW



PLAN VIEW



SIDE VIEW


Note:
T-BOLTS AND HARDWARE ARE METRIC SIZES. DIMENSIONS ARE CONVERTED TO IMPERIAL UNITS TO THE NEAREST TWO DECIMAL PLACES.



ITEM NUMBER: VARIES	CHANNEL LIP: SMOOTH 
-------------------------------	---

ITEM DESCRIPTION:
HBC-C M16-T-BOLT, NUT & WASHERS






PLAN VIEW


BOLT DESCRIPTION	ITEM NUMBER	BOLT LENGTH, "L" IN. [MM]
HBC-C M20x60 8.8F	2095653	2.36 [60]
HBC-C M20x80 8.8F	2095654	3.15 [80]
HBC-C M20x100 8.8F	2095655	3.94 [100]
HBC-C M20x125 8.8F	2095656	4.92 [125]
HBC-C M20x150 8.8F	2095657	5.91 [150]

NOTE: NUT IS INCLUDED WITH T-BOLT


WASHER DESCRIPTION	ITEM NUMBER
FLAT WASHER A 21/37-F	2008399




ELEVATION VIEW




SIDE VIEW




PLAN VIEW



SIDE VIEW



PLAN VIEW



SIDE VIEW


Note:
T-BOLTS AND HARDWARE ARE METRIC SIZES. DIMENSIONS ARE CONVERTED TO IMPERIAL UNITS TO THE NEAREST TWO DECIMAL PLACES.



ITEM NUMBER: VARIES	CHANNEL LIP: SMOOTH 
-------------------------------	---

ITEM DESCRIPTION:
HBC-C M20-T-BOLT, NUT & WASHERS






PLAN VIEW


BOLT DESCRIPTION	ITEM NUMBER	BOLT LENGTH, "L" IN. [MM]
HBC-C-N M12x40 8.8F	2066370	1.57 [40]

NOTE: NUT IS INCLUDED WITH T-BOLT


ITEM	WASHER DESCRIPTION	ITEM NUMBER
A	FLAT WASHER A 13/24-F	304771
B	M12 SPLIT WASHER DIN127 HDG	2150395




ELEVATION VIEW




SIDE VIEW




PLAN VIEW




SIDE VIEW




PLAN VIEW



SIDE VIEW



PLAN VIEW



SIDE VIEW


Note:
T-BOLTS AND HARDWARE ARE METRIC SIZES. DIMENSIONS ARE CONVERTED TO IMPERIAL UNITS TO THE NEAREST TWO DECIMAL PLACES.



ITEM NUMBER: VARIES	CHANNEL LIP: SMOOTH 
-------------------------------	---

ITEM DESCRIPTION:
HBC-C-N M12-T-BOLT, NUT & WASHERS







PLAN VIEW

BOLT DESCRIPTION	ITEM NUMBER	BOLT LENGTH, "L" IN. [MM]
HBC-C-N M16x40 8.8F	2069471	1.57 [40]
HBC-C-N M16x50 8.8F	433478	1.97 [50]
HBC-C-N M16x60 8.8F	2019736	2.36 [60]
HBC-C-N M16x80 8.8F	433479	3.15 [80]
HBC-C-N M16x100 8.8F	2019737	3.94 [100]
HBC-C-N M16x150 8.8F	2019738	5.91 [150]


NOTE: NUT IS INCLUDED WITH T-BOLT




ELEVATION VIEW




SIDE VIEW




PLAN VIEW




SIDE VIEW




PLAN VIEW



SIDE VIEW



PLAN VIEW



SIDE VIEW


Note:
T-BOLTS AND HARDWARE ARE METRIC SIZES. DIMENSIONS ARE CONVERTED TO IMPERIAL UNITS TO THE NEAREST TWO DECIMAL PLACES.



ITEM NUMBER: VARIES	CHANNEL LIP: SMOOTH 
-------------------------------	---

ITEM DESCRIPTION:
HBC-C-N M16-T-BOLT, NUT & WASHERS






PLAN VIEW


BOLT DESCRIPTION	ITEM NUMBER	BOLT LENGTH, "L" IN. [MM]
HBC-C-N M20x80 8.8F	2019739	3.15 [80]
HBC-C-N M20x150 8.8F	2019820	5.91 [150]

NOTE: NUT IS INCLUDED WITH T-BOLT


WASHER DESCRIPTION	ITEM NUMBER
FLAT WASHER A 21/37-F	2008399




ELEVATION VIEW




SIDE VIEW




PLAN VIEW



SIDE VIEW



PLAN VIEW



SIDE VIEW


Note:
T-BOLTS AND HARDWARE ARE METRIC SIZES. DIMENSIONS ARE CONVERTED TO IMPERIAL UNITS TO THE NEAREST TWO DECIMAL PLACES.



ITEM NUMBER: VARIES	CHANNEL LIP: SMOOTH 
-------------------------------	---

ITEM DESCRIPTION:
HBC-C-N M20-T-BOLT, NUT & WASHERS







PLAN VIEW

BOLT DESCRIPTION	ITEM NUMBER	BOLT LENGTH, "L" IN. [MM]
HBC-C M12x40 50R	2095684	1.57 [40]
HBC-C M12x40 50R	433463	1.57 [40]
HBC-C M12x50 50R	2095685	1.97 [50]
HBC-C M12x50 50R	433465	1.97 [50]
HBC-C M12x80 50R	2095686	3.15 [80]
HBC-C M12x80 50R	433466	3.15 [80]
HBC-C M12x100 50R	2095687	3.94 [100]
HBC-C M12x100 50R	433467	3.94 [100]


NOTE: NUT IS INCLUDED WITH T-BOLT




ELEVATION VIEW



SIDE VIEW




PLAN VIEW




SIDE VIEW


ITEM	WASHER DESCRIPTION	ITEM NUMBER
A	FLAT WASHER A 13/24-F	304771
B	M12 SPLIT WASHER DIN127 HDG	2150395




PLAN VIEW



SIDE VIEW



PLAN VIEW




SIDE VIEW

Note:
T-BOLTS AND HARDWARE ARE METRIC SIZES. DIMENSIONS ARE CONVERTED TO IMPERIAL UNITS TO THE NEAREST TWO DECIMAL PLACES.



ITEM NUMBER: VARIES	CHANNEL LIP: SMOOTH 
ITEM DESCRIPTION: HBC-C M12 50R-T-BOLT, NUT & WASHERS	






PLAN VIEW


BOLT DESCRIPTION	ITEM NUMBER	BOLT LENGTH, "L" IN. [MM]
HBC-C M16x50 50R	2095688	1.97 [50]
HBC-C M16x50 50R	433471	1.97 [50]
HBC-C M16x60 50R	2095689	2.36 [60]
HBC-C M16x80 50R	2095690	3.15 [80]
HBC-C M16x100 50R	2095691	3.94 [100]

NOTE: NUT IS INCLUDED WITH T-BOLT


ITEM	WASHER DESCRIPTION	ITEM NUMBER
A	FLAT WASHER A 17/30-F	304772
B	M16 SPLIT WASHER DIN127 HDG	2150396




ELEVATION VIEW




SIDE VIEW




PLAN VIEW




SIDE VIEW




PLAN VIEW



SIDE VIEW




PLAN VIEW



SIDE VIEW

Note:
T-BOLTS AND HARDWARE ARE METRIC SIZES. DIMENSIONS ARE CONVERTED TO IMPERIAL UNITS TO THE NEAREST TWO DECIMAL PLACES.



ITEM NUMBER: VARIES	CHANNEL LIP: SMOOTH 
-------------------------------	---

ITEM DESCRIPTION:
HBC-C M16 50R-T-BOLT, NUT & WASHERS

